



Maxos LED inserts for TTX400 – efficiency champion with great payback

Maxos LED inserts for TTX400

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven TTX400 trunking system

Maxos LED inserts for TTX400


Features

- Mid-power LED boards; exchangeable LED unit
- Up to 169 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of medium, wide and double asymmetric beam lenses
- Compatible with our standard TTX400 rails for TL5 49 W and TL-D 58 W lengths


Application

- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers, showrooms

Dimensional drawing



Product details



Maxos LED inserts for TTX400

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	-
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	≥80
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%
Suitable for random switching	Not applicable

General Information

			Lamp family	Embedded control	Product family
Order Code	Full Product Name	Glow-wire test	code		code
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	Temperature 650 °C, duration 30 s	LED66S	Constant light output	4MX400
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	Temperature 850 °C, duration 30 s	LED66S	-	4MX433
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	Temperature 650 °C, duration 30 s	LED55S	-	4MX433

Maxos LED inserts for TTX400

Order Code	Full Product Name	Glow-wire test	Lamp family code	Embedded control	Product family code
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	Temperature 850 °C, duration 30 s	LED66S	-	4MX433
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	Temperature 850 °C, duration 30 s	LED66S	-	4MX433
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED55S	-	4MX433
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	Temperature 850 °C, duration 30 s	LED55S	-	4MX433
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX433
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	Temperature 650 °C, duration 30 s	-	-	4MX433
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	Temperature 650 °C, duration 30 s	-	-	4MX433
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	Temperature 650 °C, duration 30 s	-	-	4MX433
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	Temperature 650 °C, duration 30 s	-	-	4MX433
910500460579	4MX400 491 LED55S/840 PSD VWB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629123226	4MX400 491 LED40S/830 PSD NB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629123326	4MX400 491 LED40S/830 PSD WB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629123426	4MX400 491 LED40S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629123526	4MX400 491 LED40S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629123626	4MX400 491 LED55S/830 PSD NB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629123726	4MX400 491 LED55S/830 PSD WB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629123826	4MX400 491 LED55S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629123926	4MX400 491 LED55S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629124026	4MX400 581 LED40S/830 PSD NB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629124326	4MX400 581 LED40S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629124626	4MX400 581 LED55S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400

Maxos LED inserts for TTX400

Order Code	Full Product Name	Glow-wire test	Lamp family code	Embedded control	Product family code
910629124726	4MX400 581 LED55S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629158826	4MX400 581 LED66S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629158926	4MX400 581 LED66S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629162326	4MX400 491 LED40S/830 PSD A20 WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629162426	4MX400 491 LED40S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629162526	4MX400 491 LED55S/830 PSD A20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629162626	4MX400 491 LED55S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629162726	4MX400 491 LED66S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629162826	4MX400 491 LED66S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629163126	4MX400 581 LED55S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629167126	4MX400 491 LED80S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460045	4MX400 581 LED80S/840 PSD VWB WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	LED80S	-	4MX400

Maxos LED inserts for TTX400

			Lamp family	Embedded control	Product family
Order Code	Full Product Name	Glow-wire test	code		code
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910500460115	4MX400 581 LED66S/840 PSD- CLO DA20 WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910500460116	4MX400 581 LED80S/840 PSD- CLO DA20 WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910629124126	4MX400 581 LED40S/830 PSD WB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629124226	4MX400 581 LED40S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629124426	4MX400 581 LED55S/830 PSD NB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629124526	4MX400 581 LED55S/830 PSD WB WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED40S	-	4MX400
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED55S	-	4MX400
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	LED66S	-	4MX400
910629166826	4MX400 581 LED80S/840 PSD NB WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400
910629167326	4MX400 581 LED80S/840 PSD WB WH	Temperature 650 °C, duration 30 s	LED80S	-	4MX400

Light Technical (1/2)

		Correlated		Luminous				Correlated		Luminous	
		Color		Efficacy				Color		Efficacy	
		Temperature	Optical	(rated)	Luminous			Temperature	Optical	(rated)	Luminous
Order Code	Full Product Name	(Nom)	cover type	(Nom)	Flux	Order Code	Full Product Name	(Nom)	cover type	(Nom)	Flux
910500460028	4MX400 491 LED66S/840 PSD- CLO WB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm	910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm	910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm	910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm	910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm	910500460113	4MX400 491 LED66S/840 PSD- CLO DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated Color Temperature	Optical cover type	Luminous Efficacy (rated)	Luminous Flux
		(Nom)		(Nom)	
910500460114	4MX400 491 LED80S/840 PSD- CLO DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm

Order Code	Full Product Name	Correlated Color Temperature	Optical cover type	Luminous Efficacy (rated)	Luminous Flux
		(Nom)		(Nom)	
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	149 lm/W	5,500 lm
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	4000 K	Polymethyl methacrylate bowl/cover	147 lm/W	6,600 lm
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	4000 K	-	147 lm/W	6,600 lm
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	4000 K	-	147 lm/W	6,600 lm
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	4000 K	-	147 lm/W	6,600 lm
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	4000 K	-	147 lm/W	6,600 lm
910500460579	4MX400 491 LED55S/840 PSD VWB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629123226	4MX400 491 LED40S/830 PSD NB WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629123326	4MX400 491 LED40S/830 PSD WB WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629123426	4MX400 491 LED40S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm
910629123526	4MX400 491 LED40S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated Color Temperature	Optical cover type	Luminous Efficacy (rated)	Luminous Flux
		(Nom)		(Nom)	
910629123626	4MX400 491 LED55S/830 PSD NB WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm
910629123726	4MX400 491 LED55S/830 PSD WB WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm
910629123826	4MX400 491 LED55S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629123926	4MX400 491 LED55S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629124026	4MX400 581 LED40S/830 PSD NB WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629124326	4MX400 581 LED40S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm
910629124626	4MX400 581 LED55S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629124726	4MX400 581 LED55S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm
910629158826	4MX400 581 LED66S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910629158926	4MX400 581 LED66S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm

Order Code	Full Product Name	Correlated Color Temperature	Optical cover type	Luminous Efficacy (rated)	Luminous Flux
		(Nom)		(Nom)	
910629162326	4MX400 491 LED40S/830 PSD A20 WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629162426	4MX400 491 LED40S/840 PSD A20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm
910629162526	4MX400 491 LED55S/830 PSD A20 WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm
910629162626	4MX400 491 LED55S/840 PSD A20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629162726	4MX400 491 LED66S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910629162826	4MX400 491 LED66S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910629163126	4MX400 581 LED55S/840 PSD A20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629167126	4MX400 491 LED80S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460045	4MX400 581 LED80S/840 PSD VWB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated Color Temperature	Optical	Luminous Efficacy (rated)	Luminous
		(Nom)	cover type	(Nom)	Flux
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910500460115	4MX400 581 LED66S/840 PSD- CLO DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910500460116	4MX400 581 LED80S/840 PSD- CLO DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910629124126	4MX400 581 LED40S/830 PSD WB WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629124226	4MX400 581 LED40S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	4,000 lm
910629124426	4MX400 581 LED55S/830 PSD NB WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm
910629124526	4MX400 581 LED55S/830 PSD WB WH	3000 K	Polymethyl methacrylate bowl/cover	160 lm/W	5,200 lm

Order Code	Full Product Name	Correlated Color Temperature	Optical	Luminous Efficacy (rated)	Luminous
		(Nom)	cover type	(Nom)	Flux
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	3000 K	Polymethyl methacrylate bowl/cover	158 lm/W	3,800 lm
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	5,500 lm
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	4000 K	Polymethyl methacrylate bowl/cover	169 lm/W	6,600 lm
910629166826	4MX400 581 LED80S/840 PSD NB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm
910629167326	4MX400 581 LED80S/840 PSD WB WH	4000 K	Polymethyl methacrylate bowl/cover	166 lm/W	8,000 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	1	Wide beam
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	1	Narrow beam
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	1	Narrow beam
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	1	Wide beam
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	1	Narrow beam
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	1	Wide beam
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°

Order Code	Full Product Name	Number of light sources	Optic type
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	1	Wide beam
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	1	Narrow beam
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	1	Wide beam
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	1	Double asymmetric optic 20°
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	1	Narrow beam
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	1	Wide beam
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	1	Double asymmetric optic 20°
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	1	Narrow beam
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	1	Wide beam

Maxos LED inserts for TTX400

Order Code	Full Product Name	Number of light sources	Optic type
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	1	Narrow beam
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	1	Narrow beam
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	1	Wide beam
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	1	Double asymmetric optic 20°
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	1	Narrow beam
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	1	Wide beam
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	1	Double asymmetric optic 20°
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	1	Narrow beam
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	1	Wide beam
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	-	Wide beam
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	-	Wide beam
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	-	Wide beam
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	-	Wide beam
910500460579	4MX400 491 LED55S/840 PSD VWB WH	1	Very wide beam
910629123226	4MX400 491 LED40S/830 PSD NB WH	1	Narrow beam
910629123326	4MX400 491 LED40S/830 PSD WB WH	1	Wide beam
910629123426	4MX400 491 LED40S/840 PSD NB WH	1	Narrow beam
910629123526	4MX400 491 LED40S/840 PSD WB WH	1	Wide beam
910629123626	4MX400 491 LED55S/830 PSD NB WH	1	Narrow beam
910629123726	4MX400 491 LED55S/830 PSD WB WH	1	Wide beam
910629123826	4MX400 491 LED55S/840 PSD NB WH	1	Narrow beam
910629123926	4MX400 491 LED55S/840 PSD WB WH	1	Wide beam
910629124026	4MX400 581 LED40S/830 PSD NB WH	1	Narrow beam

Order Code	Full Product Name	Number of light sources	Optic type
910629124326	4MX400 581 LED40S/840 PSD WB WH	1	Wide beam
910629124626	4MX400 581 LED55S/840 PSD NB WH	1	Narrow beam
910629124726	4MX400 581 LED55S/840 PSD WB WH	1	Wide beam
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	1	Double asymmetric optic 20°
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	1	Double asymmetric optic 20°
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	1	Double asymmetric optic 20°
910629158826	4MX400 581 LED66S/840 PSD WB WH	1	Wide beam
910629158926	4MX400 581 LED66S/840 PSD NB WH	1	Narrow beam
910629162326	4MX400 491 LED40S/830 PSD A20 WH	1	Asymmetrical mirror axis angle 20°
910629162426	4MX400 491 LED40S/840 PSD A20 WH	1	Asymmetrical mirror axis angle 20°
910629162526	4MX400 491 LED55S/830 PSD A20 WH	1	Asymmetrical mirror axis angle 20°
910629162626	4MX400 491 LED55S/840 PSD A20 WH	1	Asymmetrical mirror axis angle 20°
910629162726	4MX400 491 LED66S/840 PSD NB WH	1	Narrow beam
910629162826	4MX400 491 LED66S/840 PSD WB WH	1	Wide beam
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910629163126	4MX400 581 LED55S/840 PSD A20 WH	1	Asymmetrical mirror axis angle 20°
910629167126	4MX400 491 LED80S/840 PSD WB WH	1	Wide beam
910500460045	4MX400 581 LED80S/840 PSD VWB WH	1	Very wide beam
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	1	Very wide beam
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	1	Narrow beam

Maxos LED inserts for TTX400

		Number of light sources	Optic type
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	1	Narrow beam
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	1	Wide beam
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°
910629124126	4MX400 581 LED40S/830 PSD WB WH	1	Wide beam
910629124226	4MX400 581 LED40S/840 PSD NB WH	1	Narrow beam
910629124426	4MX400 581 LED55S/830 PSD NB WH	1	Narrow beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	39 W
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	37 W
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	48 W
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	39 W
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	39 W
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	39 W
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	48 W
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	48 W
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	48 W
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	39 W
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	48 W
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	37 W
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	37 W
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	45 W
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	45 W
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	45 W
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	37 W
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	37 W
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	37 W
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	45 W
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	45 W
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	45 W
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	37 W
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	37 W

		Number of light sources	Optic type
Order Code	Full Product Name		
910629124526	4MX400 581 LED55S/830 PSD WB WH	1	Wide beam
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	1	Double asymmetric optic 20°
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	1	Wide beam
910629166826	4MX400 581 LED80S/840 PSD NB WH	1	Narrow beam
910629167326	4MX400 581 LED80S/840 PSD WB WH	1	Wide beam

Order Code	Full Product Name	Power Consumption
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	45 W
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	45 W
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	45 W
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	37 W
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	37 W
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	37 W
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	45 W
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	45 W
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	45 W
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	45 W
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	45 W
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	45 W
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	45 W
910500460579	4MX400 491 LED55S/840 PSD VWB WH	32.5 W
910629123226	4MX400 491 LED40S/830 PSD NB WH	24 W
910629123326	4MX400 491 LED40S/830 PSD WB WH	24 W
910629123426	4MX400 491 LED40S/840 PSD NB WH	24 W
910629123526	4MX400 491 LED40S/840 PSD WB WH	24 W
910629123626	4MX400 491 LED55S/830 PSD NB WH	32.5 W
910629123726	4MX400 491 LED55S/830 PSD WB WH	32.5 W
910629123826	4MX400 491 LED55S/840 PSD NB WH	32.5 W
910629123926	4MX400 491 LED55S/840 PSD WB WH	32.5 W
910629124026	4MX400 581 LED40S/830 PSD NB WH	24 W
910629124326	4MX400 581 LED40S/840 PSD WB WH	24 W
910629124626	4MX400 581 LED55S/840 PSD NB WH	32.5 W

Maxos LED inserts for TTX400

Order Code	Full Product Name	Power Consumption
910629124726	4MX400 581 LED55S/840 PSD WB WH	32.5 W
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	24 W
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	24 W
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	32.5 W
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	32.5 W
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	24 W
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	32.5 W
910629158826	4MX400 581 LED66S/840 PSD WB WH	39 W
910629158926	4MX400 581 LED66S/840 PSD NB WH	39 W
910629162326	4MX400 491 LED40S/830 PSD A20 WH	24 W
910629162426	4MX400 491 LED40S/840 PSD A20 WH	24 W
910629162526	4MX400 491 LED55S/830 PSD A20 WH	32.5 W
910629162626	4MX400 491 LED55S/840 PSD A20 WH	32.5 W
910629162726	4MX400 491 LED66S/840 PSD NB WH	39 W
910629162826	4MX400 491 LED66S/840 PSD WB WH	39 W
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	39 W
910629163126	4MX400 581 LED55S/840 PSD A20 WH	32.5 W
910629167126	4MX400 491 LED80S/840 PSD WB WH	48 W
910500460045	4MX400 581 LED80S/840 PSD VWB WH	48 W

Order Code	Full Product Name	Power Consumption
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	32.5 W
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	48 W
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	39 W
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	39 W
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	48 W
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	48 W
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	48 W
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	39 W
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	48 W
910629124126	4MX400 581 LED40S/830 PSD WB WH	24 W
910629124226	4MX400 581 LED40S/840 PSD NB WH	24 W
910629124426	4MX400 581 LED55S/830 PSD NB WH	32.5 W
910629124526	4MX400 581 LED55S/830 PSD WB WH	32.5 W
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	24 W
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	32.5 W
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	39 W
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	39 W
910629166826	4MX400 581 LED80S/840 PSD NB WH	48 W
910629167326	4MX400 581 LED80S/840 PSD WB WH	48 W

Temperature

Order Code	Full Product Name	Ambient temperature range
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	-20 to +35 °C
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	-20 to +35 °C
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	-20 to +35 °C
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	-20 to +35 °C
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	-20 to +35 °C
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	-20 to +35 °C
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	-20 to +35 °C
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	-20 to +35 °C
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	-20 to +35 °C
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	-20 to +35 °C
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	-20 to +35 °C
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	-20 to +35 °C
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	-20 to +35 °C
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	-20 to +35 °C
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	-20 to +35 °C
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	-20 to +35 °C
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	-20 to +35 °C
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	-20 to +35 °C
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	-20 to +35 °C
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	-20 to +35 °C
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	-20 to +35 °C
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	-20 to +35 °C
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	-20 to +35 °C
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	-20 to +35 °C
910500460178	4MX433 581 LED66S/840 PSD NB WH ELB3	-20 to +35 °C
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	-20 to +35 °C
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	-20 to +35 °C

Maxos LED inserts for TTX400

Order Code	Full Product Name	Ambient temperature range
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	-20 to +35 °C
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	-20 to +35 °C
910500460183	4MX433 581 LED66S/840 PSD DA20WHEELB3C-2R	-20 to +35 °C
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	-20 to +35 °C
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	-20 to +35 °C
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	-20 to +35 °C
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	-20 to +35 °C
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	-20 to +35 °C
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	-20 to +35 °C
910500460579	4MX400 491 LED55S/840 PSD VWB WH	+20 to +35 °C
910629123226	4MX400 491 LED40S/830 PSD NB WH	-20 to +35 °C
910629123326	4MX400 491 LED40S/830 PSD WB WH	-20 to +35 °C
910629123426	4MX400 491 LED40S/840 PSD NB WH	-20 to +35 °C
910629123526	4MX400 491 LED40S/840 PSD WB WH	-20 to +35 °C
910629123626	4MX400 491 LED55S/830 PSD NB WH	-20 to +35 °C
910629123726	4MX400 491 LED55S/830 PSD WB WH	-20 to +35 °C
910629123826	4MX400 491 LED55S/840 PSD NB WH	-20 to +35 °C
910629123926	4MX400 491 LED55S/840 PSD WB WH	-20 to +35 °C
910629124026	4MX400 581 LED40S/830 PSD NB WH	-20 to +35 °C
910629124326	4MX400 581 LED40S/840 PSD WB WH	-20 to +35 °C
910629124626	4MX400 581 LED55S/840 PSD NB WH	-20 to +35 °C
910629124726	4MX400 581 LED55S/840 PSD WB WH	-20 to +35 °C
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	-20 to +35 °C
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	-20 to +35 °C
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	-20 to +35 °C
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	-20 to +35 °C
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	-20 to +35 °C
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	-20 to +35 °C
910629158826	4MX400 581 LED66S/840 PSD WB WH	-20 to +35 °C
910629158926	4MX400 581 LED66S/840 PSD NB WH	-20 to +35 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Ambient temperature range
910629162326	4MX400 491 LED40S/830 PSD A20 WH	-20 to +35 °C
910629162426	4MX400 491 LED40S/840 PSD A20 WH	-20 to +35 °C
910629162526	4MX400 491 LED55S/830 PSD A20 WH	-20 to +35 °C
910629162626	4MX400 491 LED55S/840 PSD A20 WH	-20 to +35 °C
910629162726	4MX400 491 LED66S/840 PSD NB WH	-20 to +35 °C
910629162826	4MX400 491 LED66S/840 PSD WB WH	-20 to +35 °C
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	-20 to +35 °C
910629163126	4MX400 581 LED55S/840 PSD A20 WH	-20 to +35 °C
910629167126	4MX400 491 LED80S/840 PSD WB WH	-20 to +35 °C
910500460045	4MX400 581 LED80S/840 PSD VWB WH	-20 to +35 °C
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	-20 to +35 °C
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	-20 to +35 °C
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	-20 to +35 °C
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	-20 to +35 °C
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	-20 to +35 °C
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	-20 to +35 °C
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	-20 to +35 °C
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	-20 to +35 °C
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	-20 to +35 °C
910629124126	4MX400 581 LED40S/830 PSD WB WH	-20 to +35 °C
910629124226	4MX400 581 LED40S/840 PSD NB WH	-20 to +35 °C
910629124426	4MX400 581 LED55S/830 PSD NB WH	-20 to +35 °C
910629124526	4MX400 581 LED55S/830 PSD WB WH	-20 to +35 °C
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	-20 to +35 °C
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	-20 to +35 °C
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	-20 to +35 °C
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	-20 to +35 °C
910629166826	4MX400 581 LED80S/840 PSD NB WH	-20 to +35 °C
910629167326	4MX400 581 LED80S/840 PSD WB WH	-20 to +35 °C

Order Code	Full Product Name	Initial chromaticity
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5


Maxos LED inserts for TTX400

Order Code	Full Product Name	Initial chromaticity
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	(0.38, 0.38) SDCM <3.5
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	(0.38, 0.38) SDCM <3.5
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	(0.38, 0.38) SDCM <3.5
910500460579	4MX400 491 LED55S/840 PSD VWB WH	(0.38, 0.38) SDCM <3.5
910629123226	4MX400 491 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629123326	4MX400 491 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629123426	4MX400 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629123526	4MX400 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629123626	4MX400 491 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629123726	4MX400 491 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5


Order Code	Full Product Name	Initial chromaticity
910629123826	4MX400 491 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629123926	4MX400 491 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629124026	4MX400 581 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629124326	4MX400 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629124626	4MX400 581 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629124726	4MX400 581 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629158826	4MX400 581 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629158926	4MX400 581 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629162326	4MX400 491 LED40S/830 PSD A20 WH	(0.43, 0.40) SDCM <3.5
910629162426	4MX400 491 LED40S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5
910629162526	4MX400 491 LED55S/830 PSD A20 WH	(0.43, 0.40) SDCM <3.5
910629162626	4MX400 491 LED55S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5
910629162726	4MX400 491 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629162826	4MX400 491 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629163126	4MX400 581 LED55S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5
910629167126	4MX400 491 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500460045	4MX400 581 LED80S/840 PSD VWB WH	(0.38, 0.38) SDCM <3.5
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910629124126	4MX400 581 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629124226	4MX400 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629124426	4MX400 581 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629124526	4MX400 581 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910629166826	4MX400 581 LED80S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629167326	4MX400 581 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5

Maxos LED inserts for TTX400


Polar Wide Diagrams




IFPS_4MX400 G3 491 1xLED40S/830 PSD NB- Polar Normal (separate)




IFPS_4MX400 G3 491 1xLED40S/840 PSD DA- Polar Normal (separate)




IFPS_4MX400 G3 491 1xLED55S/830 PSD A20- Polar Normal (separate)




IFPS_4MX400 G3 491 1xLED55S/830 PSD NB- Polar Normal (separate)




IFPS_4MX400 G3 491 1xLED55S/830 PSD WB- Polar Normal (separate)




IFPS_4MX400 G3 491 1xLED55S/840 PSD A20- Polar Normal (separate)



IFPS_4MX400 G3 491 1xLED55S/840 PSD DA- Polar Normal (separate)






IFPS_4MX400 G3 491 1xLED55S/840 PSD NB- Polar Normal (separate)



IFPS_4MX400 G3 491 1xLED66S/830 PSD A20- Polar Normal (separate)




Polar Wide Diagrams



IFPS_4MX400 G3 491 1xLED66S/830 PSD DA-
Polar Normal (separate)

IFPS_4MX400 G3 491 1xLED66S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX400 G3 491 1xLED66S/840 PSD A20-
Polar Normal (separate)



IFPS_4MX400 G3 491 1xLED66S/840 PSD NB-
Polar Normal (separate)

IFPS_4MX400 G3 491 1xLED66S/840 PSD WB-
Polar Normal (separate)

IFPS_4MX400 G3 491 1xLED80S/830 PSD A20-
Polar Normal (separate)






IFPS_4MX400 G3 491 1xLED80S/830 PSD DA-
Polar Normal (separate)

IFPS_4MX400 G3 491 1xLED80S/830 PSD NB-
Polar Normal (separate)

IFPS_4MX400 G3 491 1xLED80S/830 PSD WB-
Polar Normal (separate)

Maxos LED inserts for TTX400




Polar Wide Diagrams



IFPS_4MX400 G3 491 1xLED80S/840 PSD DA-
Polar Normal (separate)

IFPS_4MX400 G3 581 1xLED40S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED40S/840 PSD A20-
Polar Normal (separate)



IFPS_4MX400 G3 581 1xLED40S/840 PSD NB-
Polar Normal (separate)

IFPS_4MX400 G3 581 1xLED40S/840 PSD WB-
Polar Normal (separate)

IFPS_4MX400 G3 581 1xLED55S/830 PSD A20-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED55S/830 PSD NB-
Polar Normal (separate)

IFPS_4MX400 G3 581 1xLED55S/840 PSD A20-
Polar Normal (separate)


IFPS_4MX400 G3 581 1xLED55S/840 PSD DA-
Polar Normal (separate)

Maxos LED inserts for TTX400


Polar Wide Diagrams




IFPS_4MX400 G3 581 1xLED55S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED55S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED66S/830 PSD DA-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED66S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED66S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX400 G3 581 1xLED66S/840 PSD DA-
Polar Normal (separate)



IFPS_4MX400 G3 581 1xLED66S/840 PSD WB-
Polar Normal (separate)






IFPS_4MX400 G3 581 1xLED80S/830 PSD A20-
Polar Normal (separate)



IFPS_4MX400 G3 581 1xLED80S/830 PSD DA-
Polar Normal (separate)

Maxos LED inserts for TTX400




Polar Wide Diagrams



**IFPS_4MX400 G3 581 1xLED80S/830 PSD NB-
Polar Normal (separate)**

**IFPS_4MX400 G3 581 1xLED80S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX400 G3 581 1xLED80S/840 PSD DA-
Polar Normal (separate)**



**IFPS_4MX400 G3 581 1xLED80S/840 PSD NB-
Polar Normal (separate)**

**IFPS_4MX400 491 1xLED40S/830 PSD A20-
Polar Normal (separate)**

**IFPS_4MX400 491 1xLED40S/830 PSD DA-
Polar Normal (separate)**






**IFPS_4MX400 491 1xLED40S/830 PSD NB-
Polar Normal (separate)**

**IFPS_4MX400 491 1xLED55S/830 PSD A20-
Polar Normal (separate)**

**IFPS_4MX400 491 1xLED55S/830 PSD DA-
Polar Normal (separate)**

Maxos LED inserts for TTX400




Polar Wide Diagrams



IFPS_4MX400 491 1xLED55S/830 PSD NB-
Polar Normal (separate)

IFPS_4MX400 581 1xLED40S/830 PSD DA-
Polar Normal (separate)




IFPS_4MX400 581 1xLED40S/830 PSD NB-
Polar Normal (separate)



IFPS_4MX400 581 1xLED40S/830 PSD WB-
Polar Normal (separate)

IFPS_4MX400 581 1xLED55S/830 PSD NB-
Polar Normal (separate)

IFPS_4MX400 G2 491 1xLED40S/840 PSD NB-
Polar Normal (separate)






IFPS_4MX400 G2 491 1xLED55S/840 PSD A20-
Polar Normal (separate)

IFPS_4MX400 G2 491 1xLED55S/840 PSD DA-
Polar Normal (separate)

IFPS_4MX400 G2 581 1xLED40S/840 PSD DA-
Polar Normal (separate)

Maxos LED inserts for TTX400




Polar Wide Diagrams



IFPS_4MX400 G2 581 1xLED55S/840 PSD A20-
Polar Normal (separate)

IFPS_4MX400 G2 581 1xLED55S/840 PSD DA-
Polar Normal (separate)


IFPS_4MX400 G2 581 1xLED55S/840 PSD NB-
Polar Normal (separate)



IFPS_4MX400 G2 581 1xLED55S/840 PSD WB-
Polar Normal (separate)

IFPS_4MX400 G2 581 1xLED66S/840 PSD DA-
Polar Normal (separate)

IFPS_4MX400 G2 581 1xLED66S/840 PSD NB-
Polar Normal (separate)



IFPS_4MX400 G2 581 1xLED66S/840 PSD WB-
Polar Normal (separate)

Maxos LED inserts for TTX400

