



Maxos LED Performer – účinné a přesné lineární osvětlení

Maxos LED Performer

Zákazníci usilují o úsporu energie ve srovnání s běžným osvětlením. Současně však vyžadují mimořádně kvalitní světelné podmínky: v průmyslových prostředích pro lepší bezpečnost a produktivitu i v maloobchodech, kde je důležité předvedení zboží a upoutání pozornosti kupujících. Maxos LED Performer je mimořádně flexibilní řešení, které se vyznačuje nízkou spotřebou energie a vynikajícími vyzařovacími charakteristikami, a to při zajímavých investičních nákladech.

Výhody

- Mimořádně rychlá návratnost
- Přelomový optický systém pro přesné vyzařování
- Flexibilita v nahrazování, umístění, změnách a příslušenství

Vlastnosti

- Nízká spotřeba energie ve srovnání se zářivkou
- Vynikající tvar paprsku, méně rozptýleného světla a rovnoměrné rozdělení světla ve vodorovné i svislé rovině
- Prověřené moduly Philips LED (Fortimo)
- Lze osadit jako nové nebo náhradní svítidlo do lišty Maxos

Aplikace

- Supermarkety
- Sklady
- Výrobní zařízení





Maxos LED Performer

Versions



IPPR1 4MX900i 0001.JPG

Rozměrové výkresy



Detaily o výrobku

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



Maxos LED Performer

Detaily o výrobku



IPDP_4MX900i_0011-Detail
photo

Maxos LED Performer

Obecné informace	
Značka CE	Ano
Včetně předřadníku	Ano
Značka ENEC	Značka ENEC
Značka hořlavosti	-
Test žhavým drátem	Teplota 650 °C, doba 30 s
Vyměnitelný světelný zdroj	Ne
Počet předřadниковých jednotek	1 jednotka
Kód produktové řady	4MX900
Světelně technické	
Vyzařovací úhel světelného zdroje	120 stupňů
Jmenovitá náhradní teplota chromatičnosti	4000 K
Index podání barev (CRI)	≥80
Provozní a elektrické	
Frekvence sítě	50 to 60 Hz
Teplota okolí	
Rozsah okolních teplot	-20 až +40 °C
Certifikace a použití	
Třída ochrany IEC	Bezpečnostní třída I
Kód ochrany proti mechanickým nárazům	IK02
Kód ochrany proti vniknutí	IP40
Počáteční parametry (podle IEC)	
Počáteční chromatičnost	(0.38, 0.38) SDCM <3.5
Tolerance světelného toku	+/-10%
Podmínky použití	
Vhodné pro náhodné spínání	Nevztahuje se

Obecné informace

Order Code	Full Product Name	Kód řady svítidel
66977699	4MX900 581 LED50S/840 PSD WB WH	LED50S
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S
66388099	4MX900 LED40S/840 PSD MB WH L1200	LED40S
66389799	4MX900 LED40S/840 PSD NB WH L1200	LED40S
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	LED40S
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S
66446799	4MX900 LED60S/840 PSD NB WH L1800	LED60S
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	LED60S
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S
66462799	4MX900 LED90S/840 PSD NB WH L1800	LED90S
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S
66612699	4MX900 LED40S/840 PSU WB WH L1200	LED40S
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S
66630099	4MX900 491 LED50S/840 PSD NB WH	LED50S
66631799	4MX900 491 LED50S/840 PSD DA20 WH	LED50S
66633199	4MX900 LED40S/840 PSD A30 WH L1200	LED40S
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
66636299	4MX900 581 LED40S/840 PSU A30 WH	LED40S
66637999	4MX900 581 LED50S/840 PSU A30 WH	LED50S
66638699	4MX900 491 LED40S/840 PSU A30 WH	LED40S
66639399	4MX900 491 LED50S/840 PSU A30 WH	LED50S
66640999	4MX900 581 LED50S/840 PSU WB WH	LED50S
66641699	4MX900 581 LED50S/840 PSU MB WH	LED50S
66644799	4MX900 491 LED50S/840 PSU WB WH	LED50S
66645499	4MX900 491 LED50S/840 PSU MB WH	LED50S
66646199	4MX900 491 LED50S/840 PSU NB WH	LED50S
66681299	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
66790199	4MX900 491 LED75S/840 PSU WB WH	LED75S
66800799	4MX900 491 LED75S/840 PSD WB WH	LED75S
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S
66805299	4MX900 491 LED75S/840 PSD A30 WH	LED75S
66436899	4MX900 LED60S/840 PSD WB SI L1800	LED60S
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	LED60S
66452899	4MX900 LED90S/840 PSD WB SI L1800	LED90S
66453599	4MX900 LED90S/840 PSD MB SI L1800	LED90S
66484999	4MX900 491 LED40S/840 PSU WB SI	LED40S

Světelně technické

Maxos LED Performer

Order Code	Full Product Name	Měrný výkon (jmen.) (nom.)	Světelný tok	Počet světelných zdrojů	Typ optiky
66977699	4MX900 581 LED50S/840 PSD WB WH	155 lm/W	5 000 lm	-	Široký paprsek
66387399	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4 000 lm	1	Široký paprsek
66388099	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4 000 lm	1	Střední paprsek
66389799	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4 000 lm	1	Úzký paprsek
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	154 lm/W	4 000 lm	1	Dvojitá asymetrická optika 20°
66444399	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6 000 lm	1	Široký paprsek
66445099	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6 000 lm	1	Střední paprsek
66446799	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6 000 lm	1	Úzký paprsek
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	161 lm/W	6 000 lm	1	Dvojitá asymetrická optika 20°
66460399	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9 000 lm	1	Široký paprsek
66461099	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9 000 lm	1	Střední paprsek
66462799	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9 000 lm	1	Úzký paprsek
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9 000 lm	1	Dvojitá asymetrická optika 20°
66476499	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4 000 lm	1	Široký paprsek
66477199	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4 000 lm	1	Střední paprsek
66492499	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4 000 lm	1	Široký paprsek

Order Code	Full Product Name	Měrný výkon (jmen.) (nom.)	Světelný tok	Počet světelných zdrojů	Typ optiky
66493199	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4 000 lm	1	Střední paprsek
66612699	4MX900 LED40S/840 PSU WB WH L1200	154 lm/W	4 000 lm	1	Široký paprsek
66624999	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4 000 lm	1	Široký paprsek
66625699	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4 000 lm	1	Střední paprsek
66626399	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4 000 lm	1	Úzký paprsek
66628799	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5 000 lm	1	Široký paprsek
66629499	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5 000 lm	1	Střední paprsek
66630099	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5 000 lm	1	Úzký paprsek
66631799	4MX900 491 LED50S/840 PSD DA20 WH	155 lm/W	5 000 lm	1	Dvojitá asymetrická optika 20°
66633199	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66635599	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66636299	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66637999	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66638699	4MX900 491 LED40S/840 PSU A30 WH	159 lm/W	4 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66639399	4MX900 491 LED50S/840 PSU A30 WH	155 lm/W	5 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66640999	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5 000 lm	1	Široký paprsek

Maxos LED Performer

Order Code	Full Product Name	Měrný výkon (jmen.) (nom.)	Světelný tok	Počet světelných zdrojů	Typ optiky
66641699	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5 000 lm	1	Střední paprsek
66644799	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5 000 lm	1	Široký paprsek
66645499	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5 000 lm	1	Střední paprsek
66646199	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5 000 lm	1	Úzký paprsek
66681299	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9 000 lm	1	Asymetrická zrcadlová osa, úhel 30°
66790199	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7 500 lm	1	Široký paprsek
66800799	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7 500 lm	1	Široký paprsek

Order Code	Full Product Name	Měrný výkon (jmen.) (nom.)	Světelný tok	Počet světelných zdrojů	Typ optiky
66801499	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7 500 lm	1	Střední paprsek
66805299	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7 500 lm	1	Asymetrická zrcadlová osa, úhel 30°
66436899	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6 000 lm	1	Široký paprsek
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	161 lm/W	6 000 lm	1	Dvojitá asymetrická optika 20°
66452899	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9 000 lm	1	Široký paprsek
66453599	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9 000 lm	1	Střední paprsek
66484999	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4 000 lm	1	Široký paprsek

Provozní a elektrické

Order Code	Full Product Name	Vstupní napětí	Spotřeba energie
66977699	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32,2 W
66387399	4MX900 LED40S/840 PSD WB WH L1200	220 až 240 V	25,9 W
66388099	4MX900 LED40S/840 PSD MB WH L1200	220 až 240 V	25,9 W
66389799	4MX900 LED40S/840 PSD NB WH L1200	220 až 240 V	25,9 W
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	220 až 240 V	25,9 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	220 až 240 V	37,3 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	220 až 240 V	37,3 W
66446799	4MX900 LED60S/840 PSD NB WH L1800	220 až 240 V	37,3 W
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	220 až 240 V	37,3 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	220 až 240 V	60,1 W
66461099	4MX900 LED90S/840 PSD MB WH L1800	220 až 240 V	60,1 W
66462799	4MX900 LED90S/840 PSD NB WH L1800	220 až 240 V	60,1 W

Order Code	Full Product Name	Vstupní napětí	Spotřeba energie
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	220 až 240 V	60,1 W
66476499	4MX900 581 LED40S/840 PSU WB WH	220 až 240 V	25,2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	220 až 240 V	25,2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	220 až 240 V	25,2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	220 až 240 V	25,2 W
66612699	4MX900 LED40S/840 PSU WB WH L1200	220 až 240 V	25,9 W
66624999	4MX900 491 LED40S/840 PSD WB WH	220 až 240 V	25,2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	220 až 240 V	25,2 W
66626399	4MX900 491 LED40S/840 PSD NB WH	220 až 240 V	25,2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	220 až 240 V	32,2 W
66629499	4MX900 491 LED50S/840 PSD MB WH	220 až 240 V	32,2 W
66630099	4MX900 491 LED50S/840 PSD NB WH	220 až 240 V	32,2 W
66631799	4MX900 491 LED50S/840 PSD DA20 WH	220 až 240 V	32,2 W
66633199	4MX900 LED40S/840 PSD A30 WH L1200	220 až 240 V	25,9 W
66635599	4MX900 LED60S/840 PSD A30 WH L1800	220 až 240 V	37,3 W
66636299	4MX900 581 LED40S/840 PSU A30 WH	220 až 240 V	25,2 W
66637999	4MX900 581 LED50S/840 PSU A30 WH	220 až 240 V	32,2 W
66638699	4MX900 491 LED40S/840 PSU A30 WH	220 až 240 V	25,2 W

Maxos LED Performer

Order Code	Full Product Name	Vstupní napětí	Spotřeba energie
66639399	4MX900 491 LED50S/840 PSU A30 WH	220 až 240 V	32,2 W
66640999	4MX900 581 LED50S/840 PSU WB WH	220 až 240 V	32,2 W
66641699	4MX900 581 LED50S/840 PSU MB WH	220 až 240 V	32,2 W
66644799	4MX900 491 LED50S/840 PSU WB WH	220 až 240 V	32,2 W
66645499	4MX900 491 LED50S/840 PSU MB WH	220 až 240 V	32,2 W
66646199	4MX900 491 LED50S/840 PSU NB WH	220 až 240 V	32,2 W
66681299	4MX900 LED90S/840 PSD A30 WH L1800	220 až 240 V	60,1 W
66790199	4MX900 491 LED75S/840 PSU WB WH	220 až 240 V	50,2 W
66800799	4MX900 491 LED75S/840 PSD WB WH	220 až 240 V	50,2 W

Order Code	Full Product Name	Vstupní napětí	Spotřeba energie
66801499	4MX900 491 LED75S/840 PSD MB WH	220 až 240 V	50,2 W
66805299	4MX900 491 LED75S/840 PSD A30 WH	220 až 240 V	50,2 W
66436899	4MX900 LED60S/840 PSD WB SI L1800	220 až 240 V	37,3 W
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	220 až 240 V	37,3 W
66452899	4MX900 LED90S/840 PSD WB SI L1800	220 až 240 V	60,1 W
66453599	4MX900 LED90S/840 PSD MB SI L1800	220 až 240 V	60,1 W
66484999	4MX900 491 LED40S/840 PSU WB SI	220 až 240 V	25,2 W

Řízení a stmívání

Order Code	Full Product Name	Stmívatelné
66977699	4MX900 581 LED50S/840 PSD WB WH	Ano
66387399	4MX900 LED40S/840 PSD WB WH L1200	Ano
66388099	4MX900 LED40S/840 PSD MB WH L1200	Ano
66389799	4MX900 LED40S/840 PSD NB WH L1200	Ano
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Ano
66444399	4MX900 LED60S/840 PSD WB WH L1800	Ano
66445099	4MX900 LED60S/840 PSD MB WH L1800	Ano
66446799	4MX900 LED60S/840 PSD NB WH L1800	Ano
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Ano
66460399	4MX900 LED90S/840 PSD WB WH L1800	Ano
66461099	4MX900 LED90S/840 PSD MB WH L1800	Ano
66462799	4MX900 LED90S/840 PSD NB WH L1800	Ano
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Ano
66476499	4MX900 581 LED40S/840 PSU WB WH	Ne
66477199	4MX900 581 LED40S/840 PSU MB WH	Ne
66492499	4MX900 491 LED40S/840 PSU WB WH	Ne
66493199	4MX900 491 LED40S/840 PSU MB WH	Ne
66612699	4MX900 LED40S/840 PSU WB WH L1200	Ne
66624999	4MX900 491 LED40S/840 PSD WB WH	Ano
66625699	4MX900 491 LED40S/840 PSD MB WH	Ano
66626399	4MX900 491 LED40S/840 PSD NB WH	Ano
66628799	4MX900 491 LED50S/840 PSD WB WH	Ano
66629499	4MX900 491 LED50S/840 PSD MB WH	Ano

Order Code	Full Product Name	Stmívatelné
66630099	4MX900 491 LED50S/840 PSD NB WH	Ano
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Ano
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Ano
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Ano
66636299	4MX900 581 LED40S/840 PSU A30 WH	Ne
66637999	4MX900 581 LED50S/840 PSU A30 WH	Ne
66638699	4MX900 491 LED40S/840 PSU A30 WH	Ne
66639399	4MX900 491 LED50S/840 PSU A30 WH	Ne
66640999	4MX900 581 LED50S/840 PSU WB WH	Ne
66641699	4MX900 581 LED50S/840 PSU MB WH	Ne
66644799	4MX900 491 LED50S/840 PSU WB WH	Ne
66645499	4MX900 491 LED50S/840 PSU MB WH	Ne
66646199	4MX900 491 LED50S/840 PSU NB WH	Ne
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Ano
66790199	4MX900 491 LED75S/840 PSU WB WH	Ne
66800799	4MX900 491 LED75S/840 PSD WB WH	Ano
66801499	4MX900 491 LED75S/840 PSD MB WH	Ano
66805299	4MX900 491 LED75S/840 PSD A30 WH	Ano
66436899	4MX900 LED60S/840 PSD WB SI L1800	Ano
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Ano
66452899	4MX900 LED90S/840 PSD WB SI L1800	Ano
66453599	4MX900 LED90S/840 PSD MB SI L1800	Ano
66484999	4MX900 491 LED40S/840 PSU WB SI	Ne

Mechanické a materiály

Order Code	Full Product Name	Barva těla
66977699	4MX900 581 LED50S/840 PSD WB WH	Bílá
66387399	4MX900 LED40S/840 PSD WB WH L1200	Bílá
66388099	4MX900 LED40S/840 PSD MB WH L1200	Bílá
66389799	4MX900 LED40S/840 PSD NB WH L1200	Bílá
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Bílá
66444399	4MX900 LED60S/840 PSD WB WH L1800	Bílá
66445099	4MX900 LED60S/840 PSD MB WH L1800	Bílá
66446799	4MX900 LED60S/840 PSD NB WH L1800	Bílá
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Bílá

Order Code	Full Product Name	Barva těla
66460399	4MX900 LED90S/840 PSD WB WH L1800	Bílá
66461099	4MX900 LED90S/840 PSD MB WH L1800	Bílá
66462799	4MX900 LED90S/840 PSD NB WH L1800	Bílá
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Bílá
66476499	4MX900 581 LED40S/840 PSU WB WH	Bílá
66477199	4MX900 581 LED40S/840 PSU MB WH	Bílá
66492499	4MX900 491 LED40S/840 PSU WB WH	Bílá
66493199	4MX900 491 LED40S/840 PSU MB WH	Bílá
66612699	4MX900 LED40S/840 PSU WB WH L1200	Bílá

Maxos LED Performer

Order Code	Full Product Name	Barva těla
66624999	4MX900 491 LED40S/840 PSD WB WH	Bílá
66625699	4MX900 491 LED40S/840 PSD MB WH	Bílá
66626399	4MX900 491 LED40S/840 PSD NB WH	Bílá
66628799	4MX900 491 LED50S/840 PSD WB WH	Bílá
66629499	4MX900 491 LED50S/840 PSD MB WH	Bílá
66630099	4MX900 491 LED50S/840 PSD NB WH	Bílá
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Bílá
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Bílá
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Bílá
66636299	4MX900 581 LED40S/840 PSU A30 WH	Bílá
66637999	4MX900 581 LED50S/840 PSU A30 WH	Bílá
66638699	4MX900 491 LED40S/840 PSU A30 WH	Bílá
66639399	4MX900 491 LED50S/840 PSU A30 WH	Bílá
66640999	4MX900 581 LED50S/840 PSU WB WH	Bílá


Order Code	Full Product Name	Barva těla
66641699	4MX900 581 LED50S/840 PSU MB WH	Bílá
66644799	4MX900 491 LED50S/840 PSU WB WH	Bílá
66645499	4MX900 491 LED50S/840 PSU MB WH	Bílá
66646199	4MX900 491 LED50S/840 PSU NB WH	Bílá
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Bílá
66790199	4MX900 491 LED75S/840 PSU WB WH	Bílá
66800799	4MX900 491 LED75S/840 PSD WB WH	Bílá
66801499	4MX900 491 LED75S/840 PSD MB WH	Bílá
66805299	4MX900 491 LED75S/840 PSD A30 WH	Bílá
66436899	4MX900 LED60S/840 PSD WB SI L1800	Stříbrná
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Stříbrná
66452899	4MX900 LED90S/840 PSD WB SI L1800	Stříbrná
66453599	4MX900 LED90S/840 PSD MB SI L1800	Stříbrná
66484999	4MX900 491 LED40S/840 PSU WB SI	Stříbrná

Podmínky použití


Order Code	Full Product Name	Maximální úroveň ztlumení
66977699	4MX900 581 LED50S/840 PSD WB WH	1%
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66388099	4MX900 LED40S/840 PSD MB WH L1200	1%
66389799	4MX900 LED40S/840 PSD NB WH L1200	1%
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66446799	4MX900 LED60S/840 PSD NB WH L1800	1%
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66462799	4MX900 LED90S/840 PSD NB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%
66476499	4MX900 581 LED40S/840 PSU WB WH	Nevztahuje se
66477199	4MX900 581 LED40S/840 PSU MB WH	Nevztahuje se
66492499	4MX900 491 LED40S/840 PSU WB WH	Nevztahuje se
66493199	4MX900 491 LED40S/840 PSU MB WH	Nevztahuje se
66612699	4MX900 LED40S/840 PSU WB WH L1200	Nevztahuje se
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%

Order Code	Full Product Name	Maximální úroveň ztlumení
66630099	4MX900 491 LED50S/840 PSD NB WH	1%
66631799	4MX900 491 LED50S/840 PSD DA20 WH	1%
66633199	4MX900 LED40S/840 PSD A30 WH L1200	1%
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%
66636299	4MX900 581 LED40S/840 PSU A30 WH	Nevztahuje se
66637999	4MX900 581 LED50S/840 PSU A30 WH	Nevztahuje se
66638699	4MX900 491 LED40S/840 PSU A30 WH	Nevztahuje se
66639399	4MX900 491 LED50S/840 PSU A30 WH	Nevztahuje se
66640999	4MX900 581 LED50S/840 PSU WB WH	Nevztahuje se
66641699	4MX900 581 LED50S/840 PSU MB WH	Nevztahuje se
66644799	4MX900 491 LED50S/840 PSU WB WH	Nevztahuje se
66645499	4MX900 491 LED50S/840 PSU MB WH	Nevztahuje se
66646199	4MX900 491 LED50S/840 PSU NB WH	Nevztahuje se
66681299	4MX900 LED90S/840 PSD A30 WH L1800	1%
66790199	4MX900 491 LED75S/840 PSU WB WH	Nevztahuje se
66800799	4MX900 491 LED75S/840 PSD WB WH	1%
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66805299	4MX900 491 LED75S/840 PSD A30 WH	1%
66436899	4MX900 LED60S/840 PSD WB SI L1800	1%
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	1%
66452899	4MX900 LED90S/840 PSD WB SI L1800	1%
66453599	4MX900 LED90S/840 PSD MB SI L1800	1%
66484999	4MX900 491 LED40S/840 PSU WB SI	Nevztahuje se


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD DA20-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD DA20-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSU A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSU NB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)



IFPS_4MX900 4911xLED50S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 4911xLED71S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED32S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED40S/840 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 L1200 1xLED57S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1200 1xLED57S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED48S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)**



IFPS_4MX900 G3 491 1xLED40S/830 PSD
DA20-Polar Normal (separate)






IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/840 PSD
A30-Polar Normal (separate)




Polar Wide Diagrams



**IFPS_4MX900 G3 491 1xLED40S/840 PSD
DA20-Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)**


**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)**






**IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)**




Polar Wide Diagrams



**IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED71S/830 PSD
DA20- Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-
Polar Normal (separate)**


**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)**






**IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)**




Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-Polar Normal (separate)

IFPS_4MX900 G3 L1200 1xLED40S/830 PSD NB-Polar Normal (separate)




IFPS_4MX900 G3 L1200 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 L1200 1xLED60S/840 PSU WB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/830 PSD NB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/830 PSD WB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/840 PSD MB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/840 PSD NB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/840 PSD WB-Polar Normal (separate)


Maxos LED Performer

Polar Wide Diagrams



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD

WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED90S/840 PSD

NB-Polar Normal (separate)

