



Maxos LED Performer

Maxos LED Performer

La ligne continue gradable ultra puissante. Si vous souhaitez réaliser des économies d'énergie et réduire vos coûts de maintenance tout en améliorant la qualité de votre éclairage, alors Maxos LED Performer est pour vous ! Ce système rail est le plus puissant de sa catégorie et s'adapte à toutes les applications : dans les environnements industriels et logistiques il garantit la sécurité et la productivité, dans les commerces de détail il met en valeur les marchandises et attire les acheteurs. Maxos LED Performer est une solution extrêmement flexible, avec une faible consommation d'énergie et d'excellents faisceaux lumineux, pour un retour sur investissement en moins de 5 ans selon les conditions d'utilisation.

Avantages

- Un retour sur investissement rapide
- Système optique révolutionnaire pour un faisceau précis
- Flexible en termes de solutions de remplacement, d'ajout de projecteurs et de modifications de l'installation au cours du temps

Fonctions


- Faible consommation d'énergie en comparaison avec des tubes fluorescents
- Un modelage parfait du faisceau lumineux pour une réduction maximale des pertes de flux et un éclairage précis sur les plans horizontaux et verticaux
- Fortimo LED Line R
- Possibilité de montage des unités électriques sur un rail Maxos neuf ou existant (rénovation)

Application

- Supermarchés/Hypermarchés
- Entrepôts
- Sites de production

Maxos LED Performer

Schéma dimensionnel




Détails sur le produit

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



IPDP_4MX900i_0011-Detail
photo



Maxos LED Performer

Détails sur le produit



Maxos LED Performer

Informations générales	
Marquage CE	Oui
Driver inclus	Oui
Marquage ENEC	Marquage ENEC
Inflammabilité	-
Essai au fil incandescent	Température 650 °C, durée 30 s
Source lumineuse remplaçable	Non
Nombre d'appareillages	1 unité
Code famille de produits	4MX900
Données techniques de l'éclairage	
Angle d'ouverture du faisceau de la source lumineuse	120 degré(s)
Température de couleur corrélée (nom.)	4000 K
Indice de rendu de couleur (IRC)	≥80
Nombre de sources lumineuses	1
Fonctionnement et électricité	
Tension d'entrée	220 à 240 V
Fréquence linéaire	50 to 60 Hz
Température	
Gamme de températures ambiantes	-20 à +40 °C
Approbation et application	
Classe de protection CEI	Classe de sécurité I
Protection contre les chocs mécaniques	IK02
Indice de protection	IP40
Performances initiales	
Chromaticité initiale	(0.38, 0.38) SDCM <3.5
Tolérance de flux lumineux	+/-10%
Conditions d'application	
Convient pour la commutation aléatoire	Non applicable

Informations générales

Order Code	Full Product Name	Code famille lampe
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S
66388099	4MX900 LED40S/840 PSD MB WH L1200	LED40S
66389799	4MX900 LED40S/840 PSD NB WH L1200	LED40S
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	LED40S
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S
66446799	4MX900 LED60S/840 PSD NB WH L1800	LED60S
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	LED60S
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S
66462799	4MX900 LED90S/840 PSD NB WH L1800	LED90S
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S
66630099	4MX900 491 LED50S/840 PSD NB WH	LED50S
66631799	4MX900 491 LED50S/840 PSD DA20 WH	LED50S
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
66681299	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
66711699	4MX900 491 LED75S/840 PSU A30 WH	LED75S
66727799	4MX900 491 LED50S/840 PSU DA30 WH	LED50S
66791899	4MX900 491 LED75S/840 PSU MB WH	LED75S
66800799	4MX900 491 LED75S/840 PSD WB WH	LED75S
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S
66802199	4MX900 491 LED75S/840 PSD NB WH	LED75S
66804599	4MX900 491 LED75S/840 PSD DA20 WH	LED75S
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	LED40S
66436899	4MX900 LED60S/840 PSD WB SI L1800	LED60S
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	LED60S
66452899	4MX900 LED90S/840 PSD WB SI L1800	LED90S
66453599	4MX900 LED90S/840 PSD MB SI L1800	LED90S
66484999	4MX900 491 LED40S/840 PSU WB SI	LED40S
66683699	4MX900 LED90S/840 PSD A30 SI L1800	LED90S

Données techniques de l'éclairage

Order Code	Full Product Name	Efficacité lumineuse	Flux	Type d'optique
		(nominale)	lumineux	
66387399	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4 000 lm	Faisceau extensif
66388099	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4 000 lm	Faisceau semi-intensif

Order Code	Full Product Name	Efficacité lumineuse	Flux	Type d'optique
		(nominale)	lumineux	
66389799	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4 000 lm	Faisceau intensif
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	154 lm/W	4 000 lm	Optique asymétrique double 20°

Maxos LED Performer

Order Code	Full Product Name	Efficacité lumineuse (nominale)	Flux lumineux	Type d'optique
66444399	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6 000 lm	Faisceau extensif
66445099	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6 000 lm	Faisceau semi-intensif
66446799	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6 000 lm	Faisceau intensif
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	161 lm/W	6 000 lm	Optique asymétrique double 20°
66460399	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9 000 lm	Faisceau extensif
66461099	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9 000 lm	Faisceau semi-intensif
66462799	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9 000 lm	Faisceau intensif
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9 000 lm	Optique asymétrique double 20°
66476499	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4 000 lm	Faisceau extensif
66477199	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4 000 lm	Faisceau semi-intensif
66492499	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4 000 lm	Faisceau extensif
66493199	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4 000 lm	Faisceau semi-intensif
66624999	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4 000 lm	Faisceau extensif
66625699	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4 000 lm	Faisceau semi-intensif
66626399	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4 000 lm	Faisceau intensif
66628799	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5 000 lm	Faisceau extensif

Order Code	Full Product Name	Efficacité lumineuse (nominale)	Flux lumineux	Type d'optique
66629499	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5 000 lm	Faisceau semi-intensif
66630099	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5 000 lm	Faisceau intensif
66631799	4MX900 491 LED50S/840 PSD DA20 WH	155 lm/W	5 000 lm	Optique asymétrique double 20°
66635599	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6 000 lm	Miroir asymétrique, inclinaison de l'axe de 30°
66681299	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9 000 lm	Miroir asymétrique, inclinaison de l'axe de 30°
66711699	4MX900 491 LED75S/840 PSU A30 WH	149 lm/W	7 500 lm	Miroir asymétrique, inclinaison de l'axe de 30°
66727799	4MX900 491 LED50S/840 PSU DA30 WH	155 lm/W	5 000 lm	Optique asymétrique double 30°
66791899	4MX900 491 LED75S/840 PSU MB WH	149 lm/W	7 500 lm	Faisceau semi-intensif
66800799	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7 500 lm	Faisceau extensif
66801499	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7 500 lm	Faisceau semi-intensif
66802199	4MX900 491 LED75S/840 PSD NB WH	149 lm/W	7 500 lm	Faisceau intensif
66804599	4MX900 491 LED75S/840 PSD DA20 WH	149 lm/W	7 500 lm	Optique asymétrique double 20°
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	154 lm/W	4 000 lm	Optique asymétrique double 20°
66436899	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6 000 lm	Faisceau extensif
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	161 lm/W	6 000 lm	Optique asymétrique double 20°

Maxos LED Performer

Order Code	Full Product Name	Efficacité	Flux	Type d'optique
		lumineuse (nominale)	lumineux	
66452899	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9 000 lm	Faisceau extensif
66453599	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9 000 lm	Faisceau semi- intensif
66484999	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4 000 lm	Faisceau extensif

Order Code	Full Product Name	Efficacité	Flux	Type d'optique
		lumineuse (nominale)	lumineux	
66683699	4MX900 LED90S/840 PSD A30 SI L1800	150 lm/W	9 000 lm	Miroir asymétrique, inclinaison de l'axe de 30°

Fonctionnement et électricité

Order Code	Full Product Name	Consommation électrique
66387399	4MX900 LED40S/840 PSD WB WH L1200	25,9 W
66388099	4MX900 LED40S/840 PSD MB WH L1200	25,9 W
66389799	4MX900 LED40S/840 PSD NB WH L1200	25,9 W
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	25,9 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	37,3 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	37,3 W
66446799	4MX900 LED60S/840 PSD NB WH L1800	37,3 W
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	37,3 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	60,1 W
66461099	4MX900 LED90S/840 PSD MB WH L1800	60,1 W
66462799	4MX900 LED90S/840 PSD NB WH L1800	60,1 W
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	60,1 W
66476499	4MX900 581 LED40S/840 PSU WB WH	25,2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	25,2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	25,2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	25,2 W
66624999	4MX900 491 LED40S/840 PSD WB WH	25,2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	25,2 W
66626399	4MX900 491 LED40S/840 PSD NB WH	25,2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	32,2 W

Order Code	Full Product Name	Consommation électrique
66629499	4MX900 491 LED50S/840 PSD MB WH	32,2 W
66630099	4MX900 491 LED50S/840 PSD NB WH	32,2 W
66631799	4MX900 491 LED50S/840 PSD DA20 WH	32,2 W
66635599	4MX900 LED60S/840 PSD A30 WH L1800	37,3 W
66681299	4MX900 LED90S/840 PSD A30 WH L1800	60,1 W
66711699	4MX900 491 LED75S/840 PSU A30 WH	50,2 W
66727799	4MX900 491 LED50S/840 PSU DA30 WH	32,2 W
66791899	4MX900 491 LED75S/840 PSU MB WH	50,2 W
66800799	4MX900 491 LED75S/840 PSD WB WH	50,2 W
66801499	4MX900 491 LED75S/840 PSD MB WH	50,2 W
66802199	4MX900 491 LED75S/840 PSD NB WH	50,2 W
66804599	4MX900 491 LED75S/840 PSD DA20 WH	50,2 W
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	25,9 W
66436899	4MX900 LED60S/840 PSD WB SI L1800	37,3 W
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	37,3 W
66452899	4MX900 LED90S/840 PSD WB SI L1800	60,1 W
66453599	4MX900 LED90S/840 PSD MB SI L1800	60,1 W
66484999	4MX900 491 LED40S/840 PSU WB SI	25,2 W
66683699	4MX900 LED90S/840 PSD A30 SI L1800	60,1 W

Commandes et gradation

Order Code	Full Product Name	Variation de l'intensité lumineuse
66387399	4MX900 LED40S/840 PSD WB WH L1200	Oui
66388099	4MX900 LED40S/840 PSD MB WH L1200	Oui
66389799	4MX900 LED40S/840 PSD NB WH L1200	Oui
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Oui
66444399	4MX900 LED60S/840 PSD WB WH L1800	Oui
66445099	4MX900 LED60S/840 PSD MB WH L1800	Oui
66446799	4MX900 LED60S/840 PSD NB WH L1800	Oui
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Oui
66460399	4MX900 LED90S/840 PSD WB WH L1800	Oui
66461099	4MX900 LED90S/840 PSD MB WH L1800	Oui
66462799	4MX900 LED90S/840 PSD NB WH L1800	Oui

Order Code	Full Product Name	Variation de l'intensité lumineuse
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Oui
66476499	4MX900 581 LED40S/840 PSU WB WH	Non
66477199	4MX900 581 LED40S/840 PSU MB WH	Non
66492499	4MX900 491 LED40S/840 PSU WB WH	Non
66493199	4MX900 491 LED40S/840 PSU MB WH	Non
66624999	4MX900 491 LED40S/840 PSD WB WH	Oui
66625699	4MX900 491 LED40S/840 PSD MB WH	Oui
66626399	4MX900 491 LED40S/840 PSD NB WH	Oui
66628799	4MX900 491 LED50S/840 PSD WB WH	Oui
66629499	4MX900 491 LED50S/840 PSD MB WH	Oui
66630099	4MX900 491 LED50S/840 PSD NB WH	Oui

Maxos LED Performer

Order Code	Full Product Name	Variation de l'intensité lumineuse
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Oui
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Oui
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Oui
66711699	4MX900 491 LED75S/840 PSU A30 WH	Non
66727799	4MX900 491 LED50S/840 PSU DA30 WH	Non
66791899	4MX900 491 LED75S/840 PSU MB WH	Non
66800799	4MX900 491 LED75S/840 PSD WB WH	Oui
66801499	4MX900 491 LED75S/840 PSD MB WH	Oui
66802199	4MX900 491 LED75S/840 PSD NB WH	Oui

Order Code	Full Product Name	Variation de l'intensité lumineuse
66804599	4MX900 491 LED75S/840 PSD DA20 WH	Oui
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	Oui
66436899	4MX900 LED60S/840 PSD WB SI L1800	Oui
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Oui
66452899	4MX900 LED90S/840 PSD WB SI L1800	Oui
66453599	4MX900 LED90S/840 PSD MB SI L1800	Oui
66484999	4MX900 491 LED40S/840 PSU WB SI	Non
66683699	4MX900 LED90S/840 PSD A30 SI L1800	Oui

Mécanique et boîtier

Order Code	Full Product Name	Couleur du corps
66387399	4MX900 LED40S/840 PSD WB WH L1200	Blanc
66388099	4MX900 LED40S/840 PSD MB WH L1200	Blanc
66389799	4MX900 LED40S/840 PSD NB WH L1200	Blanc
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Blanc
66444399	4MX900 LED60S/840 PSD WB WH L1800	Blanc
66445099	4MX900 LED60S/840 PSD MB WH L1800	Blanc
66446799	4MX900 LED60S/840 PSD NB WH L1800	Blanc
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Blanc
66460399	4MX900 LED90S/840 PSD WB WH L1800	Blanc
66461099	4MX900 LED90S/840 PSD MB WH L1800	Blanc
66462799	4MX900 LED90S/840 PSD NB WH L1800	Blanc
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Blanc
66476499	4MX900 581 LED40S/840 PSU WB WH	Blanc
66477199	4MX900 581 LED40S/840 PSU MB WH	Blanc
66492499	4MX900 491 LED40S/840 PSU WB WH	Blanc
66493199	4MX900 491 LED40S/840 PSU MB WH	Blanc
66624999	4MX900 491 LED40S/840 PSD WB WH	Blanc
66625699	4MX900 491 LED40S/840 PSD MB WH	Blanc
66626399	4MX900 491 LED40S/840 PSD NB WH	Blanc
66628799	4MX900 491 LED50S/840 PSD WB WH	Blanc

Order Code	Full Product Name	Couleur du corps
66629499	4MX900 491 LED50S/840 PSD MB WH	Blanc
66630099	4MX900 491 LED50S/840 PSD NB WH	Blanc
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Blanc
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Blanc
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Blanc
66711699	4MX900 491 LED75S/840 PSU A30 WH	Blanc
66727799	4MX900 491 LED50S/840 PSU DA30 WH	Blanc
66791899	4MX900 491 LED75S/840 PSU MB WH	Blanc
66800799	4MX900 491 LED75S/840 PSD WB WH	Blanc
66801499	4MX900 491 LED75S/840 PSD MB WH	Blanc
66802199	4MX900 491 LED75S/840 PSD NB WH	Blanc
66804599	4MX900 491 LED75S/840 PSD DA20 WH	Blanc
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	Argent
66436899	4MX900 LED60S/840 PSD WB SI L1800	Argent
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Argent
66452899	4MX900 LED90S/840 PSD WB SI L1800	Argent
66453599	4MX900 LED90S/840 PSD MB SI L1800	Argent
66484999	4MX900 491 LED40S/840 PSU WB SI	Argent
66683699	4MX900 LED90S/840 PSD A30 SI L1800	Argent

Conditions d'application

Order Code	Full Product Name	Niveau de gradation maximal
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66388099	4MX900 LED40S/840 PSD MB WH L1200	1%
66389799	4MX900 LED40S/840 PSD NB WH L1200	1%
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66446799	4MX900 LED60S/840 PSD NB WH L1800	1%
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66462799	4MX900 LED90S/840 PSD NB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%




Order Code	Full Product Name	Niveau de gradation maximal
66476499	4MX900 581 LED40S/840 PSU WB WH	Non applicable
66477199	4MX900 581 LED40S/840 PSU MB WH	Non applicable
66492499	4MX900 491 LED40S/840 PSU WB WH	Non applicable
66493199	4MX900 491 LED40S/840 PSU MB WH	Non applicable
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%
66630099	4MX900 491 LED50S/840 PSD NB WH	1%
66631799	4MX900 491 LED50S/840 PSD DA20 WH	1%
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%

Maxos LED Performer

Order Code	Full Product Name	Niveau de gradation maximal
66681299	4MX900 LED90S/840 PSD A30 WH L1800	1%
66711699	4MX900 491 LED75S/840 PSU A30 WH	Non applicable
66727799	4MX900 491 LED50S/840 PSU DA30 WH	Non applicable
66791899	4MX900 491 LED75S/840 PSU MB WH	Non applicable
66800799	4MX900 491 LED75S/840 PSD WB WH	1%
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66802199	4MX900 491 LED75S/840 PSD NB WH	1%
66804599	4MX900 491 LED75S/840 PSD DA20 WH	1%

Order Code	Full Product Name	Niveau de gradation maximal
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	1%
66436899	4MX900 LED60S/840 PSD WB SI L1800	1%
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	1%
66452899	4MX900 LED90S/840 PSD WB SI L1800	1%
66453599	4MX900 LED90S/840 PSD MB SI L1800	1%
66484999	4MX900 491 LED40S/840 PSU WB SI	Non applicable
66683699	4MX900 LED90S/840 PSD A30 SI L1800	1%




Polar Wide Diagrams



**IFPS_4MX900 491 1xLED40S/830 PSD DA20-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**


**IFPS_4MX900 491 1xLED40S/840 PSU A30-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/840 PSU DA30-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSU DA30-
Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSU DA30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED75S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU DA30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 L1200 1xLED57S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1200 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD NB-
Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED48S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1800 1xLED60S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED85S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD NB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED40S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD
DA20-Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**






**IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**




Polar Wide Diagrams



**IFPS_4MX900 G3 491 1xLED50S/830 PSD
DA20-Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/830 PSU
DA30-Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/840 PSD
DA20-Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)**


**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/840 PSU
DA30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU
DA30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU
DA30-Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 L1200 1xLED40S/830 PSD
NB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
NB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
WB-Polar Normal (separate)**



**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
MB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
NB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)**

Maxos LED Performer

Polar Wide Diagrams



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED90S/840 PSD
NB-Polar Normal (separate)

