



Maxos LED Performer: illuminazione efficiente e precisa

Maxos LED Performer

I clienti vogliono risparmiare energia e ridurre i costi rispetto a ciò a cui sono abituati con l'illuminazione convenzionale. Allo stesso tempo, è necessario ottenere condizioni di illuminazione eccellenti: in ambienti industriali, per garantire sicurezza e produttività; nei negozi, per fare in modo che la merce risalti e attragga i clienti. Il Performer Maxos LED è una soluzione a fila continua estremamente flessibile che offre ad un basso consumo energetico, un'eccellente modellazione del fascio ed un livello di investimento interessante.

Vantaggi

- Ritorno dell'investimento estremamente rapido
- Sistema ottico innovativo per una precisa modellazione del fascio
- Flessibile in termini di retrofit ed accessori

Caratteristiche


- Basso consumo energetico rispetto ai sistemi fluorescenti
- Modellazione eccellente del fascio per una minore luce dispersa e un'esatta distribuzione della luce sul piano orizzontale e quello verticale
- LED Philips (Fortimo)
- Disponibile sia per una nuova installazione, sia come sistema retrofit su canaline Maxos

Applicazione

- Supermercati
- Magazzini
- Impianti di produzione

Maxos LED Performer

Disegno tecnico




Dati del prodotto

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



IPDP_4MX900i_0011-Detail
photo



Maxos LED Performer

Dati del prodotto



Informazioni generali

Marchio CE	Sì
Driver incluso	Sì
Marchio ENEC	Marchio ENEC
Marchio di infiammabilità	-
Test filo incandescente	Temperatura 650 °C, durata 30 s
Sorgente luminosa sostituibile	No
Numero di riduttori	1 unità
Codice famiglia prodotto	4MX900

Dati tecnici di illuminazione

Angolo del fascio di luce della sorgente luminosa	120 °
Temperatura del colore correlata	4000 K
Indice di resa cromatica (CRI)	≥80

Funzionamento e parte elettrica

Frequenza di linea	50 to 60 Hz
--------------------	-------------

Temperatura

Range temperatura ambiente	Da -20 a +40 °C
----------------------------	-----------------

Approvazione e applicazione

Classe di protezione IEC:	Classe di isolamento I
Codice di protezione dagli impatti meccanici e una gestione termica	IK02 IP40

Performance iniziale (conforme a IEC)

Cromaticità iniziale	(0.38, 0.38) SDCM <3.5
Tolleranza al flusso luminoso	+/-10%

Condizioni di applicazione

Adatto per la commutazione casuale	Non applicabile
------------------------------------	-----------------

Informazioni generali

Order Code	Full Product Name	Codice famiglia lampada
66882399	4MX900 581 LED50S/840 PSD MB WH	LED50S
66977699	4MX900 581 LED50S/840 PSD WB WH	LED50S
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S
66388099	4MX900 LED40S/840 PSD MB WH L1200	LED40S
66389799	4MX900 LED40S/840 PSD NB WH L1200	LED40S
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	LED40S
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S
66446799	4MX900 LED60S/840 PSD NB WH L1800	LED60S
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	LED60S
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S
66462799	4MX900 LED90S/840 PSD NB WH L1800	LED90S
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S
66612699	4MX900 LED40S/840 PSU WB WH L1200	LED40S
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S
66630099	4MX900 491 LED50S/840 PSD NB WH	LED50S
66631799	4MX900 491 LED50S/840 PSD DA20 WH	LED50S
66633199	4MX900 LED40S/840 PSD A30 WH L1200	LED40S
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
66636299	4MX900 581 LED40S/840 PSU A30 WH	LED40S
66637999	4MX900 581 LED50S/840 PSU A30 WH	LED50S
66638699	4MX900 491 LED40S/840 PSU A30 WH	LED40S
66639399	4MX900 491 LED50S/840 PSU A30 WH	LED50S
66640999	4MX900 581 LED50S/840 PSU WB WH	LED50S
66641699	4MX900 581 LED50S/840 PSU MB WH	LED50S
66644799	4MX900 491 LED50S/840 PSU WB WH	LED50S
66645499	4MX900 491 LED50S/840 PSU MB WH	LED50S
66646199	4MX900 491 LED50S/840 PSU NB WH	LED50S

Order Code	Full Product Name	Codice famiglia lampada
66681299	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
66709399	4MX900 581 LED75S/840 PSU A30 WH	LED75S
66711699	4MX900 491 LED75S/840 PSU A30 WH	LED75S
66727799	4MX900 491 LED50S/840 PSU DA30 WH	LED50S
66790199	4MX900 491 LED75S/840 PSU WB WH	LED75S
66791899	4MX900 491 LED75S/840 PSU MB WH	LED75S
66795699	4MX900 581 LED75S/840 PSU WB WH	LED75S
66796399	4MX900 581 LED75S/840 PSU MB WH	LED75S
66797099	4MX900 581 LED75S/840 PSU NB WH	LED75S
66800799	4MX900 491 LED75S/840 PSD WB WH	LED75S
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S
66802199	4MX900 491 LED75S/840 PSD NB WH	LED75S
66804599	4MX900 491 LED75S/840 PSD DA20 WH	LED75S
66805299	4MX900 491 LED75S/840 PSD A30 WH	LED75S
66806999	4MX900 581 LED75S/840 PSD WB WH	LED75S
66807699	4MX900 581 LED75S/840 PSD MB WH	LED75S
66808399	4MX900 581 LED75S/840 PSD NB WH	LED75S
66810699	4MX900 581 LED75S/840 PSD DA20 WH	LED75S
66811399	4MX900 581 LED75S/840 PSD A30 WH	LED75S
66883099	4MX900 581 LED50S/840 PSD A30 WH	LED50S
66436899	4MX900 LED60S/840 PSD WB SI L1800	LED60S
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	LED60S
66452899	4MX900 LED90S/840 PSD WB SI L1800	LED90S
66453599	4MX900 LED90S/840 PSD MB SI L1800	LED90S
66484999	4MX900 491 LED40S/840 PSU WB SI	LED40S
66683699	4MX900 LED90S/840 PSD A30 SI L1800	LED90S
67195399	4MX900 581 LED50S/840 PSU A30 SI	LED50S

Dati tecnici di illuminazione

Full Product		Efficienza luminosa	Flusso luminoso	Numero di sorgenti luminose	Tipo di ottica
Order Code	Name	(specificata) (Nom)			
66882399	4MX900 581 LED50S/840 PSD MB WH	155 lm/W	5.000 lm	-	Fascio medio
66977699	4MX900 581 LED50S/840 PSD WB WH	155 lm/W	5.000 lm	-	Fascio largo
66387399	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4.000 lm	1	Fascio largo
66388099	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4.000 lm	1	Fascio medio
66389799	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4.000 lm	1	Fascio stretto
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	154 lm/W	4.000 lm	1	Ottica asimmetrica doppia 20°
66444399	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6.000 lm	1	Fascio largo
66445099	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6.000 lm	1	Fascio medio
66446799	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6.000 lm	1	Fascio stretto

Maxos LED Performer

Order Code	Full Product		Efficienza luminosa (specificata) (Nom)	Flusso luminoso	Numero di sorgenti luminose	Tipo di ottica
	Name					
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	161 lm/W	6.000 lm	1		Ottica asimmetrica doppia 20°
66460399	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9.000 lm	1		Fascio largo
66461099	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9.000 lm	1		Fascio medio
66462799	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9.000 lm	1		Fascio stretto
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9.000 lm	1		Ottica asimmetrica doppia 20°
66476499	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4.000 lm	1		Fascio largo
66477199	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4.000 lm	1		Fascio medio
66492499	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4.000 lm	1		Fascio largo
66493199	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4.000 lm	1		Fascio medio
66612699	4MX900 LED40S/840 PSU WB WH L1200	154 lm/W	4.000 lm	1		Fascio largo
66624999	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4.000 lm	1		Fascio largo
66625699	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4.000 lm	1		Fascio medio
66626399	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4.000 lm	1		Fascio stretto
66628799	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5.000 lm	1		Fascio largo

Order Code	Full Product		Efficienza luminosa (specificata) (Nom)	Flusso luminoso	Numero di sorgenti luminose	Tipo di ottica
	Name					
66629499	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5.000 lm	1		Fascio medio
66630099	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5.000 lm	1		Fascio stretto
66631799	4MX900 491 LED50S/840 PSD DA20 WH	155 lm/W	5.000 lm	1		Ottica asimmetrica doppia 20°
66633199	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4.000 lm	1		Asimmetrica speculare angolo 30°
66635599	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6.000 lm	1		Asimmetrica speculare angolo 30°
66636299	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4.000 lm	1		Asimmetrica speculare angolo 30°
66637999	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5.000 lm	1		Asimmetrica speculare angolo 30°
66638699	4MX900 491 LED40S/840 PSU A30 WH	159 lm/W	4.000 lm	1		Asimmetrica speculare angolo 30°
66639399	4MX900 491 LED50S/840 PSU A30 WH	155 lm/W	5.000 lm	1		Asimmetrica speculare angolo 30°
66640999	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5.000 lm	1		Fascio largo
66641699	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5.000 lm	1		Fascio medio
66644799	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5.000 lm	1		Fascio largo
66645499	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5.000 lm	1		Fascio medio
66646199	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5.000 lm	1		Fascio stretto
66681299	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9.000 lm	1		Asimmetrica speculare angolo 30°

Maxos LED Performer

Full Product		Efficienza luminosa (specificata) (Nom)	Flusso luminoso	Numero di sorgenti luminose	Tipo di ottica
Order Code	Name				
66709399	4MX900 581 LED75S/840 PSU A30 WH	149 lm/W	7.500 lm	1	Asimmetrica speculare angolo 30°
66711699	4MX900 491 LED75S/840 PSU A30 WH	149 lm/W	7.500 lm	1	Asimmetrica speculare angolo 30°
66727799	4MX900 491 LED50S/840 PSU DA30 WH	155 lm/W	5.000 lm	1	Ottica asimmetrica doppia 30°
66790199	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7.500 lm	1	Fascio largo
66791899	4MX900 491 LED75S/840 PSU MB WH	149 lm/W	7.500 lm	1	Fascio medio
66795699	4MX900 581 LED75S/840 PSU WB WH	149 lm/W	7.500 lm	1	Fascio largo
66796399	4MX900 581 LED75S/840 PSU MB WH	149 lm/W	7.500 lm	1	Fascio medio
66797099	4MX900 581 LED75S/840 PSU NB WH	149 lm/W	7.500 lm	1	Fascio stretto
66800799	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7.500 lm	1	Fascio largo
66801499	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7.500 lm	1	Fascio medio
66802199	4MX900 491 LED75S/840 PSD NB WH	149 lm/W	7.500 lm	1	Fascio stretto
66804599	4MX900 491 LED75S/840 PSD DA20 WH	149 lm/W	7.500 lm	1	Ottica asimmetrica doppia 20°
66805299	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7.500 lm	1	Asimmetrica speculare angolo 30°
66806999	4MX900 581 LED75S/840 PSD WB WH	149 lm/W	7.500 lm	1	Fascio largo

Funzionamento e parte elettrica

Full Product Name		Consumo	
Order Code		Tensione in ingresso	energetico
66882399	4MX900 581 LED50S/840 PSD MB WH	Da 220 a 240 V	32,2 W

Full Product		Efficienza luminosa (specificata) (Nom)	Flusso luminoso	Numero di sorgenti luminose	Tipo di ottica
Order Code	Name				
66807699	4MX900 581 LED75S/840 PSD MB WH	149 lm/W	7.500 lm	1	Fascio medio
66808399	4MX900 581 LED75S/840 PSD NB WH	149 lm/W	7.500 lm	1	Fascio stretto
66810699	4MX900 581 LED75S/840 PSD DA20 WH	149 lm/W	7.500 lm	1	Ottica asimmetrica doppia 20°
66811399	4MX900 581 LED75S/840 PSD A30 WH	149 lm/W	7.500 lm	1	Asimmetrica speculare angolo 30°
66883099	4MX900 581 LED50S/840 PSD A30 WH	155 lm/W	5.000 lm	1	Asimmetrica speculare angolo 30°
66436899	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6.000 lm	1	Fascio largo
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	161 lm/W	6.000 lm	1	Ottica asimmetrica doppia 20°
66452899	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9.000 lm	1	Fascio largo
66453599	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9.000 lm	1	Fascio medio
66484999	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4.000 lm	1	Fascio largo
66683699	4MX900 LED90S/840 PSD A30 SI L1800	150 lm/W	9.000 lm	1	Asimmetrica speculare angolo 30°
67195399	4MX900 581 LED50S/840 PSU A30 SI	155 lm/W	5.000 lm	1	Asimmetrica speculare angolo 30°

Full Product Name		Consumo	
Order Code		Tensione in ingresso	energetico
66977699	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32,2 W

Maxos LED Performer

Order Code	Full Product Name	Tensione in ingresso	Consumo energetico
66387399	4MX900 LED40S/840 PSD WB WH L1200	Da 220 a 240 V	25,9 W
66388099	4MX900 LED40S/840 PSD MB WH L1200	Da 220 a 240 V	25,9 W
66389799	4MX900 LED40S/840 PSD NB WH L1200	Da 220 a 240 V	25,9 W
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Da 220 a 240 V	25,9 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	Da 220 a 240 V	37,3 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	Da 220 a 240 V	37,3 W
66446799	4MX900 LED60S/840 PSD NB WH L1800	Da 220 a 240 V	37,3 W
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Da 220 a 240 V	37,3 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	Da 220 a 240 V	60,1 W
66461099	4MX900 LED90S/840 PSD MB WH L1800	Da 220 a 240 V	60,1 W
66462799	4MX900 LED90S/840 PSD NB WH L1800	Da 220 a 240 V	60,1 W
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Da 220 a 240 V	60,1 W
66476499	4MX900 581 LED40S/840 PSU WB WH	Da 220 a 240 V	25,2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	Da 220 a 240 V	25,2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	Da 220 a 240 V	25,2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	Da 220 a 240 V	25,2 W
66612699	4MX900 LED40S/840 PSU WB WH L1200	Da 220 a 240 V	25,9 W
66624999	4MX900 491 LED40S/840 PSD WB WH	Da 220 a 240 V	25,2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	Da 220 a 240 V	25,2 W
66626399	4MX900 491 LED40S/840 PSD NB WH	Da 220 a 240 V	25,2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	Da 220 a 240 V	32,2 W
66629499	4MX900 491 LED50S/840 PSD MB WH	Da 220 a 240 V	32,2 W
66630099	4MX900 491 LED50S/840 PSD NB WH	Da 220 a 240 V	32,2 W
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Da 220 a 240 V	32,2 W
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Da 220 a 240 V	25,9 W

Order Code	Full Product Name	Tensione in ingresso	Consumo energetico
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Da 220 a 240 V	37,3 W
66636299	4MX900 581 LED40S/840 PSU A30 WH	Da 220 a 240 V	25,2 W
66637999	4MX900 581 LED50S/840 PSU A30 WH	Da 220 a 240 V	32,2 W
66638699	4MX900 491 LED40S/840 PSU A30 WH	Da 220 a 240 V	25,2 W
66639399	4MX900 491 LED50S/840 PSU A30 WH	Da 220 a 240 V	32,2 W
66640999	4MX900 581 LED50S/840 PSU WB WH	Da 220 a 240 V	32,2 W
66641699	4MX900 581 LED50S/840 PSU MB WH	Da 220 a 240 V	32,2 W
66644799	4MX900 491 LED50S/840 PSU WB WH	Da 220 a 240 V	32,2 W
66645499	4MX900 491 LED50S/840 PSU MB WH	Da 220 a 240 V	32,2 W
66646199	4MX900 491 LED50S/840 PSU NB WH	Da 220 a 240 V	32,2 W
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Da 220 a 240 V	60,1 W
66709399	4MX900 581 LED75S/840 PSU A30 WH	Da 220 a 240 V	50,2 W
66711699	4MX900 491 LED75S/840 PSU A30 WH	Da 220 a 240 V	50,2 W
66727799	4MX900 491 LED50S/840 PSU DA30 WH	Da 220 a 240 V	32,2 W
66790199	4MX900 491 LED75S/840 PSU WB WH	Da 220 a 240 V	50,2 W
66791899	4MX900 491 LED75S/840 PSU MB WH	Da 220 a 240 V	50,2 W
66795699	4MX900 581 LED75S/840 PSU WB WH	Da 220 a 240 V	50,2 W
66796399	4MX900 581 LED75S/840 PSU MB WH	Da 220 a 240 V	50,2 W
66797099	4MX900 581 LED75S/840 PSU NB WH	Da 220 a 240 V	50,2 W
66800799	4MX900 491 LED75S/840 PSD WB WH	Da 220 a 240 V	50,2 W
66801499	4MX900 491 LED75S/840 PSD MB WH	Da 220 a 240 V	50,2 W
66802199	4MX900 491 LED75S/840 PSD NB WH	Da 220 a 240 V	50,2 W
66804599	4MX900 491 LED75S/840 PSD DA20 WH	Da 220 a 240 V	50,2 W
66805299	4MX900 491 LED75S/840 PSD A30 WH	Da 220 a 240 V	50,2 W
66806999	4MX900 581 LED75S/840 PSD WB WH	Da 220 a 240 V	50,2 W

Maxos LED Performer

Order Code	Full Product Name	Tensione in ingresso	Consumo
			energetico
66807699	4MX900 581 LED75S/840 PSD MB WH	Da 220 a 240 V	50,2 W
66808399	4MX900 581 LED75S/840 PSD NB WH	Da 220 a 240 V	50,2 W
66810699	4MX900 581 LED75S/840 PSD DA20 WH	Da 220 a 240 V	50,2 W
66811399	4MX900 581 LED75S/840 PSD A30 WH	Da 220 a 240 V	50,2 W
66883099	4MX900 581 LED50S/840 PSD A30 WH	Da 220 a 240 V	32,2 W
66436899	4MX900 LED60S/840 PSD WB SI L1800	Da 220 a 240 V	37,3 W

Order Code	Full Product Name	Tensione in ingresso	Consumo
			energetico
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Da 220 a 240 V	37,3 W
66452899	4MX900 LED90S/840 PSD WB SI L1800	Da 220 a 240 V	60,1 W
66453599	4MX900 LED90S/840 PSD MB SI L1800	Da 220 a 240 V	60,1 W
66484999	4MX900 491 LED40S/840 PSU WB SI	Da 220 a 240 V	25,2 W
66683699	4MX900 LED90S/840 PSD A30 SI L1800	Da 220 a 240 V	60,1 W
67195399	4MX900 581 LED50S/840 PSU A30 SI	Da 220 a 240 V	32,2 W

Controlli e dimmerazione

Order Code	Full Product Name	Dimmerabile
66882399	4MX900 581 LED50S/840 PSD MB WH	Si
66977699	4MX900 581 LED50S/840 PSD WB WH	Si
66387399	4MX900 LED40S/840 PSD WB WH L1200	Si
66388099	4MX900 LED40S/840 PSD MB WH L1200	Si
66389799	4MX900 LED40S/840 PSD NB WH L1200	Si
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Si
66444399	4MX900 LED60S/840 PSD WB WH L1800	Si
66445099	4MX900 LED60S/840 PSD MB WH L1800	Si
66446799	4MX900 LED60S/840 PSD NB WH L1800	Si
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Si
66460399	4MX900 LED90S/840 PSD WB WH L1800	Si
66461099	4MX900 LED90S/840 PSD MB WH L1800	Si
66462799	4MX900 LED90S/840 PSD NB WH L1800	Si
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Si
66476499	4MX900 581 LED40S/840 PSU WB WH	No
66477199	4MX900 581 LED40S/840 PSU MB WH	No
66492499	4MX900 491 LED40S/840 PSU WB WH	No
66493199	4MX900 491 LED40S/840 PSU MB WH	No
66612699	4MX900 LED40S/840 PSU WB WH L1200	No
66624999	4MX900 491 LED40S/840 PSD WB WH	Si
66625699	4MX900 491 LED40S/840 PSD MB WH	Si
66626399	4MX900 491 LED40S/840 PSD NB WH	Si
66628799	4MX900 491 LED50S/840 PSD WB WH	Si
66629499	4MX900 491 LED50S/840 PSD MB WH	Si
66630099	4MX900 491 LED50S/840 PSD NB WH	Si
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Si
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Si
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Si
66636299	4MX900 581 LED40S/840 PSU A30 WH	No
66637999	4MX900 581 LED50S/840 PSU A30 WH	No
66638699	4MX900 491 LED40S/840 PSU A30 WH	No
66639399	4MX900 491 LED50S/840 PSU A30 WH	No

Order Code	Full Product Name	Dimmerabile
66640999	4MX900 581 LED50S/840 PSU WB WH	No
66641699	4MX900 581 LED50S/840 PSU MB WH	No
66644799	4MX900 491 LED50S/840 PSU WB WH	No
66645499	4MX900 491 LED50S/840 PSU MB WH	No
66646199	4MX900 491 LED50S/840 PSU NB WH	No
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Si
66709399	4MX900 581 LED75S/840 PSU A30 WH	No
66711699	4MX900 491 LED75S/840 PSU A30 WH	No
66727799	4MX900 491 LED50S/840 PSU DA30 WH	No
66790199	4MX900 491 LED75S/840 PSU WB WH	No
66791899	4MX900 491 LED75S/840 PSU MB WH	No
66795699	4MX900 581 LED75S/840 PSU WB WH	No
66796399	4MX900 581 LED75S/840 PSU MB WH	No
66797099	4MX900 581 LED75S/840 PSU NB WH	No
66800799	4MX900 491 LED75S/840 PSD WB WH	Si
66801499	4MX900 491 LED75S/840 PSD MB WH	Si
66802199	4MX900 491 LED75S/840 PSD NB WH	Si
66804599	4MX900 491 LED75S/840 PSD DA20 WH	Si
66805299	4MX900 491 LED75S/840 PSD A30 WH	Si
66806999	4MX900 581 LED75S/840 PSD WB WH	Si
66807699	4MX900 581 LED75S/840 PSD MB WH	Si
66808399	4MX900 581 LED75S/840 PSD NB WH	Si
66810699	4MX900 581 LED75S/840 PSD DA20 WH	Si
66811399	4MX900 581 LED75S/840 PSD A30 WH	Si
66883099	4MX900 581 LED50S/840 PSD A30 WH	Si
66436899	4MX900 LED60S/840 PSD WB SI L1800	Si
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Si
66452899	4MX900 LED90S/840 PSD WB SI L1800	Si
66453599	4MX900 LED90S/840 PSD MB SI L1800	Si
66484999	4MX900 491 LED40S/840 PSU WB SI	No
66683699	4MX900 LED90S/840 PSD A30 SI L1800	Si
67195399	4MX900 581 LED50S/840 PSU A30 SI	No

Meccanica e corpo

Maxos LED Performer

Order Code	Full Product Name	Colore alloggiamento
66882399	4MX900 581 LED50S/840 PSD MB WH	Bianco
66977699	4MX900 581 LED50S/840 PSD WB WH	Bianco
66387399	4MX900 LED40S/840 PSD WB WH L1200	Bianco
66388099	4MX900 LED40S/840 PSD MB WH L1200	Bianco
66389799	4MX900 LED40S/840 PSD NB WH L1200	Bianco
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Bianco
66444399	4MX900 LED60S/840 PSD WB WH L1800	Bianco
66445099	4MX900 LED60S/840 PSD MB WH L1800	Bianco
66446799	4MX900 LED60S/840 PSD NB WH L1800	Bianco
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Bianco
66460399	4MX900 LED90S/840 PSD WB WH L1800	Bianco
66461099	4MX900 LED90S/840 PSD MB WH L1800	Bianco
66462799	4MX900 LED90S/840 PSD NB WH L1800	Bianco
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Bianco
66476499	4MX900 581 LED40S/840 PSU WB WH	Bianco
66477199	4MX900 581 LED40S/840 PSU MB WH	Bianco
66492499	4MX900 491 LED40S/840 PSU WB WH	Bianco
66493199	4MX900 491 LED40S/840 PSU MB WH	Bianco
66612699	4MX900 LED40S/840 PSU WB WH L1200	Bianco
66624999	4MX900 491 LED40S/840 PSD WB WH	Bianco
66625699	4MX900 491 LED40S/840 PSD MB WH	Bianco
66626399	4MX900 491 LED40S/840 PSD NB WH	Bianco
66628799	4MX900 491 LED50S/840 PSD WB WH	Bianco
66629499	4MX900 491 LED50S/840 PSD MB WH	Bianco
66630099	4MX900 491 LED50S/840 PSD NB WH	Bianco
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Bianco
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Bianco
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Bianco
66636299	4MX900 581 LED40S/840 PSU A30 WH	Bianco
66637999	4MX900 581 LED50S/840 PSU A30 WH	Bianco
66638699	4MX900 491 LED40S/840 PSU A30 WH	Bianco
66639399	4MX900 491 LED50S/840 PSU A30 WH	Bianco

Order Code	Full Product Name	Colore alloggiamento
66640999	4MX900 581 LED50S/840 PSU WB WH	Bianco
66641699	4MX900 581 LED50S/840 PSU MB WH	Bianco
66644799	4MX900 491 LED50S/840 PSU WB WH	Bianco
66645499	4MX900 491 LED50S/840 PSU MB WH	Bianco
66646199	4MX900 491 LED50S/840 PSU NB WH	Bianco
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Bianco
66709399	4MX900 581 LED75S/840 PSU A30 WH	Bianco
66711699	4MX900 491 LED75S/840 PSU A30 WH	Bianco
66727799	4MX900 491 LED50S/840 PSU DA30 WH	Bianco
66790199	4MX900 491 LED75S/840 PSU WB WH	Bianco
66791899	4MX900 491 LED75S/840 PSU MB WH	Bianco
66795699	4MX900 581 LED75S/840 PSU WB WH	Bianco
66796399	4MX900 581 LED75S/840 PSU MB WH	Bianco
66797099	4MX900 581 LED75S/840 PSU NB WH	Bianco
66800799	4MX900 491 LED75S/840 PSD WB WH	Bianco
66801499	4MX900 491 LED75S/840 PSD MB WH	Bianco
66802199	4MX900 491 LED75S/840 PSD NB WH	Bianco
66804599	4MX900 491 LED75S/840 PSD DA20 WH	Bianco
66805299	4MX900 491 LED75S/840 PSD A30 WH	Bianco
66806999	4MX900 581 LED75S/840 PSD WB WH	Bianco
66807699	4MX900 581 LED75S/840 PSD MB WH	Bianco
66808399	4MX900 581 LED75S/840 PSD NB WH	Bianco
66810699	4MX900 581 LED75S/840 PSD DA20 WH	Bianco
66811399	4MX900 581 LED75S/840 PSD A30 WH	Bianco
66883099	4MX900 581 LED50S/840 PSD A30 WH	Bianco
66436899	4MX900 LED60S/840 PSD WB SI L1800	Argento
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Argento
66452899	4MX900 LED90S/840 PSD WB SI L1800	Argento
66453599	4MX900 LED90S/840 PSD MB SI L1800	Argento
66484999	4MX900 491 LED40S/840 PSU WB SI	Argento
66683699	4MX900 LED90S/840 PSD A30 SI L1800	Argento
67195399	4MX900 581 LED50S/840 PSU A30 SI	Argento

Condizioni di applicazione

Order Code	Full Product Name	Livello massimo di attenuazione
66882399	4MX900 581 LED50S/840 PSD MB WH	1%
66977699	4MX900 581 LED50S/840 PSD WB WH	1%
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66388099	4MX900 LED40S/840 PSD MB WH L1200	1%
66389799	4MX900 LED40S/840 PSD NB WH L1200	1%
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66446799	4MX900 LED60S/840 PSD NB WH L1800	1%
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66462799	4MX900 LED90S/840 PSD NB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%
66476499	4MX900 581 LED40S/840 PSU WB WH	Non applicabile




Order Code	Full Product Name	Livello massimo di attenuazione
66477199	4MX900 581 LED40S/840 PSU MB WH	Non applicabile
66492499	4MX900 491 LED40S/840 PSU WB WH	Non applicabile
66493199	4MX900 491 LED40S/840 PSU MB WH	Non applicabile
66612699	4MX900 LED40S/840 PSU WB WH L1200	Non applicabile
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%
66630099	4MX900 491 LED50S/840 PSD NB WH	1%
66631799	4MX900 491 LED50S/840 PSD DA20 WH	1%
66633199	4MX900 LED40S/840 PSD A30 WH L1200	1%
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%
66636299	4MX900 581 LED40S/840 PSU A30 WH	Non applicabile
66637999	4MX900 581 LED50S/840 PSU A30 WH	Non applicabile

Maxos LED Performer

Order Code	Full Product Name	Livello massimo di attenuazione
66638699	4MX900 491 LED40S/840 PSU A30 WH	Non applicabile
66639399	4MX900 491 LED50S/840 PSU A30 WH	Non applicabile
66640999	4MX900 581 LED50S/840 PSU WB WH	Non applicabile
66641699	4MX900 581 LED50S/840 PSU MB WH	Non applicabile
66644799	4MX900 491 LED50S/840 PSU WB WH	Non applicabile
66645499	4MX900 491 LED50S/840 PSU MB WH	Non applicabile
66646199	4MX900 491 LED50S/840 PSU NB WH	Non applicabile
66681299	4MX900 LED90S/840 PSD A30 WH L1800	1%
66709399	4MX900 581 LED75S/840 PSU A30 WH	Non applicabile
66711699	4MX900 491 LED75S/840 PSU A30 WH	Non applicabile
66727799	4MX900 491 LED50S/840 PSU DA30 WH	Non applicabile
66790199	4MX900 491 LED75S/840 PSU WB WH	Non applicabile
66791899	4MX900 491 LED75S/840 PSU MB WH	Non applicabile
66795699	4MX900 581 LED75S/840 PSU WB WH	Non applicabile
66796399	4MX900 581 LED75S/840 PSU MB WH	Non applicabile
66797099	4MX900 581 LED75S/840 PSU NB WH	Non applicabile
66800799	4MX900 491 LED75S/840 PSD WB WH	1%

Order Code	Full Product Name	Livello massimo di attenuazione
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66802199	4MX900 491 LED75S/840 PSD NB WH	1%
66804599	4MX900 491 LED75S/840 PSD DA20 WH	1%
66805299	4MX900 491 LED75S/840 PSD A30 WH	1%
66806999	4MX900 581 LED75S/840 PSD WB WH	1%
66807699	4MX900 581 LED75S/840 PSD MB WH	1%
66808399	4MX900 581 LED75S/840 PSD NB WH	1%
66810699	4MX900 581 LED75S/840 PSD DA20 WH	1%
66811399	4MX900 581 LED75S/840 PSD A30 WH	1%
66883099	4MX900 581 LED50S/840 PSD A30 WH	1%
66436899	4MX900 LED60S/840 PSD WB SI L1800	1%
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	1%
66452899	4MX900 LED90S/840 PSD WB SI L1800	1%
66453599	4MX900 LED90S/840 PSD MB SI L1800	1%
66484999	4MX900 491 LED40S/840 PSU WB SI	Non applicabile
66683699	4MX900 LED90S/840 PSD A30 SI L1800	1%
67195399	4MX900 581 LED50S/840 PSU A30 SI	Non applicabile




Polar Wide Diagrams



IFPS_4MX900 491 1xLED40S/830 PSD A30-
Polar Normal (separate)

IFPS_4MX900 491 1xLED40S/830 PSD DA20-
Polar Normal (separate)

IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)


IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)

IFPS_4MX900 491 1xLED40S/830 PSU NB-
Polar Normal (separate)


Polar Wide Diagrams




IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSD A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSU A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSU DA30-
Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD A30-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED50S/830 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU DA30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED50S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED50S/840 PSU DA30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD DA20-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU DA30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSD NB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSD DA20-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED50S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD NB-Polar
Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSU NB-Polar
Normal (separate)**



**IFPS_4MX900 581 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD MB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 581 1xLED75S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 581 1xLED75S/840 PSU A30-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED32S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED40S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED40S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED57S/830 PSD MB-
Polar Normal (separate)



IFPS_4MX900 L1200 1xLED57S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED57S/830 PSU WB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 L1200 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD NB-
Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED48S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 L1800 1xLED60S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/840 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/840 PSD MB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD MB-
Polar Normal (separate)



IFPS_4MX900 L1800 1xLED85S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED90S/840 PSD NB-
Polar Normal (separate)


Polar Wide Diagrams




IFPS_4MX900 G3 491 1xLED40S/830 PSD
A30-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSU NB-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSD
A30-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSD
DA20-Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU
DA30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/840 PSU
DA30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU
DA30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**






**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-
Polar Normal (separate)**




Polar Wide Diagrams



**IFPS_4MX900 G3 491 1xLED75S/840 PSU
DA30-Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED40S/830 PSD A30-
Polar Normal (separate)**

**IFPS_4MX900 G3 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**

**IFPS_4MX900 G3 581 1xLED40S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSU NB-
Polar Normal (separate)**


**IFPS_4MX900 G3 581 1xLED40S/840 PSD A30-
Polar Normal (separate)**

**IFPS_4MX900 G3 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 G3 581 1xLED40S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED40S/840 PSU NB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/830 PSD
DA20- Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)


Polar Wide Diagrams




IFPS_4MX900 G3 581 1xLED50S/840 PSD MB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSD
DA20- Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSD WB-
Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSU NB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSD A30-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED75S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 L1200 1xLED40S/830 PSD
NB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1200 1xLED40S/840 PSU
WB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1200 1xLED60S/840 PSU
WB-Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
NB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
WB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
MB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
NB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED90S/840 PSD
NB-Polar Normal (separate)

Maxos LED Performer

