



Maxos LED Performer – svetelný rad s výkonným a presným svetlom

Maxos LED Performer

Zákazníci chcú šetriť energiu a tiež dosiahnuť nižšie náklady v porovnaní s tými, na aké sú zvyknutí pri používaní konvenčného osvetlenia. Zároveň požadujú osvetlenie vynikajúcej kvality, ktoré v prostredí priemyselnej výroby zaistí bezpečnosť a produktivitu a v obchodoch upúta pozornosť nakupujúcich a zvýši záujem o prezentovaný tovar. Mimoriadne flexibilné riešenie Maxos LED Performer ponúka nízku spotrebu energie a skvele riadený svetelný lúč za atraktívnu cenu.

Výhody

- Veľmi rýchla návratnosť investícií
- Prelomový optický systém na zabezpečenie precízneho vyžarovania svetla
- Flexibilita v súvislosti s možnosťou zámieny, umiestnením bodových svietidiel, zmenami či príslušenstvom

Vlastnosti


- Nízka spotreba energie v porovnaní s žiarivkovým riešením
- Skvele formovaný lúč minimalizuje nežiaduce rozptýlenie svetla a zabezpečuje presnú rozloženie svetla v horizontálnej i vertikálnej rovine
- Osvedčené systémy LED od spoločnosti Philips (Fortimo)
- Možnosť montáže na lištový systém Maxos
- Dostupné tiež vo flexibilnej panelovej verzii 4MX800 alebo vo verzii s vysokým výkonom 4MX850

Maxos LED Performer

Aplikácie

- Obchodné domy
- Sklady
- Výrobné priestory

Rozmerový obrázok




Podrobnosti o produkte

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



Maxos LED Performer

Podrobnosti o produkte



IPDP_4MX900i_0011-Detail
photo

Maxos LED Performer

Všeobecné informácie	
Značka CE	Áno
Vrátane napájača	Áno
Značka ENEC	Značka ENEC
Značka horľavosti	-
Požiarna odolnosť	Teplota 650 °C, trvanie 30 s
Vymeniteľný svetelný zdroj	Nie
Počet jednotiek predradníka	1 jednotka
Kód radu produktov	4MX900
Svetelné technické	
Možnosť vyžarovania svetelného zdroja	120 stupeň (stupne)
Náhradná teplota chromatickosti (men.)	4000 K
Index podania farieb (CRI)	≥80
Počet svetelných zdrojov	1
Prevádzkové a elektrické	
Vstupné napätie	220 až 240 V
Sieťová frekvencia	50 to 60 Hz
Teplota	
Široký rozsah okolitých teplôt	-20 až +40 °C
Schválenie a použitie	
Trieda ochrany IEC	Bezpečnostná trieda I
Kód krytia IP (mechanický náraz)	IK02
Krytie IP	IP40
Počiatočný výkon (súlad s požiadavkami IEC)	
Počiatočná chromatickosť	(0.38, 0.38) SDCM <3.5
Tolerancia svetelného toku	+/-10%
Podmienky použitia	
Vhodné pre náhodné prepínanie	Nevzťahuje sa na zariadenie

Všeobecné informácie

Order Code	Full Product Name	Kód radu svetelného zdroja
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S
66388099	4MX900 LED40S/840 PSD MB WH L1200	LED40S
66389799	4MX900 LED40S/840 PSD NB WH L1200	LED40S
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	LED40S
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S
66446799	4MX900 LED60S/840 PSD NB WH L1800	LED60S
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	LED60S
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S
66462799	4MX900 LED90S/840 PSD NB WH L1800	LED90S
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S
66612699	4MX900 LED40S/840 PSU WB WH L1200	LED40S
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S
66630099	4MX900 491 LED50S/840 PSD NB WH	LED50S
66631799	4MX900 491 LED50S/840 PSD DA20 WH	LED50S
66633199	4MX900 LED40S/840 PSD A30 WH L1200	LED40S
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
66636299	4MX900 581 LED40S/840 PSU A30 WH	LED40S
66637999	4MX900 581 LED50S/840 PSU A30 WH	LED50S
66638699	4MX900 491 LED40S/840 PSU A30 WH	LED40S
66639399	4MX900 491 LED50S/840 PSU A30 WH	LED50S
66640999	4MX900 581 LED50S/840 PSU WB WH	LED50S
66641699	4MX900 581 LED50S/840 PSU MB WH	LED50S
66644799	4MX900 491 LED50S/840 PSU WB WH	LED50S
66645499	4MX900 491 LED50S/840 PSU MB WH	LED50S
66646199	4MX900 491 LED50S/840 PSU NB WH	LED50S
66681299	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
66790199	4MX900 491 LED75S/840 PSU WB WH	LED75S
66795699	4MX900 581 LED75S/840 PSU WB WH	LED75S
66796399	4MX900 581 LED75S/840 PSU MB WH	LED75S
66800799	4MX900 491 LED75S/840 PSD WB WH	LED75S
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S
66805299	4MX900 491 LED75S/840 PSD A30 WH	LED75S
66806999	4MX900 581 LED75S/840 PSD WB WH	LED75S
66807699	4MX900 581 LED75S/840 PSD MB WH	LED75S
66436899	4MX900 LED60S/840 PSD WB SI L1800	LED60S
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	LED60S
66452899	4MX900 LED90S/840 PSD WB SI L1800	LED90S
66453599	4MX900 LED90S/840 PSD MB SI L1800	LED90S
66484999	4MX900 491 LED40S/840 PSU WB SI	LED40S

Svetelné technické

Maxos LED Performer

Order Code	Full Product Name	Merný výkon (menovitý)			Typ optiky
		(nom.)	Svetelný tok		
66387399	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4 000 lm	Široké vyžarovanie	
66388099	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4 000 lm	Stredné vyžarovanie	
66389799	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4 000 lm	Úzke vyžarovanie	
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	154 lm/W	4 000 lm	Dvojitá asymetrická optika, 20°	
66444399	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6 000 lm	Široké vyžarovanie	
66445099	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6 000 lm	Stredné vyžarovanie	
66446799	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6 000 lm	Úzke vyžarovanie	
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	161 lm/W	6 000 lm	Dvojitá asymetrická optika, 20°	
66460399	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9 000 lm	Široké vyžarovanie	
66461099	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9 000 lm	Stredné vyžarovanie	
66462799	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9 000 lm	Úzke vyžarovanie	
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9 000 lm	Dvojitá asymetrická optika, 20°	
66476499	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4 000 lm	Široké vyžarovanie	
66477199	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4 000 lm	Stredné vyžarovanie	
66492499	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4 000 lm	Široké vyžarovanie	
66493199	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4 000 lm	Stredné vyžarovanie	
66612699	4MX900 LED40S/840 PSU WB WH L1200	154 lm/W	4 000 lm	Široké vyžarovanie	
66624999	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4 000 lm	Široké vyžarovanie	
66625699	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4 000 lm	Stredné vyžarovanie	
66626399	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4 000 lm	Úzke vyžarovanie	

Order Code	Full Product Name	Merný výkon (menovitý)			Typ optiky
		(nom.)	Svetelný tok		
66628799	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5 000 lm	Široké vyžarovanie	
66629499	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5 000 lm	Stredné vyžarovanie	
66630099	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5 000 lm	Úzke vyžarovanie	
66631799	4MX900 491 LED50S/840 PSD DA20 WH	155 lm/W	5 000 lm	Dvojitá asymetrická optika, 20°	
66633199	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4 000 lm	Asymetrický reflektor, uhol osi 30°	
66635599	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6 000 lm	Asymetrický reflektor, uhol osi 30°	
66636299	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4 000 lm	Asymetrický reflektor, uhol osi 30°	
66637999	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5 000 lm	Asymetrický reflektor, uhol osi 30°	
66638699	4MX900 491 LED40S/840 PSU A30 WH	159 lm/W	4 000 lm	Asymetrický reflektor, uhol osi 30°	
66639399	4MX900 491 LED50S/840 PSU A30 WH	155 lm/W	5 000 lm	Asymetrický reflektor, uhol osi 30°	
66640999	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5 000 lm	Široké vyžarovanie	
66641699	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5 000 lm	Stredné vyžarovanie	
66644799	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5 000 lm	Široké vyžarovanie	
66645499	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5 000 lm	Stredné vyžarovanie	
66646199	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5 000 lm	Úzke vyžarovanie	
66681299	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9 000 lm	Asymetrický reflektor, uhol osi 30°	

Maxos LED Performer

Order Code	Full Product Name	Merný výkon (menovitý)		
		(nom.)	Svetelný tok	Typ optiky
66790199	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7 500 lm	Široké vyžarovanie
66795699	4MX900 581 LED75S/840 PSU WB WH	149 lm/W	7 500 lm	Široké vyžarovanie
66796399	4MX900 581 LED75S/840 PSU MB WH	149 lm/W	7 500 lm	Stredné vyžarovanie
66800799	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7 500 lm	Široké vyžarovanie
66801499	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7 500 lm	Stredné vyžarovanie
66805299	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7 500 lm	Asymetrický reflektor, uhol osi 30°

Order Code	Full Product Name	Merný výkon (menovitý)		
		(nom.)	Svetelný tok	Typ optiky
66806999	4MX900 581 LED75S/840 PSD WB WH	149 lm/W	7 500 lm	Široké vyžarovanie
66807699	4MX900 581 LED75S/840 PSD MB WH	149 lm/W	7 500 lm	Stredné vyžarovanie
66436899	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6 000 lm	Široké vyžarovanie
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	161 lm/W	6 000 lm	Dvojitá asymetrická optika, 20°
66452899	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9 000 lm	Široké vyžarovanie
66453599	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9 000 lm	Stredné vyžarovanie
66484999	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4 000 lm	Široké vyžarovanie

Prevádzkové a elektrické

Order Code	Full Product Name	Spotreba
66387399	4MX900 LED40S/840 PSD WB WH L1200	25,9 W
66388099	4MX900 LED40S/840 PSD MB WH L1200	25,9 W
66389799	4MX900 LED40S/840 PSD NB WH L1200	25,9 W
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	25,9 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	37,3 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	37,3 W
66446799	4MX900 LED60S/840 PSD NB WH L1800	37,3 W
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	37,3 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	60,1 W
66461099	4MX900 LED90S/840 PSD MB WH L1800	60,1 W
66462799	4MX900 LED90S/840 PSD NB WH L1800	60,1 W
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	60,1 W
66476499	4MX900 581 LED40S/840 PSU WB WH	25,2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	25,2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	25,2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	25,2 W
66612699	4MX900 LED40S/840 PSU WB WH L1200	25,9 W
66624999	4MX900 491 LED40S/840 PSD WB WH	25,2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	25,2 W
66626399	4MX900 491 LED40S/840 PSD NB WH	25,2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	32,2 W
66629499	4MX900 491 LED50S/840 PSD MB WH	32,2 W
66630099	4MX900 491 LED50S/840 PSD NB WH	32,2 W
66631799	4MX900 491 LED50S/840 PSD DA20 WH	32,2 W
66633199	4MX900 LED40S/840 PSD A30 WH L1200	25,9 W

Order Code	Full Product Name	Spotreba
66635599	4MX900 LED60S/840 PSD A30 WH L1800	37,3 W
66636299	4MX900 581 LED40S/840 PSU A30 WH	25,2 W
66637999	4MX900 581 LED50S/840 PSU A30 WH	32,2 W
66638699	4MX900 491 LED40S/840 PSU A30 WH	25,2 W
66639399	4MX900 491 LED50S/840 PSU A30 WH	32,2 W
66640999	4MX900 581 LED50S/840 PSU WB WH	32,2 W
66641699	4MX900 581 LED50S/840 PSU MB WH	32,2 W
66644799	4MX900 491 LED50S/840 PSU WB WH	32,2 W
66645499	4MX900 491 LED50S/840 PSU MB WH	32,2 W
66646199	4MX900 491 LED50S/840 PSU NB WH	32,2 W
66681299	4MX900 LED90S/840 PSD A30 WH L1800	60,1 W
66790199	4MX900 491 LED75S/840 PSU WB WH	50,2 W
66795699	4MX900 581 LED75S/840 PSU WB WH	50,2 W
66796399	4MX900 581 LED75S/840 PSU MB WH	50,2 W
66800799	4MX900 491 LED75S/840 PSD WB WH	50,2 W
66801499	4MX900 491 LED75S/840 PSD MB WH	50,2 W
66805299	4MX900 491 LED75S/840 PSD A30 WH	50,2 W
66806999	4MX900 581 LED75S/840 PSD WB WH	50,2 W
66807699	4MX900 581 LED75S/840 PSD MB WH	50,2 W
66436899	4MX900 LED60S/840 PSD WB SI L1800	37,3 W
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	37,3 W
66452899	4MX900 LED90S/840 PSD WB SI L1800	60,1 W
66453599	4MX900 LED90S/840 PSD MB SI L1800	60,1 W
66484999	4MX900 491 LED40S/840 PSU WB SI	25,2 W

Ovládanie a stmievanie

Maxos LED Performer

Order Code	Full Product Name	Stmievateľné
66387399	4MX900 LED40S/840 PSD WB WH L1200	Áno
66388099	4MX900 LED40S/840 PSD MB WH L1200	Áno
66389799	4MX900 LED40S/840 PSD NB WH L1200	Áno
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Áno
66444399	4MX900 LED60S/840 PSD WB WH L1800	Áno
66445099	4MX900 LED60S/840 PSD MB WH L1800	Áno
66446799	4MX900 LED60S/840 PSD NB WH L1800	Áno
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Áno
66460399	4MX900 LED90S/840 PSD WB WH L1800	Áno
66461099	4MX900 LED90S/840 PSD MB WH L1800	Áno
66462799	4MX900 LED90S/840 PSD NB WH L1800	Áno
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Áno
66476499	4MX900 581 LED40S/840 PSU WB WH	Nie
66477199	4MX900 581 LED40S/840 PSU MB WH	Nie
66492499	4MX900 491 LED40S/840 PSU WB WH	Nie
66493199	4MX900 491 LED40S/840 PSU MB WH	Nie
66612699	4MX900 LED40S/840 PSU WB WH L1200	Nie
66624999	4MX900 491 LED40S/840 PSD WB WH	Áno
66625699	4MX900 491 LED40S/840 PSD MB WH	Áno
66626399	4MX900 491 LED40S/840 PSD NB WH	Áno
66628799	4MX900 491 LED50S/840 PSD WB WH	Áno
66629499	4MX900 491 LED50S/840 PSD MB WH	Áno
66630099	4MX900 491 LED50S/840 PSD NB WH	Áno
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Áno
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Áno

Order Code	Full Product Name	Stmievateľné
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Áno
66636299	4MX900 581 LED40S/840 PSU A30 WH	Nie
66637999	4MX900 581 LED50S/840 PSU A30 WH	Nie
66638699	4MX900 491 LED40S/840 PSU A30 WH	Nie
66639399	4MX900 491 LED50S/840 PSU A30 WH	Nie
66640999	4MX900 581 LED50S/840 PSU WB WH	Nie
66641699	4MX900 581 LED50S/840 PSU MB WH	Nie
66644799	4MX900 491 LED50S/840 PSU WB WH	Nie
66645499	4MX900 491 LED50S/840 PSU MB WH	Nie
66646199	4MX900 491 LED50S/840 PSU NB WH	Nie
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Áno
66790199	4MX900 491 LED75S/840 PSU WB WH	Nie
66795699	4MX900 581 LED75S/840 PSU WB WH	Nie
66796399	4MX900 581 LED75S/840 PSU MB WH	Nie
66800799	4MX900 491 LED75S/840 PSD WB WH	Áno
66801499	4MX900 491 LED75S/840 PSD MB WH	Áno
66805299	4MX900 491 LED75S/840 PSD A30 WH	Áno
66806999	4MX900 581 LED75S/840 PSD WB WH	Áno
66807699	4MX900 581 LED75S/840 PSD MB WH	Áno
66436899	4MX900 LED60S/840 PSD WB SI L1800	Áno
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Áno
66452899	4MX900 LED90S/840 PSD WB SI L1800	Áno
66453599	4MX900 LED90S/840 PSD MB SI L1800	Áno
66484999	4MX900 491 LED40S/840 PSU WB SI	Nie

Mechanické časti a teleso

Order Code	Full Product Name	Farba telesa
66387399	4MX900 LED40S/840 PSD WB WH L1200	Biela
66388099	4MX900 LED40S/840 PSD MB WH L1200	Biela
66389799	4MX900 LED40S/840 PSD NB WH L1200	Biela
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Biela
66444399	4MX900 LED60S/840 PSD WB WH L1800	Biela
66445099	4MX900 LED60S/840 PSD MB WH L1800	Biela
66446799	4MX900 LED60S/840 PSD NB WH L1800	Biela
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Biela
66460399	4MX900 LED90S/840 PSD WB WH L1800	Biela
66461099	4MX900 LED90S/840 PSD MB WH L1800	Biela
66462799	4MX900 LED90S/840 PSD NB WH L1800	Biela
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Biela
66476499	4MX900 581 LED40S/840 PSU WB WH	Biela
66477199	4MX900 581 LED40S/840 PSU MB WH	Biela
66492499	4MX900 491 LED40S/840 PSU WB WH	Biela
66493199	4MX900 491 LED40S/840 PSU MB WH	Biela
66612699	4MX900 LED40S/840 PSU WB WH L1200	Biela
66624999	4MX900 491 LED40S/840 PSD WB WH	Biela
66625699	4MX900 491 LED40S/840 PSD MB WH	Biela
66626399	4MX900 491 LED40S/840 PSD NB WH	Biela
66628799	4MX900 491 LED50S/840 PSD WB WH	Biela
66629499	4MX900 491 LED50S/840 PSD MB WH	Biela
66630099	4MX900 491 LED50S/840 PSD NB WH	Biela

Order Code	Full Product Name	Farba telesa
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Biela
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Biela
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Biela
66636299	4MX900 581 LED40S/840 PSU A30 WH	Biela
66637999	4MX900 581 LED50S/840 PSU A30 WH	Biela
66638699	4MX900 491 LED40S/840 PSU A30 WH	Biela
66639399	4MX900 491 LED50S/840 PSU A30 WH	Biela
66640999	4MX900 581 LED50S/840 PSU WB WH	Biela
66641699	4MX900 581 LED50S/840 PSU MB WH	Biela
66644799	4MX900 491 LED50S/840 PSU WB WH	Biela
66645499	4MX900 491 LED50S/840 PSU MB WH	Biela
66646199	4MX900 491 LED50S/840 PSU NB WH	Biela
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Biela
66790199	4MX900 491 LED75S/840 PSU WB WH	Biela
66795699	4MX900 581 LED75S/840 PSU WB WH	Biela
66796399	4MX900 581 LED75S/840 PSU MB WH	Biela
66800799	4MX900 491 LED75S/840 PSD WB WH	Biela
66801499	4MX900 491 LED75S/840 PSD MB WH	Biela
66805299	4MX900 491 LED75S/840 PSD A30 WH	Biela
66806999	4MX900 581 LED75S/840 PSD WB WH	Biela
66807699	4MX900 581 LED75S/840 PSD MB WH	Biela
66436899	4MX900 LED60S/840 PSD WB SI L1800	Strieborná
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Strieborná

Maxos LED Performer

Order Code	Full Product Name	Farba telesa
66452899	4MX900 LED90S/840 PSD WB SI L1800	Strieborná
66453599	4MX900 LED90S/840 PSD MB SI L1800	Strieborná


Order Code	Full Product Name	Farba telesa
66484999	4MX900 491 LED40S/840 PSU WB SI	Strieborná

Podmienky použitia


Order Code	Full Product Name	Maximálna úroveň stmievania
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66388099	4MX900 LED40S/840 PSD MB WH L1200	1%
66389799	4MX900 LED40S/840 PSD NB WH L1200	1%
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66446799	4MX900 LED60S/840 PSD NB WH L1800	1%
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66462799	4MX900 LED90S/840 PSD NB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%
66476499	4MX900 581 LED40S/840 PSU WB WH	Nevztahuje sa na zariadenie
66477199	4MX900 581 LED40S/840 PSU MB WH	Nevztahuje sa na zariadenie
66492499	4MX900 491 LED40S/840 PSU WB WH	Nevztahuje sa na zariadenie
66493199	4MX900 491 LED40S/840 PSU MB WH	Nevztahuje sa na zariadenie
66612699	4MX900 LED40S/840 PSU WB WH L1200	Nevztahuje sa na zariadenie
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%
66630099	4MX900 491 LED50S/840 PSD NB WH	1%
66631799	4MX900 491 LED50S/840 PSD DA20 WH	1%
66633199	4MX900 LED40S/840 PSD A30 WH L1200	1%

Order Code	Full Product Name	Maximálna úroveň stmievania
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%
66636299	4MX900 581 LED40S/840 PSU A30 WH	Nevztahuje sa na zariadenie
66637999	4MX900 581 LED50S/840 PSU A30 WH	Nevztahuje sa na zariadenie
66638699	4MX900 491 LED40S/840 PSU A30 WH	Nevztahuje sa na zariadenie
66639399	4MX900 491 LED50S/840 PSU A30 WH	Nevztahuje sa na zariadenie
66640999	4MX900 581 LED50S/840 PSU WB WH	Nevztahuje sa na zariadenie
66641699	4MX900 581 LED50S/840 PSU MB WH	Nevztahuje sa na zariadenie
66644799	4MX900 491 LED50S/840 PSU WB WH	Nevztahuje sa na zariadenie
66645499	4MX900 491 LED50S/840 PSU MB WH	Nevztahuje sa na zariadenie
66646199	4MX900 491 LED50S/840 PSU NB WH	Nevztahuje sa na zariadenie
66681299	4MX900 LED90S/840 PSD A30 WH L1800	1%
66790199	4MX900 491 LED75S/840 PSU WB WH	Nevztahuje sa na zariadenie
66795699	4MX900 581 LED75S/840 PSU WB WH	Nevztahuje sa na zariadenie
66796399	4MX900 581 LED75S/840 PSU MB WH	Nevztahuje sa na zariadenie
66800799	4MX900 491 LED75S/840 PSD WB WH	1%
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66805299	4MX900 491 LED75S/840 PSD A30 WH	1%
66806999	4MX900 581 LED75S/840 PSD WB WH	1%
66807699	4MX900 581 LED75S/840 PSD MB WH	1%
66436899	4MX900 LED60S/840 PSD WB SI L1800	1%
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	1%
66452899	4MX900 LED90S/840 PSD WB SI L1800	1%
66453599	4MX900 LED90S/840 PSD MB SI L1800	1%
66484999	4MX900 491 LED40S/840 PSU WB SI	Nevztahuje sa na zariadenie


Polar Wide Diagrams



IFPS_4MX900 491 1xLED40S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/830 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD DA20-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSU NB-
Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD DA20-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 L1200 1xLED32S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED40S/840 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1200 1xLED57S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD NB-
Polar Normal (separate)**



**IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1800 1xLED48S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD
DA20-Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED60S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 L1800 1xLED85S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD
A30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD
DA20-Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD
A30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD
DA20-Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD
DA20- Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED75S/840 PSD WB-
Polar Normal (separate)**






**IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)**




Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-Polar Normal (separate)

IFPS_4MX900 G3 L1200 1xLED40S/830 PSD NB-Polar Normal (separate)




IFPS_4MX900 G3 L1200 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 L1200 1xLED60S/840 PSU WB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/830 PSD NB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/830 PSD WB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/840 PSD MB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/840 PSD NB-Polar Normal (separate)

IFPS_4MX900 G3 L1800 1xLED60S/840 PSD WB-Polar Normal (separate)


Maxos LED Performer

Polar Wide Diagrams



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD

WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED90S/840 PSD

NB-Polar Normal (separate)

