



# LED Bollard II BCP150/151 – reliable landscape lighting for harmonious city living

## **LED Bollard II**

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience with optimized-quality lighting at minimum cost. Combining reliable low-power LEDs and an integrated driver, the robustly designed LED Bollard II delivers an affordable LED lighting solution to meet your landscaping needs.

#### **Benefits**

- · Reliable, robust design
- · Easy to install and maintenance-free
- · Environmentally friendly: no hazardous substances (no mercury, no lead) or UV

#### **Features**

- $\cdot$  Low-power white-light LED light source, available in a choice of warm white (3000 K) or neutral white (4000 K)
- Integrated baseplate and driver for easy installation
- · Choice of colors for housing (dark grey RAL7043, light grey RAL9006)
- · Height 0.5 m or 0.8 m
- Long lifetime of 25,000 hours (70% lumen maintenance @ Tc = 25°C)
- IP65 protection and IK10 impact resistance

## **LED Bollard II**

## **Application**

- · Parks and gardens
- · Squares, plazas
- · Residential areas

### Versions



LED Bollard II BCP150/151



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.