



## FWC LED

Only texts for Benelux market available

### Benefits

• Only texts for Benelux market available

### Features

• Only texts for Benelux market available

### Application

• Only texts for Benelux market available

## Versions

BWC110 amenity-lighting  
luminaire



BWC110 amenity-lighting  
luminaire with photocell



BWC110 amenity-lighting  
luminaire



BWC110 amenity-lighting  
luminaire with photocell



# FWC LED

## Versions



**BWC120 amenity-lighting luminaire**



**BWC120 amenity-lighting luminaire with photocell**



**BWC120 amenity-lighting luminaire**



**BWC120 amenity-lighting luminaire with photocell**

**Approval and Application**

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Philips standard surge protection level kV

**Controls and Dimming**

Dimmable	No
----------	----

**General Information**

Luminaire light beam spread	180°
Cap-Base	-
CE mark	CE mark
Light source colour	830 warm white
Optical cover/lens type	OB
Driver included	Yes
Flammability mark	F
Glow-wire test	Temperature 650 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1
Optic type	-

**Initial Performance (IEC Compliant)**

Init. Corr. Colour Temperature	3000 K
Init. Colour Rendering Index	80

**Light Technical**

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0.08

**General Information**

Order Code	Full Product Name	Lamp family code	Product Family Code
85189999	BWC110 LED9-/830 PSU II WH	LED9	BWC110
85190599	BWC110 LED9-/830 PSU II WH PH	LED9	BWC110
85191299	BWC110 LED9-/830 PSU II BK	LED9	BWC110
85192999	BWC110 LED9-/830 PSU II BK PH	LED9	BWC110
85193699	BWC120 LED18-/830 PSU II WH	LED18	BWC120
85194399	BWC120 LED18-/830 PSU II WH PH	LED18	BWC120
85195099	BWC120 LED18-/830 PSU II BK	LED18	BWC120
85196799	BWC120 LED18-/830 PSU II BK PH	LED18	BWC120

**Initial Performance (IEC Compliant)**

Order Code	Full Product Name	Initial luminous flux
85189999	BWC110 LED9-/830 PSU II WH	668 lm
85190599	BWC110 LED9-/830 PSU II WH PH	668 lm
85191299	BWC110 LED9-/830 PSU II BK	668 lm
85192999	BWC110 LED9-/830 PSU II BK PH	668 lm

Order Code	Full Product Name	Initial luminous flux
85193699	BWC120 LED18-/830 PSU II WH	1336 lm
85194399	BWC120 LED18-/830 PSU II WH PH	1336 lm
85195099	BWC120 LED18-/830 PSU II BK	1336 lm
85196799	BWC120 LED18-/830 PSU II BK PH	1336 lm

**Mechanical and Housing**

Order Code	Full Product Name	Colour
85189999	BWC110 LED9-/830 PSU II WH	White
85190599	BWC110 LED9-/830 PSU II WH PH	White
85191299	BWC110 LED9-/830 PSU II BK	Black
85192999	BWC110 LED9-/830 PSU II BK PH	Black

Order Code	Full Product Name	Colour
85193699	BWC120 LED18-/830 PSU II WH	White
85194399	BWC120 LED18-/830 PSU II WH PH	White
85195099	BWC120 LED18-/830 PSU II BK	Black
85196799	BWC120 LED18-/830 PSU II BK PH	Black

