



產品說明

MASTER PL-L 4 Pin 4-針腳型

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 2 個平行螢光燈管

优点

- 每次開燈，無論時間長短，都能展現最佳的照明狀態
- 使用壽命長，光量輸出不衰減

特点

- 4 接腳基座，無點燈器和電容
- 燈管特性取決於操作條件與採用何種控制裝置
- 燈管效能取決於燈泡最低點溫度
- 可調光

应用


- 適用於店面、辦公室、飯店和特殊目的的照明需求，以及住宅區戶外空間和公園等處

安全提示


- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-L 4 Pin 4-針腳型

Versions



二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/865/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm
MASTER PL-L 36W/840/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm
MASTER PL-L 36W/865/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm
MASTER PL-L 36W/865/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm
MASTER PL-L 55W/865/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

一般資訊	
燈座基底	2G11
控制與調光	
可調光	是
認證與應用	
汞 (Hg) 含量 (標稱)	2.0 mg

一般資訊

Order Code	Full Product Name	標稱使用壽命
927903086572	MASTER PL-L 18W/865/4P 1CT/25	-
927903408472	MASTER PL-L 36W/840/4P 1CT/25	15,000 h
927903486570	MASTER PL-L 36W/865/4P 1CT/25	-

Order Code	Full Product Name	標稱使用壽命
927903486572	MASTER PL-L 36W/865/4P 1CT/25	15,000 h
927908786572	MASTER PL-L 55W/865/4P 1CT/25	15,000 h

照明技術

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	色彩名稱	相關色彩溫度 (規範)	演色性指數 (CRI)	光效 (額定) (標準)	光通量
927903086572	MASTER PL-L 18W/865/4P 1CT/25	0.313	0.337	冷日光色	6500 K	80	65 lm/W	1,170 lm
927903408472	MASTER PL-L 36W/840/4P 1CT/25	-	-	冷白光 (CW)	4100 K	82	81 lm/W	2,900 lm
927903486570	MASTER PL-L 36W/865/4P 1CT/25	0.313	0.337	冷日光色	6500 K	80	80 lm/W	2,800 lm
927903486572	MASTER PL-L 36W/865/4P 1CT/25	-	-	冷日光色	6500 K	80	80 lm/W	2,900 lm

MASTER PL-L 4 Pin 4-針腳型

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	色彩名稱	相關色彩溫度 (規範)	演色性指數 (CRI)	光效 (額定) (標準)	光通量
927908786572	MASTER PL-L 55W/865/4P 1CT/25	-	-	冷日光色	6500 K	80	82 lm/W	4,600 lm

運轉與電力

Order Code	Full Product Name	燈具電流 (標稱)	耗電量
927903086572	MASTER PL-L 18W/865/4P 1CT/25	0.375 A	18.0 W
927903408472	MASTER PL-L 36W/840/4P 1CT/25	0.435 A	36.0 W
927903486570	MASTER PL-L 36W/865/4P 1CT/25	0.435 A	36.3 W

Order Code	Full Product Name	燈具電流 (標稱)	耗電量
927903486572	MASTER PL-L 36W/865/4P 1CT/25	0.435 A	36 W
927908786572	MASTER PL-L 55W/865/4P 1CT/25	0.525 A	55.0 W

認證與應用

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (最大)
927903086572	MASTER PL-L 18W/865/4P 1CT/25	18 kWh	2 mg
927903408472	MASTER PL-L 36W/840/4P 1CT/25	40 kWh	-
927903486570	MASTER PL-L 36W/865/4P 1CT/25	37 kWh	2 mg

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (最大)
927903486572	MASTER PL-L 36W/865/4P 1CT/25	40 kWh	-
927908786572	MASTER PL-L 55W/865/4P 1CT/25	61 kWh	-

