



Product Description

MASTER PL-L 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Lamp performance is governed by temperature of the coolest spot
- Dimming is possible

Application

- Designed for general lighting in shops, offices, hotels and specific task lighting, as well as outdoors in residential areas and parks

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-L 4 Pin

Versions



LPPR PLL4P 18W




LPPR PLL4P 40W



LPPR PLL4P 55W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/865/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm
MASTER PL-L 40W/830/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm
MASTER PL-L 55W/840/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

General Information	
Cap base	2G11
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) content (max.)	2 mg
Mercury (Hg) content (nom.)	2.0 mg

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Colour designation	Correlated Colour	Colour	Luminous efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)		Temperature	rendering index (CRI)		
63514340	MASTER PL-L 18W/865/4P 1CT/25	0.313	0.337	Cool Daylight	6500 K	80	65 lm/W	1,170 lm
61094240	MASTER PL-L 40W/830/4P 1CT/25	0.44	0.403	Warm White (WW)	3000 K	82	88 lm/W	3,500 lm
61542840	MASTER PL-L 55W/840/4P 1CT/25	0.38	0.38	Cool White (CW)	4000 K	80	87 lm/W	4,700 lm

Operating and Electrical

MASTER PL-L 4 Pin

Order Code	Full Product Name	Lamp current	Power Consumption
		(nom.)	
63514340	MASTER PL-L 18W/865/4P 1CT/25	0.375 A	18.0 W
61094240	MASTER PL-L 40W/830/4P 1CT/25	0.320 A	40.0 W

Order Code	Full Product Name	Lamp current	Power Consumption
		(nom.)	
61542840	MASTER PL-L 55W/840/4P 1CT/25	0.525 A	55.3 W

Approval and Application

Order Code	Full Product Name	Energy consumption kWh/1,000
		hours
63514340	MASTER PL-L 18W/865/4P 1CT/25	18 kWh
61094240	MASTER PL-L 40W/830/4P 1CT/25	40 kWh

Order Code	Full Product Name	Energy consumption kWh/1,000
		hours
61542840	MASTER PL-L 55W/840/4P 1CT/25	56 kWh

