

# **Product Description**

### **MASTER PL-L 4 Pin**

Energy-saving compact fluorescent lampsCompact long-arc low-pressure mercury discharge lampEnvelope consists of 2 parallel fluorescent tubes

#### Renefite

- · Optimal light performance for short or long operation per switch on
- $\boldsymbol{\cdot}$  Long life and sustainable light output

#### **Features**

- · 4-pin base without starter and capacitor
- · Lamp characteristics are influenced by operating conditions and control gear used
- · Lamp performance is governed by temperature of the coolest spot
- · Dimming is possible

### **Application**


• Designed for general lighting in shops, offices, hotels and specific task lighting, as well as outdoors in residential areas and parks

#### **Warnings and Safety**


- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- · Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# **MASTER PL-L 4 Pin**

#### Versions



# Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 24W/827/4P	39.0 mm	18.0 mm	289.2 mm	315 mm	321.6 mm
1CT/25					



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.