



The original!

MASTER PL-S 4 Pin

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

Application


- Designed for use in hotels, restaurants, theatres and homes
- Suitable for use in signs, corridors, security and orientation lighting

Warnings and Safety


- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-S 4 Pin


Versions




5W, 2G7, 4P



7W, 2G7, 4P




9W, 2G7, 4P



11W, 2G7, 4P

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 11W/840/4P 1CT/10	28 mm	13 mm	196 mm	214 mm	219.9 mm
MASTER PL-S 11W/840/4P 1CT/5X10BOX	28 mm	13 mm	196 mm	214 mm	219.9 mm
MASTER PL-S 11W/830/4P 1CT/5X10BOX	28 mm	13 mm	196 mm	214 mm	219.9 mm
MASTER PL-S 11W/827/4P 1CT/5X10BOX	28 mm	13 mm	196 mm	214 mm	219.9 mm
MASTER PL-S 9W/840/4P 1CT/5X10BOX	28 mm	13 mm	128 mm	145 mm	151.1 mm
MASTER PL-S 5W/827/4P 1CT/ 5X10BOX	28 mm	13 mm	66 mm	83 mm	89.1 mm
MASTER PL-S 9W/827/4P 1CT/ 5X10BOX	28 mm	13 mm	128 mm	145 mm	151.1 mm
MASTER PL-S 7W/840/4P 1CT/ 5X10BOX	28 mm	13 mm	96 mm	113 mm	119.1 mm
MASTER PL-S 7W/830/4P 1CT/ 5X10BOX	28 mm	13 mm	96 mm	113 mm	119.1 mm
MASTER PL-S 5W/840/4P 1CT/5X10BOX	28 mm	13 mm	66 mm	83 mm	89.1 mm
MASTER PL-S 9W/830/4P 1CT/5X10BOX	28 mm	13 mm	128 mm	145 mm	151.1 mm

MASTER PL-S 4 Pin

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg

Controls and Dimming

Dimmable	Yes
----------	-----

General Information

Cap-Base	2G7
Life To 50% Failures Preheat (Nom)	13000 h
LSF Preheat 16000 h Rated	30 %
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	92 %

Light Technical

LLMF 12000 h Rated	86 %
LLMF 2000 h Rated	95 %
LLMF 4000 h Rated	92 %
LLMF 6000 h Rated	90 %
LLMF 8000 h Rated	88 %

Temperature

Design Temperature (Nom)	28 °C
--------------------------	-------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927935482711	MASTER PL-S 5W/827/4P 1CT/5X10BOX	6 kWh
927935484011	MASTER PL-S 5W/840/4P 1CT/5X10BOX	6 kWh
927935883011	MASTER PL-S 7W/830/4P 1CT/5X10BOX	8 kWh
927935884011	MASTER PL-S 7W/840/4P 1CT/5X10BOX	8 kWh
927936282711	MASTER PL-S 9W/827/4P 1CT/5X10BOX	9 kWh
927936283011	MASTER PL-S 9W/830/4P 1CT/5X10BOX	9 kWh
927936284011	MASTER PL-S 9W/840/4P 1CT/5X10BOX	9 kWh
927936682711	MASTER PL-S 11W/827/4P 1CT/5X10BOX	13 kWh
927936683011	MASTER PL-S 11W/830/4P 1CT/5X10BOX	13 kWh
927936684011	MASTER PL-S 11W/840/4P 1CT/5X10BOX	13 kWh
927936684065	MASTER PL-S 11W/840/4P 1CT/10	13 kWh

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927935482711	MASTER PL-S 5W/827/4P 1CT/5X10BOX	0.180 A	5.4 W
927935484011	MASTER PL-S 5W/840/4P 1CT/5X10BOX	0.180 A	5.4 W
927935883011	MASTER PL-S 7W/830/4P 1CT/5X10BOX	0.175 A	7.1 W
927935884011	MASTER PL-S 7W/840/4P 1CT/5X10BOX	0.175 A	7.1 W
927936282711	MASTER PL-S 9W/827/4P 1CT/5X10BOX	0.170 A	8.6 W
927936283011	MASTER PL-S 9W/830/4P 1CT/5X10BOX	0.170 A	8.6 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927936284011	MASTER PL-S 9W/840/4P 1CT/5X10BOX	0.170 A	8.6 W
927936682711	MASTER PL-S 11W/827/4P 1CT/5X10BOX	0.160 A	11.6 W
927936683011	MASTER PL-S 11W/830/4P 1CT/5X10BOX	0.160 A	11.6 W
927936684011	MASTER PL-S 11W/840/4P 1CT/5X10BOX	0.160 A	11.6 W
927936684065	MASTER PL-S 11W/840/4P 1CT/10	0.160 A	11.6 W

Light Technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927935482711	MASTER PL-S 5W/827/4P 1CT/5X10BOX	827	Incandescent White	2700 K	82

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927935484011	MASTER PL-S 5W/840/4P 1CT/5X10BOX	840	Cool White (CW)	4000 K	80

MASTER PL-S 4 Pin

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927935883011	MASTER PL-S 7W/830/4P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82
927935884011	MASTER PL-S 7W/840/4P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82
927936282711	MASTER PL-S 9W/827/4P 1CT/5X10BOX	827	Incandescent White	2700 K	82
927936283011	MASTER PL-S 9W/830/4P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82
927936284011	MASTER PL-S 9W/840/4P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927936682711	MASTER PL-S 11W/827/4P 1CT/5X10BOX	827	Incandescent White	2700 K	82
927936683011	MASTER PL-S 11W/830/4P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82
927936684011	MASTER PL-S 11W/840/4P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82
927936684065	MASTER PL-S 11W/840/4P 1CT/10	840	Cool White (CW)	4000 K	82

Light Technical (2/2)

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
927935482711	MASTER PL-S 5W/827/4P 1CT/5X10BOX	52 lm/W	250 lm	259 lm
927935484011	MASTER PL-S 5W/840/4P 1CT/5X10BOX	52 lm/W	250 lm	259 lm
927935883011	MASTER PL-S 7W/830/4P 1CT/5X10BOX	62 lm/W	400 lm	405 lm
927935884011	MASTER PL-S 7W/840/4P 1CT/5X10BOX	62 lm/W	400 lm	405 lm
927936282711	MASTER PL-S 9W/827/4P 1CT/5X10BOX	73 lm/W	600 lm	583 lm
927936283011	MASTER PL-S 9W/830/4P 1CT/5X10BOX	73 lm/W	600 lm	583 lm

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
927936284011	MASTER PL-S 9W/840/4P 1CT/5X10BOX	73 lm/W	600 lm	583 lm
927936682711	MASTER PL-S 11W/827/4P 1CT/5X10BOX	80 lm/W	900 lm	880 lm
927936683011	MASTER PL-S 11W/830/4P 1CT/5X10BOX	82 lm/W	900 lm	900 lm
927936684011	MASTER PL-S 11W/840/4P 1CT/5X10BOX	82 lm/W	900 lm	900 lm
927936684065	MASTER PL-S 11W/840/4P 1CT/10	82 lm/W	900 lm	900 lm

