



產品說明

MASTER PL-C 2 Pin 2-針腳型

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 4 個平行細長螢光燈管

优点

- 每次開燈，無論時間長短，都能展現最佳的照明狀態
- 使用壽命長，光量輸出不衰減

特点

- 2 接腳底座，內建立即式點燈器和電容
- 燈管特性取決於操作條件與採用何種控制裝置
- 無法調光

应用

- 適用於專業或居家環境的一般或輔助照明
- 嵌入式或吸頂式嵌燈、壁燈、桌燈和吊燈

安全提示

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 2 Pin 2-針腳型

Versions




LPPR PLC2P 13W



LPPR PLC2P 18W

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 18W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 26W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

控制與調光	
可調光	否
認證與應用	
汞 (Hg) 含量 (標稱)	1.4 mg

一般資訊

Order Code	Full Product Name	燈座基底
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	G24d-1
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	G24d-2
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	G24d-2
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	G24d-3

Order Code	Full Product Name	燈座基底
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	G24d-3
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	G24d-3
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	G24d-3

照明技術

Order Code	Full Product Name	色彩名稱	相關色彩溫度 (規範)	演色性指數 (CRI)	光效 (額定) (標準)	光通量
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	冷白光 (CW)	4000 K	82	69 lm/W	925 lm

MASTER PL-C 2 Pin 2-針腳型

Order Code	Full Product Name	色彩名稱	相關色彩溫度 (規範)	演色性指數 (CRI)	光效 (額定) (標準)	光通量
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	白熾白色	2700 K	82	67 lm/W	1,200 lm
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	冷白光 (CW)	4000 K	82	67 lm/W	1,200 lm
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	白熾白色	2700 K	82	68 lm/W	1,800 lm
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	暖白光 (WW)	3000 K	82	68 lm/W	1,800 lm
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	冷白光 (CW)	4000 K	82	68 lm/W	1,800 lm
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	冷日光色	6500 K	80	66 lm/W	1,740 lm

運轉與電力

Order Code	Full Product Name	燈具電流 (標稱)	耗電量	Order Code	Full Product Name	燈具電流 (標稱)	耗電量
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	0.170 A	13.4 W	927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	0.335 A	26.5 W
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	0.230 A	17.9 W	927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	0.335 A	26.5 W
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	0.230 A	17.9 W	927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.335 A	26.5 W
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	0.335 A	26.5 W				

認證與應用

Order Code	Full Product Name	能源消耗 kWh/1000 h	Order Code	Full Product Name	能源消耗 kWh/1000 h
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	17 kWh	927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	32 kWh
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	22 kWh	927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	32 kWh
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	22 kWh	927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	32 kWh
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	32 kWh			

