



# 10-15% more efficient!

## MASTER PL-C 2 Pin

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Benefits

### Features

### Application

### Warnings and Safety

### Versions



10W, G24d-1, 2P



13W, G24d-1, 2P




18W, G24d-2, 2P



26W, G24d-3, 2P

# MASTER PL-C 2 Pin

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 10W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 10W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 10W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/ 840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/ 840/2P 1CT/5X10CC	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/ 840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/ 830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/ 830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/827/2P 1CT/5X10CC	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 18W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/840/2P 1CT/5X10CC	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/ 830 /2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC	27.1 mm	27.1 mm	80.7 mm	99.0 mm	121.6 mm

# MASTER PL-C 2 Pin

## Dimensional drawing

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 10W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 10W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm

### Approval and Application

**Mercury (Hg) Content (Nom)** 1.4 mg

### Controls and Dimming

**Dimmable** No

### General Information

**Life To 10% Failures (Nom)** 6500 h

**Life To 50% Failures (Nom)** 10000 h

**LSF 2000 h Rated** 99 %

**LSF 4000 h Rated** 98 %

**LSF 6000 h Rated** 92 %

**LSF 8000 h Rated** 78 %

### Temperature

**Design Temperature (Nom)** 28 °C

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	13 kWh	B
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	13 kWh	B
927903883040	MASTER PL-C 10W/830/2P 1CT/5X10BOX	13 kWh	B
927903884002	MASTER PL-C 10W/840/2P 1CT/5X10BOX	13 kWh	B
927903884040	MASTER PL-C 10W/840/2P 1CT/5X10BOX	13 kWh	B
927903886502	MASTER PL-C 10W/865/2P 1CT/5X10BOX	13 kWh	B
927904882701	MASTER PL-C 13W/827/2P 1CT/5X10BOX	17 kWh	A
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	17 kWh	A
927904883001	MASTER PL-C 13W/830/2P 1CT/5X10BOX	17 kWh	A
927904883040	MASTER PL-C 13W/830/2P 1CT/5X10BOX	17 kWh	A
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	17 kWh	A
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	17 kWh	A
927904886502	MASTER PL-C 13W/865/2P 1CT/5X10BOX	17 kWh	B
927904886540	MASTER PL-C 13W/865/2P 1CT/5X10BOX	17 kWh	B
927904982762	MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC	-	A
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	22 kWh	B
927905782740	MASTER PL-C 18W/827/2P 1CT/5X10BOX	22 kWh	B
927905783001	MASTER PL-C 18W/830/2P 1CT/5X10BOX	22 kWh	B
927905783040	MASTER PL-C 18W/830 /2P 1CT/5X10BOX	22 kWh	B
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	22 kWh	B
927905784003	MASTER PL-C 18W/840/2P 1CT/5X10CC	22 kWh	B
927905784040	MASTER PL-C 18W/840/2P 1CT/5X10BOX	22 kWh	B
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	22 kWh	B

## MASTER PL-C 2 Pin

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
927905786540	MASTER PL-C 18W/865/2P 1CT/5X10BOX	22 kWh	B
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	32 kWh	B
927906182703	MASTER PL-C 26W/827/2P 1CT/5X10CC	32 kWh	B
927906182740	MASTER PL-C 26W/827/2P 1CT/5X10BOX	32 kWh	B
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	32 kWh	B
927906183040	MASTER PL-C 26W/830/2P 1CT/5X10BOX	32 kWh	B
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	32 kWh	B
927906184003	MASTER PL-C 26W/840/2P 1CT/5X10CC	32 kWh	B
927906184040	MASTER PL-C 26W/840/2P 1CT/5X10BOX	32 kWh	B
927906186502	MASTER PL-C 26W/865/2P 1CT/5X10BOX	32 kWh	B
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	32 kWh	B
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	32 kWh	B

### Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)	Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927903882701	MASTER PL-C 10W/827/2P 1CT/ 5X10BOX	0.190 A	10.0 W	927905782740	MASTER PL-C 18W/827/2P 1CT/ 5X10BOX	0.230 A	17.9 W
927903882740	MASTER PL-C 10W/827/2P 1CT/ 5X10BOX	0.190 A	10.0 W	927905783001	MASTER PL-C 18W/830/2P 1CT/ 5X10BOX	0.230 A	17.9 W
927903883040	MASTER PL-C 10W/830/2P 1CT/ 5X10BOX	0.190 A	10.0 W	927905783040	MASTER PL-C 18W/830 /2P 1CT/ 5X10BOX	0.230 A	17.9 W
927903884002	MASTER PL-C 10W/840/2P 1CT/ 5X10BOX	0.190 A	10.0 W	927905784001	MASTER PL-C 18W/840/2P 1CT/ 5X10BOX	0.230 A	17.9 W
927903884040	MASTER PL-C 10W/840/2P 1CT/ 5X10BOX	0.190 A	10.0 W	927905784003	MASTER PL-C 18W/840/2P 1CT/ 5X10CC	0.230 A	17.9 W
927903886502	MASTER PL-C 10W/865/2P 1CT/ 5X10BOX	0.190 A	10.0 W	927905784040	MASTER PL-C 18W/840/2P 1CT/ 5X10BOX	0.230 A	17.9 W
927904882701	MASTER PL-C 13W/827/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927905786502	MASTER PL-C 18W/865/2P 1CT/ 5X10BOX	0.230 A	17.9 W
927904882740	MASTER PL-C 13W/827/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927905786540	MASTER PL-C 18W/865/2P 1CT/ 5X10BOX	0.230 A	17.9 W
927904883001	MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927906182701	MASTER PL-C 26W/827/2P 1CT/ 5X10BOX	0.335 A	26.5 W
927904883040	MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927906182703	MASTER PL-C 26W/827/2P 1CT/ 5X10CC	0.335 A	26.5 W
927904884002	MASTER PL-C 13W/840/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927906182740	MASTER PL-C 26W/827/2P 1CT/ 5X10BOX	0.335 A	26.5 W
927904884040	MASTER PL-C 13W/840/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927906183001	MASTER PL-C 26W/830/2P 1CT/ 5X10BOX	0.335 A	26.5 W
927904886502	MASTER PL-C 13W/865/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927906183040	MASTER PL-C 26W/830/2P 1CT/ 5X10BOX	0.335 A	26.5 W
927904886540	MASTER PL-C 13W/865/2P 1CT/ 5X10BOX	0.170 A	13.4 W	927906184001	MASTER PL-C 26W/840/2P 1CT/ 5X10BOX	0.335 A	26.5 W
927904982762	MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC	0.285 A	12.7 W	927906184003	MASTER PL-C 26W/840/2P 1CT/ 5X10CC	0.335 A	26.5 W
927905782701	MASTER PL-C 18W/827/2P 1CT/ 5X10BOX	0.230 A	17.9 W	927906184040	MASTER PL-C 26W/840/2P 1CT/ 5X10BOX	0.335 A	26.5 W

## MASTER PL-C 2 Pin

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927906186502	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.335 A	26.5 W
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.335 A	26.5 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.335 A	26.5 W

### General Information

Order Code	Full Product Name	Cap-Base
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	G24D-1
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	G24D-1
927903883040	MASTER PL-C 10W/830/2P 1CT/5X10BOX	G24D-1
927903884002	MASTER PL-C 10W/840/2P 1CT/5X10BOX	G24D-1
927903884040	MASTER PL-C 10W/840/2P 1CT/5X10BOX	G24D-1
927903886502	MASTER PL-C 10W/865/2P 1CT/5X10BOX	G24D-1
927904882701	MASTER PL-C 13W/827/2P 1CT/5X10BOX	G24D-1
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	G24D-1
927904883001	MASTER PL-C 13W/830/2P 1CT/5X10BOX	G24D-1
927904883040	MASTER PL-C 13W/830/2P 1CT/5X10BOX	G24D-1
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	G24D-1
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	G24D-1
927904886502	MASTER PL-C 13W/865/2P 1CT/5X10BOX	G24D-1
927904886540	MASTER PL-C 13W/865/2P 1CT/5X10BOX	G24D-1
927904982762	MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC	GX23-2
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	G24D-2
927905782740	MASTER PL-C 18W/827/2P 1CT/5X10BOX	G24D-2
927905783001	MASTER PL-C 18W/830/2P 1CT/5X10BOX	G24D-2

Order Code	Full Product Name	Cap-Base
927905783040	MASTER PL-C 18W/830 /2P 1CT/5X10BOX	G24D-2
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	G24D-2
927905784003	MASTER PL-C 18W/840/2P 1CT/5X10CC	G24D-2
927905784040	MASTER PL-C 18W/840/2P 1CT/5X10BOX	G24D-2
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	G24D-2
927905786540	MASTER PL-C 18W/865/2P 1CT/5X10BOX	G24D-2
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	G24D-3
927906182703	MASTER PL-C 26W/827/2P 1CT/5X10CC	G24D-3
927906182740	MASTER PL-C 26W/827/2P 1CT/5X10BOX	G24D-3
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	G24D-3
927906183040	MASTER PL-C 26W/830/2P 1CT/5X10BOX	G24D-3
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	G24D-3
927906184003	MASTER PL-C 26W/840/2P 1CT/5X10CC	G24D-3
927906184040	MASTER PL-C 26W/840/2P 1CT/5X10BOX	G24D-3
927906186502	MASTER PL-C 26W/865/2P 1CT/5X10BOX	G24D-3
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	G24D-3
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	G24D-3

### Light Technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	>80
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	>80
927903883040	MASTER PL-C 10W/830/2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	>80
927903884002	MASTER PL-C 10W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82
927903884040	MASTER PL-C 10W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927903886502	MASTER PL-C 10W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	82
927904882701	MASTER PL-C 13W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	83
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	83
927904883001	MASTER PL-C 13W/830/2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82
927904883040	MASTER PL-C 13W/830/2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82

## MASTER PL-C 2 Pin

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
927904884002	MASTER PL-C 13W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82	927905786540	MASTER PL-C 18W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	82
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82	927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	82
927904886502	MASTER PL-C 13W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	80	927906182703	MASTER PL-C 26W/827/2P 1CT/5X10CC	827	Incandescent White	2700 K	82
927904886540	MASTER PL-C 13W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	80	927906182740	MASTER PL-C 26W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	82
927904982762	MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC	827	Incandescent White	2700 K	82	927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82
927905782701	MASTER PL-C 18W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	82	927906183040	MASTER PL-C 26W/830/2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82
927905782740	MASTER PL-C 18W/827/2P 1CT/5X10BOX	827	Incandescent White	2700 K	82	927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82
927905783001	MASTER PL-C 18W/830/2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82	927906184003	MASTER PL-C 26W/840/2P 1CT/5X10CC	840	Cool White (CW)	4100 K	82
927905783040	MASTER PL-C 18W/830 /2P 1CT/5X10BOX	830	Warm White (WW)	3000 K	82	927906184040	MASTER PL-C 26W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82	927906186502	MASTER PL-C 26W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	80
927905784003	MASTER PL-C 18W/840/2P 1CT/5X10CC	840	Cool White (CW)	4000 K	82	927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	80
927905784040	MASTER PL-C 18W/840/2P 1CT/5X10BOX	840	Cool White (CW)	4000 K	82	927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	80
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	865	Cool Daylight	6500 K	82						

### Light Technical (2/2)

Order Code	Full Product Name	LLMF 2000 h Rated	LLMF 4000 h Rated	LLMF 6000 h Rated	LLMF 8000 h Rated	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	92 %	87 %	83 %	81 %	60 lm/W	600 lm	600 lm
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	92 %	87 %	83 %	81 %	60 lm/W	600 lm	600 lm

## MASTER PL-C 2 Pin

Order Code	Full Product Name	LLMF 2000 h	LLMF 4000 h	LLMF 6000 h	LLMF 8000 h	Luminous Efficacy	Luminous Flux	Luminous Flux
		Rated	Rated	Rated	Rated	(rated) (Nom)	(Nom)	(Rated) (Nom)
927903883040	MASTER PL-C 10W/830/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	60 lm/W	600 lm	600 lm
927903884002	MASTER PL-C 10W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	60 lm/W	600 lm	600 lm
927903884040	MASTER PL-C 10W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	60 lm/W	600 lm	600 lm
927903886502	MASTER PL-C 10W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	56 lm/W	600 lm	600 lm
927904882701	MASTER PL-C 13W/827/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	69 lm/W	925 lm	925 lm
927904882740	MASTER PL-C 13W/827/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	69 lm/W	925 lm	925 lm
927904883001	MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	69 lm/W	925 lm	925 lm
927904883040	MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	69 lm/W	925 lm	925 lm
927904884002	MASTER PL-C 13W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	69 lm/W	925 lm	925 lm
927904884040	MASTER PL-C 13W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	69 lm/W	925 lm	925 lm
927904886502	MASTER PL-C 13W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	63 lm/W	845 lm	845 lm
927904886540	MASTER PL-C 13W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	63 lm/W	845 lm	845 lm
927904982762	MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC	92 %	87 %	84 %	81 %	62 lm/W	800 lm	800 lm
927905782701	MASTER PL-C 18W/827/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905782740	MASTER PL-C 18W/827/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905783001	MASTER PL-C 18W/830/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905783040	MASTER PL-C 18W/830 /2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905784001	MASTER PL-C 18W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905784003	MASTER PL-C 18W/840/2P 1CT/ 5X10CC	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905784040	MASTER PL-C 18W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	67 lm/W	1200 lm	1200 lm
927905786502	MASTER PL-C 18W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	67 lm/W	1200 lm	1120 lm
927905786540	MASTER PL-C 18W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	67 lm/W	1200 lm	1120 lm
927906182701	MASTER PL-C 26W/827/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906182703	MASTER PL-C 26W/827/2P 1CT/ 5X10CC	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906182740	MASTER PL-C 26W/827/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm

## MASTER PL-C 2 Pin

Order Code	Full Product Name	LLMF 2000 h Rated	LLMF 4000 h Rated	LLMF 6000 h Rated	LLMF 8000 h Rated	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
927906183001	MASTER PL-C 26W/830/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906183040	MASTER PL-C 26W/830/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906184001	MASTER PL-C 26W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906184003	MASTER PL-C 26W/840/2P 1CT/ 5X10CC	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906184040	MASTER PL-C 26W/840/2P 1CT/ 5X10BOX	92 %	87 %	83 %	81 %	68 lm/W	1800 lm	1800 lm
927906186502	MASTER PL-C 26W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	66 lm/W	1740 lm	1740 lm
927906186540	MASTER PL-C 26W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	66 lm/W	1740 lm	1740 lm
927906186565	MASTER PL-C 26W/865/2P 1CT/ 5X10BOX	90 %	85 %	81 %	77 %	66 lm/W	1740 lm	1740 lm

