



Product Description

MASTER PL-C 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is possible

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER PL-C 4 Pin

Versions



LPPR PLC4P 26W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	109.9 mm
MASTER PL-C 10W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	109.9 mm
MASTER PL-C 13W/827/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 18W/827/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 18W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 18W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 26W/827/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 26W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 26W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg

General Information

MASTER PL-C 4 Pin

Order Code	Full Product Name	Cap-Base
62329470	MASTER PL-C 10W/830/4P 1CT/5X10BOX	G24q-1
62330070	MASTER PL-C 10W/840/4P 1CT/5X10BOX	G24q-1
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	G24q-1
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	G24q-1
62332470	MASTER PL-C 13W/840/4P 1CT/5X10BOX	G24q-1
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	G24q-2

Order Code	Full Product Name	Cap-Base
62333170	MASTER PL-C 18W/830/4P 1CT/5X10BOX.	G24q-2
62334870	MASTER PL-C 18W/840/4P 1CT/5X10BOX	G24q-2
62328770	MASTER PL-C 26W/827/4P 1CT/5X10BOX	G24q-3
62335570	MASTER PL-C 26W/830/4P 1CT/5X10BOX	G24q-3
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	G24q-3

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color	Color	Luminous Efficacy	Luminous Flux
		Coordinate X	Coordinate Y		Temperature (Nom)	rendering		
		(Nom)	(Nom)			index (CRI)	(rated) (Nom)	
62329470	MASTER PL-C 10W/830/4P 1CT/5X10BOX	0.44	0.403	Warm White (WW)	3000 K	82	60 lm/W	600 lm
62330070	MASTER PL-C 10W/840/4P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	80	60 lm/W	600 lm
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	82	69 lm/W	925 lm
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	0.44	0.403	Warm White (WW)	3000 K	82	72 lm/W	925 lm
62332470	MASTER PL-C 13W/840/4P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	80	69 lm/W	925 lm
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	82	67 lm/W	1,200 lm
62333170	MASTER PL-C 18W/830/4P 1CT/5X10BOX.	0.44	0.403	Warm White (WW)	3000 K	82	67 lm/W	1,200 lm
62334870	MASTER PL-C 18W/840/4P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	80	67 lm/W	1,200 lm
62328770	MASTER PL-C 26W/827/4P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	81	67 lm/W	1,800 lm
62335570	MASTER PL-C 26W/830/4P 1CT/5X10BOX	0.44	0.403	Warm White (WW)	3000 K	81	67 lm/W	1,800 lm
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	80	67 lm/W	1,800 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
62329470	MASTER PL-C 10W/830/4P 1CT/5X10BOX	0.190 A	10.4 W
62330070	MASTER PL-C 10W/840/4P 1CT/5X10BOX	0.190 A	10.4 W
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	0.170 A	13.8 W
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	0.170 A	13.8 W
62332470	MASTER PL-C 13W/840/4P 1CT/5X10BOX	0.170 A	13.8 W
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	0.230 A	18.4 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
62333170	MASTER PL-C 18W/830/4P 1CT/5X10BOX.	0.230 A	18.4 W
62334870	MASTER PL-C 18W/840/4P 1CT/5X10BOX	0.230 A	18.4 W
62328770	MASTER PL-C 26W/827/4P 1CT/5X10BOX	0.335 A	27.4 W
62335570	MASTER PL-C 26W/830/4P 1CT/5X10BOX	0.335 A	27.4 W
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	0.335 A	27.4 W

MASTER PL-C 4 Pin

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
62329470	MASTER PL-C 10W/830/4P 1CT/5X10BOX	11 kWh
62330070	MASTER PL-C 10W/840/4P 1CT/5X10BOX	11 kWh
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	14 kWh
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	14 kWh
62332470	MASTER PL-C 13W/840/4P 1CT/5X10BOX	14 kWh
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	19 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
62333170	MASTER PL-C 18W/830/4P 1CT/5X10BOX	19 kWh
62334870	MASTER PL-C 18W/840/4P 1CT/5X10BOX	19 kWh
62328770	MASTER PL-C 26W/827/4P 1CT/5X10BOX	28 kWh
62335570	MASTER PL-C 26W/830/4P 1CT/5X10BOX	28 kWh
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	28 kWh

