



Product Description

MASTER PL-T TOP 4 Pin

Energy saving compact fluorescent lamp
Compact long-arc low-pressure mercury discharge lamp
Envelope consists of 6 parallel narrow fluorescent tubes
Amalgam controlled operation

Benefits

- Optimal lighting performance for long periods of continuous operation
- Substantially higher light output (+30%) per light point than conventional solutions
- High temperature independency at higher application temperatures
- Long life and sustainable light output

Features

- 4-pin base without glow switch starter and capacitor
- Hot restrike - moderate light run up after cooling down at low temperatures
- Optimized lighting performance over a broad temperature range due to Philips amalgam technology
- Dimming is possible

Application


- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units
- First choice for long switching cycles and highest light output

MASTER PL-T TOP 4 Pin

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 32W/840/4P 1CT/ 5X10BOX	41 mm	98.7 mm	123.0 mm	138.7 mm

