



Energy savings without changing a ballast!

Energy Advantage CDM Lamps with AllStart Technology E-Rated

Philips Energy Advantage CDM AllStart E-rated lamps provide energy savings without compromising light quality.

Benefits

- Energy savings up to 17%*
- · Reduced maintenance and recycling costs
- · Long life: 20,000 hours rated average life
- * 145W CDM lamp with AllStart Technology compared to 175W metal halide lamp.

Features

- Excellent color rendering of CRI >80
- · Crisp white light
- \cdot Use in enclosed fixtures only
- Direct retrofit lamp to both probe and pulse start magnetic 175W ballasts (not suitable for operation on electronic ballasts)

Application

 Ideal for low-ceiling industrial, retail and distribution centers as well as outdoor applications

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)


Energy Advantage CDM Lamps with AllStart Technology E-Rated

Versions



LPPR D-CDM-AL 0001

Dimensional drawing







© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.