



Simply irresistible. Superior light quality from start to finish

MasterColor CDM-T T6

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Benefits

- Energy-efficient alternative to incandescent/halogen.
- Improved lumen maintenance over standard metal halide.
- A compact solution for retail displays.

Features

- Universal burning position.
- 81-85 CRI (color rendering index)
- Color stability over life within $\pm 200\text{K}$.
- Lamp to lamp color consistency over life.
- Lamps feature FadeBlock, an integrated UV blocking medium for reduced fading of fabrics and paintings.
- 22W, 39W, 70W and 150W versions.

Application

- Ideal for retail display lighting, general and indirect lighting, wall washing and fiberoptic systems.

MasterColor CDM-T T6

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Versions



CDM-T 70W, /830, /942 G12




CDM-T 35W /830, /842 G12



CDM-T, 150W, G12

Dimensional drawing



Product

MasterColor CDM-T 70W/830 G12 T6 CL

CDM150/T6/942 12PK

CDM150/T6/830 12PK

MasterColor CDM-T 35W/830 G12 T6 CL

MasterColor CDM-T 70W/942 G12 T6 CL

MasterColor CDM-T T6

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Re-ignition Time (Min) (Max)	15 min
------------------------------	--------

General Information

Cap-Base	G12
Life To 10% Failures (Nom)	10000 h
Life To 20% Failures (Nom)	11000 h
Life To 50% Failures (Nom)	12000 h
Life To 5% Failures (Nom)	9000 h
Operating Position	UNIVERSAL

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T19

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy	
			Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928082305115	MasterColor CDM-T 70W/830 G12 T6 CL	80 kWh	A	4.6 mg
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	80 kWh	A	6.1 mg
928083105115	MasterColor CDM-T 35W/830 G12 T6 CL	43 kWh	A	3.1 mg
928083705115	CDM150/T6/830 12PK	162 kWh	A+	14.3 mg
928084605115	CDM150/T6/942 12PK	162 kWh	A	10.4 mg

Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928082305115	MasterColor CDM-T 70W/830 G12 T6 CL	0.98 A	96 V	80 V	88 V
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	0.98 A	96 V	80 V	88 V
928083105115	MasterColor CDM-T 35W/830 G12 T6 CL	0.53 A	90 V	76 V	82 V

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928083705115	CDM150/T6/830 12PK	1.8 A	106 V	86 V	96 V
928084605115	CDM150/T6/942 12PK	1.9 A	98 V	82 V	90 V

Operating and Electrical (2/2)

Order Code	Full Product Name	Power (Rated) (Nom)
928082305115	MasterColor CDM-T 70W/830 G12 T6 CL	73 W
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	73 W
928083105115	MasterColor CDM-T 35W/830 G12 T6 CL	39 W

Order Code	Full Product Name	Power (Rated) (Nom)
928083705115	CDM150/T6/830 12PK	147 W
928084605115	CDM150/T6/942 12PK	147 W

Luminaire Design Requirements

Order Code	Full Product Name	Bulb Temperature (Max)
928082305115	MasterColor CDM-T 70W/830 G12 T6 CL	500 °C
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	500 °C
928083105115	MasterColor CDM-T 35W/830 G12 T6 CL	500 °C

Order Code	Full Product Name	Bulb Temperature (Max)
928083705115	CDM150/T6/830 12PK	650 °C
928084605115	CDM150/T6/942 12PK	650 °C

Light Technical (1/3)

Order Code	Full Product Name	Chromaticity		Color	
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Designation
928082305115	MasterColor CDM-T	0.432	0.395	830	Warm White (WW)

Order Code	Full Product Name	Chromaticity		Color	
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Designation
	70W/830 G12 T6 CL				

MasterColor CDM-T T6

Order Code	Full Product Name	Chromaticity	Chromaticity	Color	
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Designation
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	0.377	0.376	942	Cool White (CW)
928083105115	MasterColor CDM-T	0.428	0.397	830	Warm White (WW)

Order Code	Full Product Name	Chromaticity	Chromaticity	Color	
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Designation
	35W/830 G12 T6 CL				
928083705115	CDM150/T6/830 12PK	0.436	0.396	830	Warm White (WW)
928084605115	CDM150/T6/942 12PK	0.375	0.363	942	Cool White (CW)

Light Technical (2/3)


Order Code	Full Product Name	Correlated Color	Color Rendering	Lumen	Lumen	Lumen	Lumen	Lumen	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	Index (Nom)	Maintenance 10000 h (Nom)	Maintenance 2000 h (Min)	Maintenance 2000 h (Nom)	Maintenance 5000 h (Min)	Maintenance 5000 h (Nom)	(rated) (Nom)	(Rated) (Min)
928082305115	MasterColor CDM-T 70W/830 G12 T6 CL	3000 K	84	70 %	75 %	85 %	70 %	80 %	85 lm/W	5600 lm
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	4200 K	92	65 %	75 %	85 %	65 %	75 %	85 lm/W	-
928083105115	MasterColor CDM-T 35W/830 G12 T6 CL	3000 K	83	50 %	70 %	80 %	60 %	70 %	79 lm/W	-
928083705115	CDM150/T6/830 12PK	3000 K	88	60 %	65 %	75 %	60 %	70 %	88 lm/W	11700 lm
928084605115	CDM150/T6/942 12PK	4200 K	96	70 %	75 %	85 %	70 %	80 %	82 lm/W	10900 lm

Light Technical (3/3)

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
928082305115	MasterColor CDM-T 70W/830 G12 T6 CL	6200 lm
928084505115	MasterColor CDM-T 70W/942 G12 T6 CL	6200 lm
928083105115	MasterColor CDM-T 35W/830 G12 T6 CL	3100 lm

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
928083705115	CDM150/T6/830 12PK	13000 lm
928084605115	CDM150/T6/942 12PK	12100 lm


Color Rendering Diagrams




LDCR_CDM-T_150W_830-Colour rendering diagram

MasterColor CDM-T T6

Color Rendering Diagrams



LDCR_CDM-T_70W_942-Colour rendering diagram



LDCR_CDM-T_150W_942-Colour rendering diagram

