



High efficiency with a crisp, sparkling light

MasterColor CDM PAR38

Philips MasterColor® Ceramic Metal Halide PAR38 Lamps offer high-efficiency, ceramic metal halide reflector lamps with a stable color over lifetime and a crisp, sparkling light.

Benefits

- Philips MC PAR38 lamps deliver improved lumen maintenance over standard metal halide PAR lamps.
- Philips MC PAR38 lamps reduce lighting cost of ownership - they are an energy efficient alternative to incandescent or halogen PAR lamps.

Features

- Superior color stability— within $\pm 200\text{K}$.
- Lamp to lamp color consistency over life higher lumen maintenance.
- Improved lumen maintenance over standard metal halide.
- Feature ALTO lamp technology with reduced mercury.
- Operate on existing ballasts.
- Lamps feature integrated UV blocking medium for reduced fading of fabrics and paintings.
- 70 and 100 watt flood and spot, 3000, and 4000K versions

Application

- Ideal for retail accent and display lighting and architectural lighting for interior and exterior applications.

MasterColor CDM PAR38

Warnings and Safety


- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Versions



CDM PAR38 Medium Base

Dimensional drawing



Product

MasterColor CDM100/PAR38/FL/3K ALTO ELITE 12PK

MasterColor CDM70/PAR38/FL/3K ALTO ELITE 12PK

MasterColor CDM100/PAR38/FL/4K ALTO ELITE 12PK

MasterColor CDM PAR38

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Re-ignition Time (Min) (Max)	8 min
------------------------------	-------

General Information

Cap-Base	E26
Life To 50% Failures (Nom)	16000 h
Operating Position	Universal

Luminaire Design Requirements

Bulb Temperature (Max)	350 °C
------------------------	--------

Light Technical

Beam Angle (Max)	31 °
Beam Angle (Min)	19
Beam Angle (Nom)	25 °
Beam Description	Flood

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	PAR38

Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
456475	MasterColor CDM70/ PAR38/FL/3K ALTO ELITE 12PK	0.92 A	115 V	90 V	95 V
456517	MasterColor CDM100/ PAR38/FL/3K ALTO ELITE 12PK	1.1 A	110 V	85 V	90 V
456533	MasterColor CDM100/ PAR38/FL/4K ALTO ELITE 12PK	1.10 A	122 V	97 V	102 V

Operating and Electrical (2/2)

Order Code	Full Product Name	Power (Rated) (Nom)
456475	MasterColor CDM70/PAR38/FL/3K ALTO ELITE 12PK	70 W
456517	MasterColor CDM100/PAR38/FL/3K ALTO ELITE 12PK	100 W

Order Code	Full Product Name	Power (Rated) (Nom)
456533	MasterColor CDM100/PAR38/FL/4K ALTO ELITE 12PK	95.0 W

Light Technical (1/2)

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Code	Color Designation
456475	MasterColor CDM70/ PAR38/FL/3K ALTO ELITE 12PK	0.430	0.403	830	Warm White (WW)
456517	MasterColor CDM100/	0.430	0.402	830	Warm White (WW)

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Code	Color Designation
	PAR38/FL/3K ALTO ELITE 12PK				
456533	MasterColor CDM100/ PAR38/FL/4K ALTO ELITE 12PK	0.380	0.375	940	Cool White (CW)

Light Technical (2/2)

MasterColor CDM PAR38

Order Code	Full Product Name	Correlated Color	Color Rendering Index	Color Rendering Index	Luminous Flux	Luminous Intensity
		Temperature (Nom)	(Min)	(Nom)	(Rated) (Nom)	(Nom)
456475	MasterColor CDM70/ PAR38/FL/3K ALTO ELITE 12PK	3000 K	80	87	4800 lm	15000 cd
456517	MasterColor CDM100/ PAR38/FL/3K	3000 K	-	92	6800 lm	20000 cd

Order Code	Full Product Name	Correlated Color	Color Rendering Index	Color Rendering Index	Luminous Flux	Luminous Intensity
		Temperature (Nom)	(Min)	(Nom)	(Rated) (Nom)	(Nom)
	ALTO ELITE 12PK					
456533	MasterColor CDM100/ PAR38/FL/4K ALTO ELITE 12PK	4200 K	-	92	6400 lm	20000 cd

