



AspiraVision Compact (35, 50 & 70 W) for CDM – The smart electronic gear

AspiraVision Compact for CDM

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

Benefits

- SOFT START allows installation with fewer circuit breakers; Loop Through allows faster, cost-efficient installation
- Longer lifetime
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future

Features

- SOFT START
- Loop Through (in independent version)
- Improved thermal performance
- Low electromagnetic interference
- Voltage drop detection

Application

- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only





AspiraVision Compact for CDM

Versions



GPPR IAVC 0002

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|---|--------|---------|----------|----------|---------|
| HID-AV C 35-70 /I CDM 220-240V 50/60Hz | 4.8 mm | 34.7 mm | 189.2 mm | 170.7 mm | 83.5 mm |

| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|---|--------|---------|----------|---------|---------|---------|
| HID-AV C 35-70 /S CDM 220-240V 50/60Hz | 4.5 mm | 32.1 mm | 110.0 mm | 98.5 mm | 75.0 mm | 63.5 mm |



AspiraVision Compact for CDM

Operating and Electrical

| | |
|--|--------------|
| Input frequency | 50 to 60 Hz |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Number of products on MCB (16 A type B) (nom.) | 58 |

Mechanical and Housing

| Order Code | Full Product Name | Housing | Order Code | Full Product Name | Housing |
|------------|--|---------|------------|--|---------|
| 23310700 | HID-AV C 35-70 /S CDM 220-240V 50/60Hz | /S | 23312100 | HID-AV C 35-70 /I CDM 220-240V 50/60Hz | /I |

