PHILIPS

Lighting



AspiraVision Compact (35, 50 & 70 W) for CDM – The smart electronic gear

AspiraVision Compact for CDM

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps.The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

Benefits

- SOFT START allows installation with fewer circuit breakers; Loop Through allows faster, cost-efficient installation
- Longer lifetime
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future

Features

- SOFT START
- Loop Through (in independent version)
- Improved thermal performance
- Low electromagnetic interference
- Voltage drop detection

Application


- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

AspiraVision Compact for CDM

Versions



Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-AV C 35-70 /S CDM 220-240V 50/60Hz	4.5 mm	32.1 mm	110.0 mm	98.5 mm	75.0 mm	63.5 mm

Product
HID-AV C 35-70 /I CDM 220-240V 50/60Hz

Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V

General Information	
Number Of Products On MCB (16A Type B) (Nom)	58
Number Of Lamps	1 piece/unit
Lamp Type	CDM

System characteristics	
Lamp Power On CDM	39-73 W
Rated Ballast-Lamp Power	35-70 W

AspiraVision Compact for CDM

Mechanical and Housing

Order Code	Full Product Name	Housing
913700683866	HID-AV C 35-70 /S CDM 220-240V 50/60Hz	/S

Order Code	Full Product Name	Housing
913700684066	HID-AV C 35-70 /I CDM 220-240V 50/60Hz	/I

© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.