



AspiraVision Compact (35, 50 & 70 W) for CDM – The smart electronic gear

AspiraVision Compact for CDM

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

Benefits

- SOFT START allows installation with fewer circuit breakers; Loop Through allows faster, cost-efficient installation
- Longer lifetime
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future

Features


- SOFT START
- Loop Through (in independent version)
- Improved thermal performance
- Low electromagnetic interference
- Voltage drop detection

Application


- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

AspiraVision Compact for CDM

Versions



Dimensional drawing



HID-AV C 35-70 /S CDM 220-240V 50/60Hz

Product	D1	C1	A1	A2	B1	B2
HID-AV C 35-70 /S CDM 220-240V 50/60Hz	4.5 mm	32.1 mm	110.0 mm	98.5 mm	75.0 mm	63.5 mm

Product	D1	C1	A1	A2	B1
HID-AV C 50 /I CDM 220-240V 50/60Hz	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

HID-AV C 50 /I CDM 220-240V 50/60Hz

AspiraVision Compact for CDM

Operating and Electrical	
Input Frequency	50-60
Input Voltage	220 to 240
General Information	
Number Of Products On MCB (16A Type B) (Nom)	58
Number Of Lamps	1
Lamp Type	CDM
System characteristics	
Lamp Power On CDM	39-73
Rated Ballast-Lamp Power	35-70 W

Mechanical and Housing

order code	Housing
913700683866	/S

order code	Housing
913700684066	/I

