



Long-lasting, reliable solution

HID-Basic BSX for SOX

Impregnated electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

Benefits

- Compact dimensions and lightweight – easy to fit in linear luminaires
- Simple installation
- Long-lasting reliable solution protected from overheating

Features


- Based on magnetic fluorescent ballast design
- Equipped with double-insert contacts
- Minimal watt losses thanks to orthocyclic winding process
- Ballasts for alternative mains voltages/frequencies available upon request

Application

- Outdoor lighting (most popular application: road lighting)

HID-Basic BSX for SOX

Dimensional drawing



| Product | D1 | C1 | C3 | A1 | A2 | A3 | A4 | B1 | B2 |
|-----------------|-----|------|-----|-------|-------|------|------|------|------|
| BSX 35/55 L82 | 4.2 | 28.0 | 1.5 | 196.0 | 180.0 | 54.0 | 54.0 | 39.0 | 20.0 |
| 240V 50Hz | mm | mm | mm | mm | mm | mm | mm | mm | mm |
| WITH BRACKET | | | | | | | | | |

