



Beautiful sparkle, simple use

MASTERColour CDM-R

Range of compact, high-efficiency, discharge reflector lamps with a stable color over lifetime and a crisp, sparkling light

Benefits

- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Stable color impression over lifetime

Features

- Crisp white light
- Superior color quality
- High beam intensities are achieved very easy and efficiently from these compact reflector lamps

Application

- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTERColour CDM-R

Versions



CDM-R 35W, 70W /830, /
930, /942 PAR30L 30D

Dimensional drawing




Product

MASTERColour CDM-R 35W/830 E27 PAR30L 30D 1CT




MASTERColour CDM-R

Accent Diagrams



Beam Diagrams



LDBE_CDM-R_0012-Beam diagram

