



Beautiful sparkle, simple use

MASTERColour CDM-R

Range of compact, high-efficiency, discharge reflector lamps with a stable color over lifetime and a crisp, sparkling light

Benefits

- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Stable color impression over lifetime

Features

- Crisp white light
- Superior color quality
- High beam intensities are achieved very easy and efficiently from these compact reflector lamps

Application



- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-R

Dimensional drawing



Product	D (max)	D	C (max)	C
MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	65 mm	64 mm	92 mm	90 mm
MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	65 mm	64 mm	92 mm	90 mm
MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	65 mm	64 mm	95 mm	92 mm
MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	65 mm	64 mm	95 mm	92 mm
MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	65 mm	64 mm	92 mm	90 mm
MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	65 mm	64 mm	92 mm	90 mm
MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	65 mm	64 mm	95 mm	92 mm
MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	65 mm	64 mm	95 mm	92 mm

Product	D (max)	D	C (max)	C
MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	97 mm	95 mm	120 mm	118 mm
MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	97 mm	95 mm	120 mm	118 mm
MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	97 mm	95 mm	123 mm	118 mm
MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	97 mm	95 mm	120 mm	118 mm
MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	97 mm	95 mm	120 mm	118 mm
MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm

General Information	
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
928070900694	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	E27	1,000
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	E27	1,000
928071000694	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	E27	1,000

Order Code	Full Product Name	Cap-Base	Switching Cycle
928071100693	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	E27	1,050
928071100694	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	E27	1,050
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	E27	1,050

MASTERColour CDM-R

Order Code	Full Product Name	Cap-Base	Switching Cycle
928071200693	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	E27	1,050
928071200694	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	E27	1,050
928073500610	MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	E26	-
928073800610	MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	E26	-
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	E27	800
928085300610	MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	E26	-
928085400610	MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	E26	-
928085600610	MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	E26	-
928087500610	MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	E26	-

Order Code	Full Product Name	Cap-Base	Switching Cycle
928089400693	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	E27	1,050
928091600610	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	E26	-
928091800610	MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	E26	-
928094400610	MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	E26	-
928488700191	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	E27	1,000
928488800191	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	E27	800
928488900191	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	E27	800
928489100191	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	E27	800
928489200191	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	E27	800

Light Technical (1/2)

Order Code	Full Product Name	Beam Angle (Nom)	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	LLMF At End Of Nominal Lifetime (Nom)
928070900694	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	10 degree(s)	0.431	0.400	Warm White (WW)	3000 K	81	48 %
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	30 degree(s)	0.431	0.400	Warm White (WW)	3000 K	81	48 %
928071000694	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	30 degree(s)	0.431	0.400	Warm White (WW)	3000 K	81	48 %
928071100693	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	10 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	62 %
928071100694	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	10 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	62 %
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	40 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	62 %
928071200693	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	40 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	62 %
928071200694	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	40 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	62 %
928073500610	MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	10 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	-
928073800610	MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	40 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	-
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	30 degree(s)	0.433	0.402	Warm White (WW)	3000 K	81	52 %
928085300610	MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	10 degree(s)	0.433	0.402	Warm White (WW)	3000 K	81	-
928085400610	MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	30 degree(s)	0.433	0.402	Warm White (WW)	3000 K	81	-

MASTERColour CDM-R

Order Code	Full Product Name	Beam Angle (Nom)	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	LLMF At End Of Nominal Lifetime (Nom)
928085600610	MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	30 degree(s)	0.431	0.400	Warm White (WW)	3000 K	81	-
928087500610	MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	40 degree(s)	0.371	0.366	Cool White (CW)	4200 K	93	-
928089400693	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	40 degree(s)	0.371	0.366	Cool White (CW)	4200 K	93	61 %
928091600610	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	30 degree(s)	0.375	0.370	Cool White (CW)	4200 K	92	-
928091800610	MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	10 degree(s)	0.375	0.370	Cool White (CW)	4200 K	92	-
928094400610	MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	30 degree(s)	0.427	0.397	Warm White (WW)	3000 K	81	-
928488700191	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	10 degree(s)	0.431	0.400	Warm White (WW)	3000 K	81	48 %
928488800191	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	30 degree(s)	0.431	0.400	Warm White (WW)	3000 K	81	48 %
928488900191	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	30 degree(s)	0.433	0.402	Warm White (WW)	3000 K	81	52 %
928489100191	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	30 degree(s)	0.375	0.370	Cool White (CW)	4100 K	92	68 %
928489200191	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	10 degree(s)	0.375	0.370	Cool White (CW)	4100 K	92	68 %

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Luminous Intensity (Nom)
928070900694	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	2,150 lm	44,000 cd
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	-	7,400 cd
928071000694	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	-	7,400 cd
928071100693	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	-	68,000 cd
928071100694	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	-	68,000 cd
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	4,500 lm	9,500 cd
928071200693	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	-	9,500 cd
928071200694	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	-	9,500 cd
928073500610	MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	-	68,000 cd
928073800610	MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	4,500 lm	9,500 cd
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	-	5,300 cd

Order Code	Full Product Name	Luminous Flux	Luminous Intensity (Nom)
928085300610	MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	-	21,000 cd
928085400610	MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	-	5,300 cd
928085600610	MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	-	7,400 cd
928087500610	MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	-	9,000 cd
928089400693	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	-	9,000 cd
928091600610	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	1,900 lm	5,000 cd
928091800610	MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	1,900 lm	21,500 cd
928094400610	MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	4,500 lm	13,500 cd
928488700191	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	-	44,000 cd
928488800191	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	-	6,600 cd
928488900191	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	-	5,000 cd

MASTERC colour CDM-R

Order Code	Full Product Name	Luminous Flux	Luminous Intensity (Nom)
928489100191	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	-	5,000 cd

Order Code	Full Product Name	Luminous Flux	Luminous Intensity (Nom)
928489200191	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	-	21,500 cd

Operating and Electrical

Order Code	Full Product Name	Warm-up time to 60% light	Voltage (Nom)	Power Consumption
928070900694	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	120 s	86 V	39.1 W
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	120 s	86 V	39.1 W
928071000694	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	120 s	86 V	39.1 W
928071100693	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	120 s	90 V	73.2 W
928071100694	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	120 s	90 V	73.2 W
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	120 s	90 V	73.2 W
928071200693	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	120 s	90 V	73.2 W
928071200694	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	120 s	90 V	73.2 W
928073500610	MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	120 s	90 V	73.2 W
928073800610	MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	120 s	90 V	73.2 W
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	120 s	88 V	39.1 W
928085300610	MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	120 s	88 V	39.1 W

Order Code	Full Product Name	Warm-up time to 60% light	Voltage (Nom)	Power Consumption
928085400610	MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	120 s	88 V	39.1 W
928085600610	MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	120 s	86 V	39.1 W
928087500610	MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	-	88 V	73.2 W
928089400693	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	120 s	88 V	73 W
928091600610	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	-	85 V	39.1 W
928091800610	MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	-	85 V	39.1 W
928094400610	MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	-	90 V	73.2 W
928488700191	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	120 s	86 V	38 W
928488800191	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	120 s	86 V	38 W
928488900191	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	120 s	88 V	38 W
928489100191	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	120 s	85 V	39 W
928489200191	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	120 s	85 V	39.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928070900694	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	PAR30L
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	PAR30L

Order Code	Full Product Name	Bulb Shape
928071000694	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	PAR30L
928071100693	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	PAR30L

MASTERColour CDM-R


Order Code	Full Product Name	Bulb Shape
928071100694	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	PAR30L
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	PAR30L
928071200693	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	PAR30L
928071200694	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	PAR30L
928073500610	MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	PAR30L
928073800610	MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	PAR30L
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	PAR20
928085300610	MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	PAR20
928085400610	MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	PAR20
928085600610	MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	PAR30L



Approval and Application


Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928070900694	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	42 kWh	2.8 mg
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	42 kWh	2.8 mg
928071000694	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	42 kWh	2.8 mg
928071100693	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	80 kWh	8.3 mg
928071100694	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT	80 kWh	8.3 mg
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	80 kWh	8.3 mg
928071200693	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	80 kWh	8.3 mg
928071200694	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	80 kWh	8.3 mg
928073500610	MASTERC CDM-R 70W/830 E26 PAR30L 10D 1CT	80 kWh	8.3 mg
928073800610	MASTERC CDM-R 70W/830 E26 PAR30L 40D 1CT	80 kWh	8.3 mg
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	42 kWh	2.8 mg
928085300610	MASTERC CDM-R 35W/830 E26 PAR20 10D 1CT	42 kWh	2.8 mg
928085400610	MASTERC CDM-R 35W/830 E26 PAR20 30D 1CT	42 kWh	2.8 mg
928085600610	MASTERC CDM-R 35W/830 E26 PAR30L 30D 1CT	42 kWh	2.8 mg
928087500610	MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	-	6.6 mg
928089400693	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	80 kWh	6.6 mg
928091600610	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	-	2.8 mg
928091800610	MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	-	2.8 mg


Order Code	Full Product Name	Bulb Shape
928087500610	MASTERC CDM-R 70W/942 E26 PAR30L 40D 1CT	PAR30L
928089400693	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT	PAR30L
928091600610	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	PAR20
928091800610	MASTERC CDM-R 35W/942 E26 PAR20 10D 1CT	PAR20
928094400610	MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	PAR30L
928488700191	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	PAR30L
928488800191	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	PAR30L
928488900191	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	PAR20
928489100191	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	PAR20
928489200191	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	PAR20

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928094400610	MASTERC CDM-R 70W/830 E26 PAR30L 30D 1CT	-	8.3 mg
928488700191	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT	42 kWh	2.8 mg
928488800191	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	42 kWh	2.8 mg
928488900191	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	42 kWh	2.8 mg
928489100191	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT	43 kWh	2.8 mg
928489200191	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT	43 kWh	2.8 mg












Accent Diagrams




Accent Diagram - MASTERC CDM-R 70W/830
 E26 PAR30L 30D 1CT




Accent Diagram - MASTERC CDM-R 35W/942
 E27 PAR20 10D 1CT




Accent Diagram - MASTERC CDM-R 35W/942
 E26 PAR20 30D 1CT




Accent Diagram - MASTERC CDM-R 70W/830
 E27 PAR30L 10D 1CT




Accent Diagram - MASTERC CDM-R 70W/830
 E26 PAR30L 40D 1CT




Accent Diagram - MASTERC CDM-R 70W/942
 E27 PAR30L 40D 1CT



Accent Diagram - MASTERC CDM-R 35W/830
 E26 PAR20 10D 1CT




Accent Diagram - MASTERC CDM-R 35W/830
 E27 PAR20 30D 1CT



Accent Diagram - MASTERC CDM-R 35W/830
 E27 PAR30L 10D 1CT


MASTERColour CDM-R

Accent Diagrams




Accent Diagram - MASTERC CDM-R 35W/830
E27 PAR30L 30D 1CT


Beam Diagrams




Beam diagram - MASTERC CDM-R 70W/830
E26 PAR30L 30D 1CT




Beam diagram - MASTERC CDM-R 35W/942
E27 PAR20 10D 1CT




Beam diagram - MASTERC CDM-R 35W/942
E26 PAR20 30D 1CT



Beam diagram - MASTERC CDM-R 70W/830
E27 PAR30L 10D 1CT




Beam diagram - MASTERC CDM-R 70W/830
E26 PAR30L 40D 1CT




Beam diagram - MASTERC CDM-R 70W/942
E27 PAR30L 40D 1CT


Beam Diagrams




Beam diagram - MASTERC CDM-R 35W/830
 E26 PAR20 10D 1CT



Beam diagram - MASTERC CDM-R 35W/830
 E27 PAR20 30D 1CT



Beam diagram - MASTERC CDM-R 35W/830
 E27 PAR30L 10D 1CT



Beam diagram - MASTERC CDM-R 35W/830
 E27 PAR30L 30D 1CT

