



Perfect sparkle, trendy design

MASTERColour CDM-R111 Elite

MASTERColour CDM-R111 Elite combines the trendy look of 111 mm aluminum-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

Benefits

Features

Application

Warnings and Safety


Versions



CDM-R111 Elite GX8.5

MASTERCcolour CDM-R111 Elite

Dimensional drawing



Product	D (max)	C (max)
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 24D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 40D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	111 mm	95 mm
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 10D	111 mm	95 mm

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Voltage (Nom)	89 V
Re-Ignition Time (Min) (Max)	15 min
Warm Up Time To 60% Light (Nom)	120 s

General Information

Cap-Base	GX8.5
Life To 20% Failures (Nom)	10500 h
Life To 50% Failures (Nom)	12000 h
Life To 5% Failures (Nom)	8000 h
Operating Position	UNIVERSAL
Switching Cycle	1050X

Light Technical

Color Code	930
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
LLmf At End Of Nominal Lifetime (Nom)	70 %
Lumen Maintenance 12000 h (Nom)	70 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 4000 h (Nom)	85 %

Mechanical and Housing

Bulb Finish	Reflector
Bulb Shape	R111

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928195305330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	43 kWh	B	4.7 mg
928195305391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	43 kWh	B	4.7 mg
928195405330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	43 kWh	A	4.7 mg
928195405391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	43 kWh	A	4.7 mg
928195505330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 40D	43 kWh	A	4.7 mg
928195605330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 10D	80 kWh	B	6.6 mg
928195705330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 24D	80 kWh	A	6.6 mg
928195805330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D	80 kWh	A	6.6 mg

Operating and Electrical

MASTERCcolour CDM-R111 Elite

Order Code	Full Product Name	Lamp			Power (Rated) (Nom)
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	
928195305330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	0.440 A	97 V	81 V	39.1 W
928195305391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	0.440 A	97 V	81 V	39.1 W
928195405330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	0.440 A	97 V	81 V	39.1 W
928195405391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	0.440 A	97 V	81 V	39.1 W

Order Code	Full Product Name	Lamp			Power (Rated) (Nom)
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	
928195505330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 40D	0.440 A	97 V	81 V	39.1 W
928195605330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 10D	-	98 V	80 V	73.2 W
928195705330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 24D	-	98 V	80 V	73.2 W
928195805330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D	-	98 V	80 V	73.2 W

General Information

Order Code	Full Product Name	Life To 10% Failures (Nom)
928195305330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	5500 h
928195305391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	5500 h
928195405330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	5500 h
928195405391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	5500 h

Order Code	Full Product Name	Life To 10% Failures (Nom)
928195505330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 40D	5500 h
928195605330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 10D	9500 h
928195705330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 24D	9500 h
928195805330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D	9500 h

Light Technical (1/2)

Order Code	Full Product Name	Beam		Chromaticity	
		Angle (Nom)	Beam Description	Coordinate X (Nom)	Coordinate Y (Nom)
928195305330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	10 °	Spot	0.432	0.392
928195305391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	10 °	Spot	0.432	0.392
928195405330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	24 °	Narrow Flood	0.432	0.392
928195405391	MASTERCcolour CDM-R111 Elite CDM-R111 Elite	24 °	Narrow Flood	0.432	0.392

Order Code	Full Product Name	Beam		Chromaticity	
		Angle (Nom)	Beam Description	Coordinate X (Nom)	Coordinate Y (Nom)
928195505330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	40 °	Flood	0.432	0.392
928195605330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 10D	10 °	Spot	0.441	0.397
928195705330	MASTERCcolour CDM-R111 Elite CDM-R111 Elite	24 °	Narrow Flood	0.441	0.397


MASTERCLOUR CDM-R111 Elite



Order Code	Full Product Name	Beam		Chromaticity	
		Angle (Nom)	Beam Description	Coordinate X (Nom)	Coordinate Y (Nom)
928195805330	MASTERCLOUR CDM-R111 Elite	40 °	Flood	0.441	0.397

Order Code	Full Product Name	Beam		Chromaticity	
		Angle (Nom)	Beam Description	Coordinate X (Nom)	Coordinate Y (Nom)
	CDM-R111 Elite				
	70W/930 GX8.5				
	40D				




Light Technical (2/2)

Order Code	Full Product Name	Color		Luminous Efficacy (rated) (Nom)	Design Mean Lumens	Luminous Intensity (Min)	Luminous Intensity (Nom)
		Rendering Index (Min)	Rendering Index (Nom)				
928195305330	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	87	90	37 lm/W	1200 lm	27000 cd	36000 cd
928195305391	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 10D	87	90	37 lm/W	1200 lm	27000 cd	36000 cd
928195405330	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	87	90	46 lm/W	1500 lm	6500 cd	8500 cd
928195405391	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	87	90	46 lm/W	1500 lm	6500 cd	8500 cd
928195505330	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 40D	87	90	46 lm/W	1500 lm	3500 cd	4500 cd
928195605330	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 10D	89	92	39 lm/W	2400 lm	34000 cd	45000 cd
928195705330	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 24D	89	92	50 lm/W	3100 lm	12000 cd	16000 cd
928195805330	MASTERCLOUR CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D	89	92	50 lm/W	3100 lm	6500 cd	8500 cd







Accent Diagrams






LDAC_CDMR111E_0002-Accent diagram



LDAC_CDMR111E_0008-Accent diagram

Beam Diagrams




LDBE_CDMR111E_0001-Beam diagram


LDBE_CDMR111E_0002-Beam diagram

LDBE_CDMR111E_0003-Beam diagram


Beam Diagrams



LDBE_CDMR111E_0007-Beam diagram



LDBE_CDMR111E_0008-Beam diagram



LDBE_CDMR111E_0009-Beam diagram

