



Perfect sparkle, easy application

MASTERColour CDM-Rm Elite Mini

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Easy to install and replace, reducing installation and relamping costs
- Easy to install and replace, reducing installation and relamping costs
- Fits in small luminaires which are less visible
- Fits in small luminaires which are less visible

Features

- Crisp white sparkling light
- Crisp white sparkling light
- Excellent color rendering, with extra red
- Excellent colour rendering, with extra red
- High efficacy with unparalleled lumen maintenance
- High efficacy with unparalleled lumen maintenance
- Mini design fitting in open luminaires
- Mini design fitting in open luminaires
- UV-blocking front glass
- UV-blocking front glass

MASTERColour CDM-Rm Elite Mini

Application

- Accent and display lighting in retail
- Accent and display lighting in retail
- General and decorative indoor lighting
- General and decorative indoor lighting

Warnings and Safety



- Use only with electronic control gear
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CDM-Rm 0008


Dimensional drawing



| Product | D (max) | D | C (max) | C | C1 (max) | A (max) |
|---------------------------|---------|-------|---------|----------|----------|---------|
| CDM-Rm Elite Mini 20W/830 | 51 mm | 50 mm | 65.4 mm | 62.75 mm | 60.9 mm | 59 mm |
| GX10 MR16 25D | | | | | | |


MASTERColour CDM-Rm Elite Mini

Accent Diagrams



Accent Diagram - CDM-Rm Elite Mini 20W/830
GX10 MR16 25D

Beam Diagrams



Beam diagram - CDM-Rm Elite Mini 20W/830
GX10 MR16 25D

