



Product Description

MASTERColour CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Benefits

- · Stable colour impression over lifetime
- · High lamp efficacy results in low operating costs and low heat generation
- · Long lamp life compared with incandescent and halogen lamps
- · Relatively low heat output enhances comfort for shoppers and staff
- · All types are UV-Block for reduced fading risks

Features

- · Warm or cool white colour impression
- · Colour rendering good to excellent
- $\boldsymbol{\cdot}$ Allows small-size luminaires designs that give high beam intensities

Application

- Shops and shop windows, offices and public buildings
- · Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety

- · Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTERColour CDM-T

Versions




LPPR CDM-T 0005

Dimensional drawing



| Product | D (max) | D | 0 | L (min) | L (max) | L | C (max) |
|------------------|---------|-----------|------|---------|---------|-------|---------|
| MASTERC CDM-T | 20 mm | 0.75 inch | 8 mm | 55 mm | 57 mm | 56 mm | 110 mm |
| 150W/942 G12 1CT | | | | | | | |





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.