



產品說明

MASTERColour CDM-TC 陶瓷複金屬燈

超精巧、高效率單端型放電燈，光色歷久如新，光線清晰明亮

优点

- 使用壽命優於白熾燈與鹵素燈
- 石英外管阻隔紫外線，避免光照導致商品褪色
- 歷久如新的穩定光色
- 高效率燈具，節省運作成本，降低光照熱度 (使顧客與工作人員更感舒適)

特点

- 清晰明亮的白色光
- 絕佳的演色性
- 迷你燈具也能展現高強度光束照明效果

应用

- 重點與展示照明，提供清亮晶瑩的照明效果
- 一般與裝飾照明

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



MASTERColour CDM-TC 陶瓷複金屬燈

Versions



LPPR CDM-TC 0002

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 35W/830	15 mm	0.5 in	5 mm	51 mm	53 mm	52 mm	85 mm
G8.5 1CT/12							
MASTERC CDM-TC 35W/842	15 mm	0.5 in	5 mm	51 mm	53 mm	52 mm	85 mm
G8.5 1CT/12							

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 70W/830	15 mm	0.5 in	7 mm	51 mm	53 mm	52 mm	85 mm
G8.5 1CT/12							

一般資訊	
燈座基底	G8.5
操作位置	UNIVERSAL
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡材質	抗 UV 石英
燈泡形狀	T14

MASTERCoulour CDM-TC 陶瓷複金屬燈

照明技術

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	色彩名稱	相關色彩溫度 (規範)	演色性指數 (CRI)	光效 (額定) (標準)
928085205129	MASTERC CDM-TC 35W/830 G8.5 1CT/12	0.432	0.394	暖白光 (WW)	3000 K	81	79 lm/W
928093805129	MASTERC CDM-TC 35W/842 G8.5 1CT/12	0.374	0.369	冷白光 (CW)	4200 K	85	79 lm/W
928086505129	MASTERC CDM-TC 70W/830 G8.5 1CT/12	0.439	0.398	暖白光 (WW)	3000 K	83	86 lm/W

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量	Order Code	Full Product Name	電壓 (標稱)	耗電量
928085205129	MASTERC CDM-TC 35W/830 G8.5 1CT/12	88 V	39.1 W	928086505129	MASTERC CDM-TC 70W/830 G8.5 1CT/12	83 V	73.2 W
928093805129	MASTERC CDM-TC 35W/842 G8.5 1CT/12	85 V	39.1 W				

認證與應用

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (標稱)
928085205129	MASTERC CDM-TC 35W/830 G8.5 1CT/12	43 kWh	3.1 mg
928093805129	MASTERC CDM-TC 35W/842 G8.5 1CT/12	43 kWh	2.7 mg
928086505129	MASTERC CDM-TC 70W/830 G8.5 1CT/12	80 kWh	4.6 mg

