



Product Description

MASTERColour CDM-T Elite

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Outstanding rendering of displayed merchandise due to high colour rendering (Ra 90) in combination with high lumen output; best offer in the market for 'enhancing merchandize'
- Stable color and lumen output over life keeps your store attractive season after season
- Excellent colour quality, which remains stable over lifetime
- Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life
- Light output over lifetime maintains display brightness
- High efficacy and long lifetime for lowest operating costs and low heat generation
- Relatively low heat generation enhances comfort for shoppers and staff
- UV Block for reduced fading risk of merchandise

MASTERCcolour CDM-T Elite

Features

- Crisp white sparkling light
- Crisp white light
- Excellent color rendering, with extra red
- Excellent colour rendering (Ra 90)
- High efficacy with unparalleled lumen maintenance
- Reliable lifetime performance
- Stable color performance over lifetime
- Stable colour performance during lifetime
- UV-blocking glass
- Increased light output compared with regular MASTERCcolour lamps
- Improved maintenance compared with regular MASTERCcolour lamps
- Burning position for
- CDM Elite-T 35W: vertical +/- 60 degrees
- CDM Elite-T 70W: universal


Application

- Accent and display lighting in retail
- Accent and display lighting with a sparkling effect, excellent solution for Retail
- General and decorative indoor lighting
- Decorative outdoor floodlighting
- Outdoor area lighting

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 35W/942 G12 1CT	20 mm	5.2 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/942 G12 1CT	20 mm	7.75 mm	55 mm	57 mm	56 mm	103 mm

MASTERC colour CDM-T Elite

General Information

Cap-Base	G12
Operating Position	UNIVERSAL

Light Technical

Color rendering index (CRI)	90
-----------------------------	----

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T19

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Correlated Color		Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Designation	Temperature (Nom)	(rated) (Nom)	
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	0.435	0.395	Warm White (WW)	3000 K	98 lm/W	-
928193605129	MASTERC CDM-T Elite 35W/942 G12 1CT	0.366	0.364	Cool White (CW)	4200 K	98 lm/W	-
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	103 lm/W	7,800 lm
928193705129	MASTERC CDM-T Elite 70W/942 G12 1CT	0.362	0.363	Cool White (CW)	4200 K	100 lm/W	-


Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	85 V	39.1 W
928193605129	MASTERC CDM-T Elite 35W/942 G12 1CT	90 V	39.1 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	85 V	73.2 W
928193705129	MASTERC CDM-T Elite 70W/942 G12 1CT	87 V	73.2 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury	Mercury
			Content (Hg) (Max)	Content (Hg) (Nom)
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	43 kWh	-	4.7 mg
928193605129	MASTERC CDM-T Elite 35W/942 G12 1CT	43 kWh	-	4.9 mg
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	74 kWh	6.6 mg	6.6 mg
928193705129	MASTERC CDM-T Elite 70W/942 G12 1CT	80 kWh	-	6.6 mg



MASTERColour CDM-T Elite

