



Beautiful sparkle, reliable life

MASTERColour CDM-TP

Range of protected, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light to be used in open luminaires

Benefits

- High lamp efficacy results in low operating costs and low heat generation
- Stable color impression over lifetime
- Long lamp life compared with incandescent and halogen lamps
- Relatively low heat output enhances comfort for shoppers and staff
- All types have UV-Block filtering for reduced fading risks

Features

- Crisp white light
- Superior color quality
- Lamp design is well-suited to be used in luminaires for power-spots (high intensity) and high-bay general lighting
- Double UV-Block quartz sleeves and a hard-glass outer bulb

Application

- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety

- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-TP

Dimensional drawing

D

Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERColour CDM-TP 150W/942 PGX12-2 1CT/12	32.00 mm	8 mm	89 mm	93 mm	91 mm	149 mm

