



产品描述

MASTERColour CDM-TP

防护型高效放电灯系列在整个寿命期间具有稳定的光色和明亮通透的闪光，可在开放式灯具上使用

优点

- 高光效,节约运行成本,热辐射低
- 卓越的色彩稳定性,在寿命周期内无偏差,无色差,最大程度保证环境的舒适性
- 节能省电,节约运行成本
- 防护型,适用于开放式灯具,便于安装与替换
- 防紫外线玻壳,减少商品褪色的危险

特点

- 暖白色和白色两种色温
- 良好的显色性
- 适用于电厂(高压)和高顶棚的环境照明
- 防护型,适用于开放式灯具,便于安装与替换
- 防紫外双石英玻壳
- 任意燃点位置

应用

- 用于商店、商店橱窗、办公室及公共空间的照明
- 室外装饰：泛光照明和步行区的照明
- 适用于开放式灯具
- 最好与电子镇流器配套使用,延长光源寿命,增强系统效率和防止频闪的装置
- 必须使用强电流保护装置(IEC 61167)
- 如果电压经常超过额定电压的 3%，必须采用其他等级的镇流器

安全提示

- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTERColour CDM-TP

Versions



LPPR CDM-TP PGX12-2

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TP 150W/942	32.00 mm	8 mm	89 mm	93 mm	91 mm	149 mm
PGX12-2 1CT/12						

