



Long-lasting, reliable solution

HID-Constant wattage BSX for SOX

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

Benefits

- Excellent resistance to humid conditions
- Long-lasting reliable solution – outstanding product lifetime of 15 years average
- Minimal watt losses thanks to orthocyclic winding process
- Control gear can be installed remotely

Features


- Series capacitor required in circuits with constant wattage
- Silicon potted ballast under IP21 canopy
- Equipped with screw terminal blocks as standard
- Ballasts for alternative mains voltages/frequencies available upon request

Application


- Outdoor lighting

HID-Constant wattage BSX for SOX

Versions



Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 180 H96 220-240V 50Hz CW-178/78	4.2 mm	78.0 mm	178.0 mm	162.0 mm	100.0 mm	42.0 mm

