



Product Description

HPL-N

Standard High Pressure Mercury lamp

Benefits

- Good budget alternative

Features

- Equipped with 1 or 2 auxiliary electrodes to ensure quick and reliable ignition
- Single-ended gas-filled glass bulb (HG-SG) with a quartz mercury vapour discharge tube
- Internally coated ovoid outer bulb, providing a cool, bluish white light with reasonable colour qualities

Application

- All outdoor applications, factories, transport sector and industrial area lighting

Warnings and Safety

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


HPL-N

Versions



LPPR HPL 0002

Dimensional drawing



Product	D (max)	C (max)
HPL-N 250W/542 E40 1SL/12	91 mm	226 mm

