



# Product Description

## HPL-N

Standard High Pressure Mercury lamp

### Benefits

- Good budget alternative

### Features

- Equipped with 1 or 2 auxiliary electrodes to ensure quick and reliable ignition
- Single-ended gas-filled glass bulb (HG-SG) with a quartz mercury vapour discharge tube
- Internally coated ovoid outer bulb, providing a cool, bluish white light with reasonable colour qualities

### Application

- All outdoor applications, factories, transport sector and industrial area lighting

### Warnings and Safety

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


HPL-N

Versions



LPPR HPL E26 E27

Dimensional drawing



Product	D (max)	C (max)
HPL-N 80W/542 E27 1CT/24	71 mm	155 mm

