



Product Description

HPI-T

Quartz metal halide lamps with clear outer bulb

Benefits

- High safety and comfort level, maintained over life
- Minimal maintenance cost

Features

- Clear tubular outer bulb
- Unique 3-band technology resulting in high luminous efficacy, both initially and over long lifetime
- Renders a natural white color appearance and good color stability

Application


- Sports lighting, floodlighting of buildings and monuments, area lighting e.g. harbours and building sites

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

HPI-T


Dimensional drawing



Product

HPI-T 2000W/542 E40 380V 1SL/4

Color Rendering Diagrams



LDCR_HPI-THW_1000W_2000W-Colour rendering diagram

