



Product Description

MASTER MHN-SE

Very compact quartz metal halide lamps with single-pin GX-22 lamp cap

Οφέλη

- Allows compact, highly efficient luminaire systems with high-precision optics for good beam control and minimal light spill
- Very good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers a superior solution for professional stadiums with regular TV coverage

Χαρακτηριστικά

- Single-pin concept for superior optical performance
- High luminous efficacy
- Natural white color appearance, very good color rendering and good color stability
- Daylight color temperature eases transition from daylight to artificial lighting

Εφαρμογή

- Professional sports lighting

Προειδοποίηση & ασφάλεια


- Να χρησιμοποιείται αποκλειστικά σε πλήρως κλειστά φωτιστικά, ακόμα και κατά τη διάρκεια των δοκιμών (IEC61167, IEC 62035, IEC60598)
- Το φωτιστικό πρέπει να έχει τη δυνατότητα συγκράτησης πολύ θερμών τμημάτων του λαμπτήρα σε περίπτωση θραύσης του
- Ένας λαμπτήρας που σπάει είναι εξαιρετικά απίθανο να έχει επίδραση στην υγεία σας. Εάν σπάσει ένας λαμπτήρας, αερίστε τον χώρο για 30 λεπτά και αφαιρέστε τα σπασμένα κομμάτια, κατά προτίμηση με γάντια. Τοποθετήστε τα σε μια πλαστική σακούλα, κλείστε τη καλά και αποθέστε τη στα προς ανακύκλωση απορρίμματα της περιοχής σας. Μην χρησιμοποιείτε ηλεκτρική σκούπα.

MASTER MHN-SE

Versions



Σχεδιάγραμμα διαστάσεων



Product

MASTER MHN-SE 2000W/956 GX22 400V HO UNP

