

PHILIPS

Lighting



Philips GreenSpace – High-efficiency, sustainable LED solution with 65% recycled materials

GreenSpace

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

Benefits

- Good value for money
- Low return of investment years due to high efficiency and long lifetime
- Wide range of mounting options to fit different ceiling types
- The perfect fit for retrofit projects (custom sizes) which provides faster installation
- Various light output choices to suit different application needs
- Office-compliant, with stable color performance and wide light distribution

Features

- Mini (DN460B) and compact (DN470B) sizes for recessed
- Surface mounted, track and pendant versions available
- Custom cut-out sizes between 150mm–280 mm, in total 28 sizes available
- High system efficacy: up to 131 lm/w
- UGR19 version with anti-glare ring
- Available in 3000 lumen to cover applications with higher ceilings
- Selection of colors: White, silver and black
- IP54 version with a front cover and emergency lighting option available
- Configurable with many driver types such as DALI, POE and wireless with InterAct ready
- Fast installation due to variety of connections and cables

Application

- Retail
- Offices
- Hospitals and Care Centers
- Hospitality

Versions



Standard GreenSpace Pendant




Greenspace EU gen 2-DN462B




Standard GreenSpace Surface Mounted

Dimensional drawing



Dimensional drawing



Product details

Greenspace_EU_gen_2-DN473B-DPP.TIF



Greenspace_EU_gen_2-DN472B-DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-1DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-3DPP.TIF



Product details

Greenspace_EU_gen_2-DN462B-
DPP.TIF



Greenspace_EU_gen_2-
DN462_463_472_473B-2DPP.TIF



Greenspace_EU_gen_2-DN463B-
DPP.TIF



General Information	
CE mark	Yes
Driver included	Yes
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Optic type	-
Operating and Electrical	
Line Frequency	50 to 60 Hz
Approval and Application	
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information (1/2)

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
910505102037	DN461B LED11S/830 DIA- VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102038	DN461B LED11S/830 DIA- VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102039	DN461B LED11S/840 DIA- VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102040	DN461B LED11S/840 DIA- VLC-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102071	DN461B LED20S/840 DIA- VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102077	DN463B LED11S/830 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102078	DN463B LED11S/840 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102286	DN461B LED11S/830 PSD- E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102287	DN461B LED11S/840 PSD- E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
912500100066	DN463B LED11S/830 PSU- E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100067	DN463B LED11S/840 PSU- E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
912500100518	DN461B LED11S/830 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100519	DN461B LED11S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103009	DN471C LED20S/830 PSU D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103015	DN471C LED20S/840 PSU D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103021	DN470P LED20S/830 PSU D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103027	DN470P LED20S/840 PSU D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102996	DN470C LED20S/830 PSU D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
			flammable surfaces		
912500103003	DN470C LED20S/840 PSU D22H16 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
910505102087	DN471B LED20S/830 WIA-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102089	DN471B LED20S/840 WIA-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102290	DN471B LED20S/830 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102291	DN471B LED20S/840 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100526	DN471B LED20S/830 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100527	DN471B LED20S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
912500101314	DN471B LED30S/830 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
912500101315	DN471B LED30S/840 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102079	DN470B LED11S/840 DIA- VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102085	DN470B LED20S/840 WIA-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102111	DN472B LED20S/830 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102113	DN472B LED20S/840 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102115	DN472B LED30S/830 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102116	DN472B LED30S/840 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102147	DN470B LED20S/830 WIA-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102271	DN470B LED20S/830 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102272	DN470B LED30S/830 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102288	DN470B LED20S/840 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102289	DN470B LED30S/840 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100522	DN470B LED20S/830 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100523	DN470B LED20S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500101305	DN470B LED30S/830 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
912500101307	DN470B LED30S/840 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
912500103008	DN471C LED20S/830 DIA- VLC D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103011	DN471C LED20S/830 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103014	DN471C LED20S/840 DIA- VLC D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103017	DN471C LED20S/840 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103023	DN470P LED20S/830 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103029	DN470P LED20S/840 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
910505102033	DN460B LED11S/830 DIA- VLC-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102034	DN460B LED11S/830 DIA- VLC-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102035	DN460B LED11S/840 DIA- VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102036	DN460B LED20S/840 DIA- VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
910505102072	DN462B LED11S/830 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102074	DN462B LED11S/840 DIA- VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
910505102284	DN460B LED11S/830 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102285	DN460B LED11S/840 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100514	DN460B LED11S/830 PSU-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	LED11S
912500100515	DN460B LED11S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
910505102073	DN462B LED11S/830 DIA- VLC-E C WH PCO P	-	-	Temperature 750 °C, duration 5 s	-
910505102075	DN462B LED11S/840 DIA- VLC-E C WH PCO P	-	-	Temperature 750 °C, duration 5 s	-
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
910505102112	DN472B LED20S/830 DIA- VLC-E C WH PCO P	-	-	Temperature 750 °C, duration 5 s	-
910505102114	DN472B LED20S/840 DIA- VLC-E C WH PCO P	-	-	Temperature 750 °C, duration 5 s	-
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
912500103030	DN470T LED20S/830 DIA- VLC D22H16 5C6 GR	ENEC mark	For mounting on normally	Temperature 650 °C, duration 5 s	-

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
			flammable surfaces		
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102997	DN470C LED20S/830 PSU D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103004	DN470C LED20S/840 PSU D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500102998	DN470C LED20S/830 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103005	DN470C LED20S/840 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	LED20S

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	LED20S
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	LED20S
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	LED20S
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103022	DN470P LED20S/830 PSU D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103028	DN470P LED20S/840 PSU D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103010	DN471C LED20S/830 PSU D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103016	DN471C LED20S/840 PSU D22H16 GR	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	ENEC mark	flammable surfaces	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	ENEC mark	flammable surfaces	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s

General Information (2/2)

Order Code	Full Product Name	Product family code	Service tag	Order Code	Full Product Name	Product family code	Service tag
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	DN461B	-	910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	DN471B	-
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	DN461B	-	910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	DN471B	-
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	DN461B	-	910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	DN471B	-
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	DN461B	-	910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	DN471B	-
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	DN461B	-	910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	DN471B	-
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC	DN463B	-	910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	DN471B	-
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC	DN463B	-	910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	DN471B	-
910505102286	DN461B LED11S/830 PSD-E C WH P	DN461B	-	910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC	DN473B	-
910505102287	DN461B LED11S/840 PSD-E C WH P	DN461B	-	910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC	DN473B	-
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	DN463B	Yes	910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC	DN473B	-
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	DN463B	Yes	910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC	DN473B	-
912500100518	DN461B LED11S/830 PSU-E C WH P	DN461B	Yes	910505102290	DN471B LED20S/830 PSD-E C WH P	DN471B	-
912500100519	DN461B LED11S/840 PSU-E C WH P	DN461B	Yes	910505102291	DN471B LED20S/840 PSD-E C WH P	DN471B	-
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	DN461B	Yes	912500100074	DN473B LED20S/830 PSU-E C WH PCC P	DN473B	Yes
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	DN461B	Yes	912500100075	DN473B LED20S/840 PSU-E C WH PCC P	DN473B	Yes
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	-	-	912500100526	DN471B LED20S/830 PSU-E C WH P	DN471B	Yes
912500103009	DN471C LED20S/830 PSU D22H16 BK	-	-	912500100527	DN471B LED20S/840 PSU-E C WH P	DN471B	Yes
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	-	-	912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	DN471B	Yes
912500103015	DN471C LED20S/840 PSU D22H16 BK	-	-	912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	DN471B	Yes
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	-	-	912500101314	DN471B LED30S/830 PSU-E C WH P	DN471B	Yes
912500103021	DN470P LED20S/830 PSU D22H16 BK	-	-	912500101315	DN471B LED30S/840 PSU-E C WH P	DN471B	Yes
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	-	-	912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	DN471B	Yes
912500103027	DN470P LED20S/840 PSU D22H16 BK	-	-	912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	DN471B	Yes
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	-	-	910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	DN470B	-
912500102996	DN470C LED20S/830 PSU D22H16 BK	-	-	910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	DN470B	-
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	-	-	910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	DN470B	-
912500103003	DN470C LED20S/840 PSU D22H16 BK	-	-				
910505102087	DN471B LED20S/830 WIA-E C WH P	DN471B	-				
910505102089	DN471B LED20S/840 WIA-E C WH P	DN471B	-				
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	DN471B	-				

Product			
Order Code	Full Product Name	family code	Service tag
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	DN470B	-
910505102085	DN470B LED20S/840 WIA-E C WH P	DN470B	-
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	DN472B	-
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	DN472B	-
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	DN470B	-
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	DN470B	-
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	DN470B	-
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	DN470B	-
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	DN472B	-
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	DN472B	-
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	DN472B	-
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	DN472B	-
910505102147	DN470B LED20S/830 WIA-E C WH P	DN470B	-
910505102271	DN470B LED20S/830 PSD-E C WH P	DN470B	-
910505102272	DN470B LED30S/830 PSD-E C WH P	DN470B	-
910505102288	DN470B LED20S/840 PSD-E C WH P	DN470B	-
910505102289	DN470B LED30S/840 PSD-E C WH P	DN470B	-
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	DN472B	Yes
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	DN472B	Yes
912500100522	DN470B LED20S/830 PSU-E C WH P	DN470B	Yes
912500100523	DN470B LED20S/840 PSU-E C WH P	DN470B	Yes
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	DN470B	Yes
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	DN470B	Yes
912500101305	DN470B LED30S/830 PSU-E C WH P	DN470B	Yes
912500101307	DN470B LED30S/840 PSU-E C WH P	DN470B	Yes
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	DN470B	Yes
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	DN470B	Yes
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	-	-
912500103011	DN471C LED20S/830 PSU D22H16 WH	-	-
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	-	-
912500103017	DN471C LED20S/840 PSU D22H16 WH	-	-
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	-	-
912500103023	DN470P LED20S/830 PSU D22H16 WH	-	-
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	-	-
912500103029	DN470P LED20S/840 PSU D22H16 WH	-	-
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	DN460B	-
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	DN460B	-
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	DN460B	-
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	DN460B	-
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	DN462B	-
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	DN462B	-

Product			
Order Code	Full Product Name	family code	Service tag
910505102284	DN460B LED11S/830 PSD-E C WH P	DN460B	-
910505102285	DN460B LED11S/840 PSD-E C WH P	DN460B	-
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	DN462B	Yes
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	DN462B	Yes
912500100514	DN460B LED11S/830 PSU-E C WH P	DN460B	Yes
912500100515	DN460B LED11S/840 PSU-E C WH P	DN460B	Yes
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	DN460B	Yes
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	DN460B	Yes
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	DN462B	-
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	DN462B	-
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	DN462B	Yes
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	DN462B	Yes
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	DN472B	-
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	DN472B	-
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	DN472B	-
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	DN472B	-
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	DN472B	Yes
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	DN472B	Yes
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	-	-
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	-	-
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	-	-
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	-	-
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	-	-
912500102997	DN470C LED20S/830 PSU D22H16 GR	-	-
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	-	-
912500103004	DN470C LED20S/840 PSU D22H16 GR	-	-
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	-	-
912500102998	DN470C LED20S/830 PSU D22H16 WH	-	-
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	-	-
912500103005	DN470C LED20S/840 PSU D22H16 WH	-	-
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	-	-
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	-	-
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	-	-
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	-	-
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	-	-
912500103022	DN470P LED20S/830 PSU D22H16 GR	-	-
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	-	-
912500103028	DN470P LED20S/840 PSU D22H16 GR	-	-
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	-	-
912500103010	DN471C LED20S/830 PSU D22H16 GR	-	-
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	-	-
912500103016	DN471C LED20S/840 PSU D22H16 GR	-	-

Product			
Order Code	Full Product Name	family code	Service tag
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	-	-
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	-	-

Product			
Order Code	Full Product Name	family code	Service tag
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	-	-
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam	Correlated	Luminous		
		angle of	Color	Efficacy		
Order Code	Name	Full Product	light	Temperature	(rated)	Luminous
Order Code	Name	source	(Nom)	(Nom)	Flux	
910505102037	DN461B	- degree(s)	3000 K	79 lm/W	1,200 lm	
	LED11S/830					
	DIA-VLC-E C					
	ELP3 WH P					
910505102038	DN461B	- degree(s)	3000 K	114 lm/W	1,200 lm	
	LED11S/830					
	DIA-VLC-E C					
	WH P					
910505102039	DN461B	- degree(s)	4000 K	82 lm/W	1,250 lm	
	LED11S/840					
	DIA-VLC-E C					
	ELP3 WH P					
910505102040	DN461B	- degree(s)	4000 K	118 lm/W	1,250 lm	
	LED11S/840					
	DIA-VLC-E C					
	WH P					
910505102071	DN461B	- degree(s)	4000 K	122 lm/W	2,200 lm	
	LED20S/840					
	DIA-VLC-E C					
	WH P					
910505102077	DN463B	- degree(s)	3000 K	109 lm/W	1,150 lm	
	LED11S/830					
	DIA-VLC-E C					
	WH PCC P					
910505102078	DN463B	- degree(s)	4000 K	114 lm/W	1,200 lm	
	LED11S/840					
	DIA-VLC-E C					
	WH PCC P					
910505102286	DN461B	-	3000 K	125 lm/W	1,200 lm	
	LED11S/830					
	PSD-E C WH P					
910505102287	DN461B	-	4000 K	130 lm/W	1,250 lm	
	LED11S/840					
	PSD-E C WH P					
912500100066	DN463B	- degree(s)	3000 K	118 lm/W	1,150 lm	
	LED11S/830					
	PSU-E C WH					
	PCC P					
912500100067	DN463B	- degree(s)	4000 K	123 lm/W	1,200 lm	
	LED11S/840					

Order Code	Full Product Name	Beam	Correlated	Luminous		
		angle of	Color	Efficacy		
Order Code	Name	Full Product	light	Temperature	(rated)	Luminous
Order Code	Name	source	(Nom)	(Nom)	Flux	
912500100518	DN461B	- degree(s)	3000 K	117 lm/W	1,200 lm	
	LED11S/830					
	PSU-E C WH P					
912500100519	DN461B	- degree(s)	4000 K	122 lm/W	1,250 lm	
	LED11S/840					
	PSU-E C WH P					
912500100538	DN461B	- degree(s)	3000 K	117 lm/W	1,200 lm	
	LED11S/830					
	PSU-E C ELP3					
	WH P					
912500100539	DN461B	- degree(s)	4000 K	122 lm/W	1,250 lm	
	LED11S/840					
	PSU-E C ELP3					
	WH P					
912500103006	DN471C	88	3000 K	127 lm/W	2,100 lm	
	LED20S/830	degree(s)				
	DIA-VLC					
	D22H16 BK					
912500103009	DN471C	88	3000 K	125 lm/W	2,100 lm	
	LED20S/830	degree(s)				
	PSU D22H16 BK					
912500103012	DN471C	88	4000 K	133 lm/W	2,200 lm	
	LED20S/840	degree(s)				
	DIA-VLC					
	D22H16 BK					
912500103015	DN471C	88	4000 K	131 lm/W	2,200 lm	
	LED20S/840	degree(s)				
	PSU D22H16 BK					
912500103018	DN470P	120	3000 K	134 lm/W	2,200 lm	
	LED20S/830	degree(s)				
	DIA-VLC					
	D22H16 BK					
912500103021	DN470P	120	3000 K	132 lm/W	2,200 lm	
	LED20S/830	degree(s)				
	PSU D22H16 BK					
912500103024	DN470P	120	4000 K	140 lm/W	2,300 lm	
	LED20S/840	degree(s)				

Order Code	Name	Beam	Correlated	Luminous	
		angle of light source	Color (Nom)	Efficacy (rated) (Nom)	Flux
DIA-VLC					
D22H16 BK					
912500103027	DN470P	120	4000 K	138 lm/W	2,300 lm
LED20S/840	degree(s)				
PSU D22H16 BK					
912500102993	DN470C	120	3000 K	134 lm/W	2,200 lm
LED20S/830	degree(s)				
DIA-VLC					
D22H16 BK					
912500102996	DN470C	120	3000 K	132 lm/W	2,200 lm
LED20S/830	degree(s)				
PSU D22H16 BK					
912500102999	DN470C	120	4000 K	140 lm/W	2,300 lm
LED20S/840	degree(s)				
DIA-VLC					
D22H16 BK					
912500103003	DN470C	120	4000 K	138 lm/W	2,300 lm
LED20S/840	degree(s)				
PSU D22H16 BK					
910505102087	DN471B	- degree(s)	3000 K	117 lm/W	1,900 lm
LED20S/830					
WIA-E C WH P					
910505102089	DN471B	- degree(s)	4000 K	120 lm/W	1,950 lm
LED20S/840					
WIA-E C WH P					
910505102103	DN471B	- degree(s)	3000 K	93 lm/W	1,900 lm
LED20S/830					
DIA-VLC-E C					
ELP3 WH P					
910505102104	DN471B	- degree(s)	3000 K	120 lm/W	1,900 lm
LED20S/830					
DIA-VLC-E C					
WH P					
910505102105	DN471B	- degree(s)	4000 K	95 lm/W	1,950 lm
LED20S/840					
DIA-VLC-E C					
ELP3 WH P					
910505102106	DN471B	- degree(s)	4000 K	123 lm/W	1,950 lm
LED20S/840					
DIA-VLC-E C					
WH P					
910505102107	DN471B	- degree(s)	3000 K	104 lm/W	2,900 lm
LED30S/830					
DIA-VLC-E C					
ELP3 WH P					
910505102108	DN471B	- degree(s)	3000 K	123 lm/W	2,900 lm
LED30S/830					
DIA-VLC-E C					
WH P					

Order Code	Name	Beam	Correlated	Luminous	
		angle of light source	Color (Nom)	Efficacy (rated) (Nom)	Flux
910505102109	DN471B	- degree(s)	4000 K	104 lm/W	3,000 lm
LED30S/840					
DIA-VLC-E C					
ELP3 WH P					
910505102110	DN471B	- degree(s)	4000 K	128 lm/W	3,000 lm
LED30S/840					
DIA-VLC-E C					
WH P					
910505102118	DN473B	- degree(s)	3000 K	114 lm/W	1,800 lm
LED20S/830					
DIA-VLC-E C					
WH PCC P					
910505102119	DN473B	- degree(s)	4000 K	117 lm/W	1,850 lm
LED20S/840					
DIA-VLC-E C					
WH PCC P					
910505102120	DN473B	- degree(s)	3000 K	123 lm/W	2,900 lm
LED30S/830					
DIA-VLC-E C					
WH PCC P					
910505102121	DN473B	- degree(s)	4000 K	128 lm/W	3,000 lm
LED30S/840					
DIA-VLC-E C					
WH PCC P					
910505102290	DN471B	-	3000 K	125 lm/W	1,900 lm
LED20S/830					
PSD-E C WH P					
910505102291	DN471B	-	4000 K	128 lm/W	1,950 lm
LED20S/840					
PSD-E C WH P					
912500100074	DN473B	- degree(s)	3000 K	121 lm/W	1,850 lm
LED20S/830					
PSU-E C WH					
PCC P					
912500100075	DN473B	- degree(s)	4000 K	125 lm/W	1,900 lm
LED20S/840					
PSU-E C WH					
PCC P					
912500100526	DN471B	- degree(s)	3000 K	125 lm/W	1,900 lm
LED20S/830					
PSU-E C WH P					
912500100527	DN471B	- degree(s)	4000 K	131 lm/W	2,000 lm
LED20S/840					
PSU-E C WH P					
912500100550	DN471B	- degree(s)	3000 K	125 lm/W	1,900 lm
LED20S/830					
PSU-E C ELP3					
WH P					

Order Code	Name	Beam	Correlated	Luminous	
		angle of light	Color	Efficacy (rated)	Flux
Full Product	source	(Nom)	(Nom)		
912500100551	DN471B	- degree(s)	4000 K	131 lm/W	2,000 lm
	LED20S/840				
	PSU-E C ELP3				
	WH P				
912500101314	DN471B	- degree(s)	3000 K	124 lm/W	2,800 lm
	LED30S/830				
	PSU-E C WH P				
912500101315	DN471B	- degree(s)	4000 K	131 lm/W	2,950 lm
	LED30S/840				
	PSU-E C WH P				
912500101326	DN471B	- degree(s)	3000 K	124 lm/W	2,800 lm
	LED30S/830				
	PSU-E C ELP3				
	WH P				
912500101327	DN471B	- degree(s)	4000 K	131 lm/W	2,950 lm
	LED30S/840				
	PSU-E C ELP3				
	WH P				
910505102079	DN470B	- degree(s)	4000 K	118 lm/W	1,250 lm
	LED11S/840				
	DIA-VLC-E C				
	WH P				
910505102080	DN470B	- degree(s)	3000 K	93 lm/W	1,900 lm
	LED20S/830				
	DIA-VLC-E C				
	ELP3 WH P				
910505102081	DN470B	- degree(s)	3000 K	120 lm/W	1,900 lm
	LED20S/830				
	DIA-VLC-E C				
	WH P				
910505102082	DN470B	- degree(s)	4000 K	95 lm/W	1,950 lm
	LED20S/840				
	DIA-VLC-E C				
	ELP3 WH P				
910505102085	DN470B	- degree(s)	4000 K	120 lm/W	1,950 lm
	LED20S/840				
	WIA-E C WH P				
910505102091	DN472B	- degree(s)	3000 K	111 lm/W	1,800 lm
	LED20S/830				
	WIA-E C WH				
	PCC P				
910505102093	DN472B	- degree(s)	4000 K	114 lm/W	1,850 lm
	LED20S/840				
	WIA-E C WH				
	PCC P				
910505102098	DN470B	- degree(s)	3000 K	104 lm/W	2,900 lm
	LED30S/830				
	DIA-VLC-E C				
	ELP3 WH P				

Order Code	Name	Beam	Correlated	Luminous	
		angle of light	Color	Efficacy (rated)	Flux
Full Product	source	(Nom)	(Nom)		
910505102099	DN470B	- degree(s)	3000 K	123 lm/W	2,900 lm
	LED30S/830				
	DIA-VLC-E C				
	WH P				
910505102101	DN470B	- degree(s)	4000 K	104 lm/W	3,000 lm
	LED30S/840				
	DIA-VLC-E C				
	ELP3 WH P				
910505102102	DN470B	- degree(s)	4000 K	128 lm/W	3,000 lm
	LED30S/840				
	DIA-VLC-E C				
	WH P				
910505102111	DN472B	- degree(s)	3000 K	114 lm/W	1,800 lm
	LED20S/830				
	DIA-VLC-E C				
	WH PCC P				
910505102113	DN472B	- degree(s)	4000 K	117 lm/W	1,850 lm
	LED20S/840				
	DIA-VLC-E C				
	WH PCC P				
910505102115	DN472B	- degree(s)	3000 K	119 lm/W	2,800 lm
	LED30S/830				
	DIA-VLC-E C				
	WH PCC P				
910505102116	DN472B	- degree(s)	4000 K	123 lm/W	2,900 lm
	LED30S/840				
	DIA-VLC-E C				
	WH PCC P				
910505102147	DN470B	- degree(s)	3000 K	117 lm/W	1,900 lm
	LED20S/830				
	WIA-E C WH P				
910505102271	DN470B	-	3000 K	125 lm/W	1,900 lm
	LED20S/830				
	PSD-E C WH P				
910505102272	DN470B	-	3000 K	129 lm/W	2,900 lm
	LED30S/830				
	PSD-E C WH P				
910505102288	DN470B	-	4000 K	128 lm/W	1,950 lm
	LED20S/840				
	PSD-E C WH P				
910505102289	DN470B	-	4000 K	133 lm/W	3,000 lm
	LED30S/840				
	PSD-E C WH P				
912500100070	DN472B	- degree(s)	3000 K	125 lm/W	1,900 lm
	LED20S/830				
	PSU-E C WH				
	PCC P				
912500100071	DN472B	- degree(s)	4000 K	131 lm/W	2,000 lm
	LED20S/840				

Order Code	Name	Beam	Correlated	Luminous		Beam	Correlated	Luminous			
		angle of light	Color	Efficacy (rated)	Flux	angle of light	Color	Efficacy (rated)	Flux		
912500100522	DN470B	- degree(s)	3000 K	131 lm/W	2,000 lm	DIA-VLC					
	LED20S/830					D22H16 WH					
	PSU-E C WH P										
912500100523	DN470B	- degree(s)	4000 K	138 lm/W	2,100 lm	912500103023	DN470P	120	3000 K	132 lm/W	2,200 lm
	LED20S/840					LED20S/830	degree(s)				
	PSU-E C WH P					PSU D22H16					
912500100546	DN470B	- degree(s)	3000 K	131 lm/W	2,000 lm		WH				
	LED20S/830										
	PSU-E C ELP3										
	WH P										
912500100547	DN470B	- degree(s)	4000 K	138 lm/W	2,100 lm	912500103026	DN470P	120	4000 K	140 lm/W	2,300 lm
	LED20S/840					LED20S/840	degree(s)				
	PSU-E C ELP3					DIA-VLC					
	WH P					D22H16 WH					
912500101305	DN470B	- degree(s)	3000 K	128 lm/W	2,900 lm	912500103029	DN470P	120	4000 K	138 lm/W	2,300 lm
	LED30S/830					LED20S/840	degree(s)				
	PSU-E C WH P					PSU D22H16					
912500101307	DN470B	- degree(s)	4000 K	137 lm/W	3,100 lm		WH				
	LED30S/840										
	PSU-E C WH P										
912500101322	DN470B	- degree(s)	3000 K	128 lm/W	2,900 lm	910505102033	DN460B	- degree(s)	3000 K	79 lm/W	1,200 lm
	LED30S/830					LED11S/830					
	PSU-E C ELP3					DIA-VLC-E C					
	WH P					ELP3 WH P					
912500101323	DN470B	- degree(s)	4000 K	137 lm/W	3,100 lm	910505102034	DN460B	- degree(s)	3000 K	114 lm/W	1,200 lm
	LED30S/840					LED11S/830					
	PSU-E C ELP3					DIA-VLC-E C					
	WH P					WH P					
912500103008	DN471C	88	3000 K	127 lm/W	2,100 lm	910505102035	DN460B	- degree(s)	4000 K	118 lm/W	1,250 lm
	LED20S/830	degree(s)				LED11S/840					
	DIA-VLC					DIA-VLC-E C					
	D22H16 WH					WH P					
912500103011	DN471C	88	3000 K	125 lm/W	2,100 lm	910505102036	DN460B	- degree(s)	4000 K	122 lm/W	2,200 lm
	LED20S/830	degree(s)				LED20S/840					
	PSU D22H16					DIA-VLC-E C					
	WH					WH P					
912500103014	DN471C	88	4000 K	133 lm/W	2,200 lm	910505102072	DN462B	- degree(s)	3000 K	109 lm/W	1,150 lm
	LED20S/840	degree(s)				LED11S/830					
	DIA-VLC					DIA-VLC-E C					
	D22H16 WH					WH PCC P					
912500103017	DN471C	88	4000 K	131 lm/W	2,200 lm	910505102074	DN462B	- degree(s)	4000 K	114 lm/W	1,200 lm
	LED20S/840	degree(s)				LED11S/840					
	PSU D22H16					DIA-VLC-E C					
	WH					WH PCC P					
912500103020	DN470P	120	3000 K	134 lm/W	2,200 lm	910505102284	DN460B	-	3000 K	125 lm/W	1,200 lm
	LED20S/830	degree(s)				LED11S/830					
	PSU-E C WH					PSD-E C WH P					
	PCC P										

Order Code	Name	Beam	Correlated	Luminous	
		angle of light	Color	Efficacy (rated)	Flux
Full Product	source	(Nom)	(Nom)		
912500100063	DN462B	- degree(s)	4000 K	128 lm/W	1,250 lm
	LED11S/840				
	PSU-E C PCC				
	WH P				
912500100514	DN460B	- degree(s)	3000 K	122 lm/W	1,250 lm
	LED11S/830				
	PSU-E C WH P				
912500100515	DN460B	- degree(s)	4000 K	127 lm/W	1,300 lm
	LED11S/840				
	PSU-E C WH P				
912500100534	DN460B	- degree(s)	3000 K	122 lm/W	1,250 lm
	LED11S/830				
	PSU-E C ELP3				
	WH P				
912500100535	DN460B	- degree(s)	4000 K	127 lm/W	1,300 lm
	LED11S/840				
	PSU-E C ELP3				
	WH P				
910505102073	DN462B	- degree(s)	3000 K	104 lm/W	1,100 lm
	LED11S/830				
	DIA-VLC-E C				
	WH PCO P				
910505102075	DN462B	- degree(s)	4000 K	109 lm/W	1,150 lm
	LED11S/840				
	DIA-VLC-E C				
	WH PCO P				
912500100530	DN462B	- degree(s)	3000 K	113 lm/W	1,100 lm
	LED11S/830				
	PSU-E C WH				
	PCO P				
912500100531	DN462B	- degree(s)	4000 K	118 lm/W	1,150 lm
	LED11S/840				
	PSU-E C WH				
	PCO P				
910505102112	DN472B	- degree(s)	3000 K	108 lm/W	1,700 lm
	LED20S/830				
	DIA-VLC-E C				
	WH PCO P				
910505102114	DN472B	- degree(s)	4000 K	111 lm/W	1,750 lm
	LED20S/840				
	DIA-VLC-E C				
	WH PCO P				
910505102292	DN472B	-	3000 K	109 lm/W	1,050 lm
	LED11S/830				
	PSU-E C WH				
	PCO P				
910505102293	DN472B	-	4000 K	114 lm/W	1,100 lm
	LED11S/840				

Order Code	Name	Beam	Correlated	Luminous	
		angle of light	Color	Efficacy (rated)	Flux
Full Product	source	(Nom)	(Nom)		
912500100542	PSD-E C WH	- degree(s)	3000 K	106 lm/W	2,050 lm
	PCO P				
912500100543	DN472B	- degree(s)	4000 K	109 lm/W	2,100 lm
	LED20S/840				
	PSU-E C WH				
	PCO P				
912500103030	DN470T	120	3000 K	134 lm/W	2,200 lm
	LED20S/830	degree(s)			
	DIA-VLC				
	D22H16 5C6 GR				
912500103032	DN470T	120	4000 K	140 lm/W	2,300 lm
	LED20S/840	degree(s)			
	DIA-VLC				
	D22H16 5C6 GR				
912500103034	DN470T	120	3000 K	132 lm/W	2,200 lm
	LED20S/830	degree(s)			
	PSU D22H16 3C				
	GR				
912500103036	DN470T	120	4000 K	138 lm/W	2,300 lm
	LED20S/840	degree(s)			
	PSU D22H16 3C				
	GR				
912500102994	DN470C	120	3000 K	134 lm/W	2,200 lm
	LED20S/830	degree(s)			
	DIA-VLC				
	D22H16 GR				
912500102997	DN470C	120	3000 K	132 lm/W	2,200 lm
	LED20S/830	degree(s)			
	PSU D22H16 GR				
912500103001	DN470C	120	4000 K	140 lm/W	2,300 lm
	LED20S/840	degree(s)			
	DIA-VLC				
	D22H16 GR				
912500103004	DN470C	120	4000 K	138 lm/W	2,300 lm
	LED20S/840	degree(s)			
	PSU D22H16 GR				
912500102995	DN470C	120	3000 K	134 lm/W	2,200 lm
	LED20S/830	degree(s)			
	DIA-VLC				
	D22H16 WH				
912500102998	DN470C	120	3000 K	132 lm/W	2,200 lm
	LED20S/830	degree(s)			
	PSU D22H16				
	WH				

Order Code	Full Product Name	Beam angle of light		Correlated Color		Luminous Efficacy (rated)		Luminous Flux (Nom)	
		source	(Nom)	Temperature	(Nom)	Luminous Flux	(Nom)	Flux	(Nom)
912500103002	DN470C	120	4000 K	140 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	DIA-VLC								
	D22H16 WH								
912500103005	DN470C	120	4000 K	138 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	PSU D22H16								
	WH								
912500100267	DN470T	120	3000 K	132 lm/W	2,200 lm				
	LED20S/830	degree(s)							
	PSU D22H16 3C								
	BK								
912500100268	DN470T	120	4000 K	138 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	PSU D22H16 3C								
	BK								
912500100269	DN470T	120	3000 K	134 lm/W	2,200 lm				
	LED20S/830	degree(s)							
	DIA-VLC								
	D22H16 5C6 BK								
912500100270	DN470T	120	4000 K	140 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	DIA-VLC								
	D22H16 5C6 BK								
912500103019	DN470P	120	3000 K	134 lm/W	2,200 lm				
	LED20S/830	degree(s)							
	DIA-VLC								
	D22H16 GR								
912500103022	DN470P	120	3000 K	132 lm/W	2,200 lm				
	LED20S/830	degree(s)							
	PSU D22H16 GR								
912500103025	DN470P	120	4000 K	140 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	DIA-VLC								
	D22H16 GR								

Order Code	Full Product Name	Beam angle of light		Correlated Color		Luminous Efficacy (rated)		Luminous Flux (Nom)	
		source	(Nom)	Temperature	(Nom)	Luminous Flux	(Nom)	Flux	(Nom)
912500103028	DN470P	120	4000 K	138 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	PSU D22H16 GR								
912500103007	DN471C	88	3000 K	127 lm/W	2,100 lm				
	LED20S/830	degree(s)							
	DIA-VLC								
	D22H16 GR								
912500103010	DN471C	88	3000 K	125 lm/W	2,100 lm				
	LED20S/830	degree(s)							
	PSU D22H16 GR								
912500103013	DN471C	88	4000 K	133 lm/W	2,200 lm				
	LED20S/840	degree(s)							
	DIA-VLC								
	D22H16 GR								
912500103016	DN471C	88	4000 K	131 lm/W	2,200 lm				
	LED20S/840	degree(s)							
	PSU D22H16 GR								
912500103031	DN470T	120	3000 K	134 lm/W	2,200 lm				
	LED20S/830	degree(s)							
	DIA-VLC								
	D22H16 5C6								
	WH								
912500103033	DN470T	120	4000 K	140 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	DIA-VLC								
	D22H16 5C6								
	WH								
912500103035	DN470T	120	3000 K	132 lm/W	2,200 lm				
	LED20S/830	degree(s)							
	PSU D22H16 3C								
	WH								
912500103037	DN470T	120	4000 K	138 lm/W	2,300 lm				
	LED20S/840	degree(s)							
	PSU D22H16 3C								
	WH								

Light Technical (2/2)

Order Code	Full Product Name	Flickering			
		value	(PstLM) -	Flickering	Number of light sources
		EN	value as per EN	Stroboscopic effect visibility	measure (SVM)
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	-	-	-	61000-3-3
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	-	-	-	61000-3-3

Order Code	Full Product Name	Flickering			
		value	(PstLM) -	Flickering	Number of light sources
		EN	value as per EN	Stroboscopic effect visibility	measure (SVM)
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	-	-	-	61000-3-3
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	-	-	0.4	61000-3-3

Order Code	Full Product Name	Flickering		
		Number of light sources	value as per EN	Stroboscopic effect visibility measure (SVM)
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	-	-	-
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	-	-	-
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	-	-	-
910505102286	DN461B LED11S/830 PSD-E C WH P	-	-	0.4
910505102287	DN461B LED11S/840 PSD-E C WH P	-	-	0.4
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	1	-	-
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	1	-	-
912500100518	DN461B LED11S/830 PSU-E C WH P	1	-	-
912500100519	DN461B LED11S/840 PSU-E C WH P	1	-	-
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	1	-	-
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	1	-	-
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	-	1	0.4
912500103009	DN471C LED20S/830 PSU-D22H16 BK	-	1	0.4
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	-	1	0.4
912500103015	DN471C LED20S/840 PSU-D22H16 BK	-	1	0.4
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	-	1	0.4
912500103021	DN470P LED20S/830 PSU-D22H16 BK	-	1	0.4
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	-	1	0.4
912500103027	DN470P LED20S/840 PSU-D22H16 BK	-	1	0.4
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	-	1	0.4
912500102996	DN470C LED20S/830 PSU-D22H16 BK	-	1	0.4
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	-	1	0.4
912500103003	DN470C LED20S/840 PSU-D22H16 BK	-	1	0.4

Order Code	Full Product Name	Flickering		
		Number of light sources	value as per EN	Stroboscopic effect visibility measure (SVM)
910505102087	DN471B LED20S/830 WIA-E C WH P	-	-	-
910505102089	DN471B LED20S/840 WIA-E C WH P	-	-	-
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	-	-	-
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	-	-	-
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	-	-	-
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	-	-	-
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	-	-	-
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	-	-	-
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	-	-	-
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	-	-	-
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	-	-	-
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	-	-	-
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	-	-	-
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	-	-	-
910505102290	DN471B LED20S/830 PSD-E C WH P	-	-	0.4
910505102291	DN471B LED20S/840 PSD-E C WH P	-	-	0.4
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	1	-	-
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	1	-	-
912500100526	DN471B LED20S/830 PSU-E C WH P	1	-	-
912500100527	DN471B LED20S/840 PSU-E C WH P	1	-	-
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	1	-	-
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	1	-	-
912500101314	DN471B LED30S/830 PSU-E C WH P	1	-	-

Order Code	Full Product Name	Flickering		
		Number of light sources	value as per EN	Stroboscopic effect visibility measure (SVM)
912500101315	DN471B LED30S/840 PSU- E C WH P	-	-	-
912500101326	DN471B LED30S/830 PSU- E C ELP3 WH P	-	-	-
912500101327	DN471B LED30S/840 PSU- E C ELP3 WH P	-	-	-
910505102079	DN470B LED11S/840 DIA- VLC-E C WH P	-	-	-
910505102080	DN470B LED20S/830 DIA- VLC-E C ELP3 WH P	-	-	-
910505102081	DN470B LED20S/830 DIA- VLC-E C WH P	-	-	0.4
910505102082	DN470B LED20S/840 DIA- VLC-E C ELP3 WH P	-	-	-
910505102085	DN470B LED20S/840 WIA- E C WH P	-	-	-
910505102091	DN472B LED20S/830 WIA- E C WH PCC P	-	-	-
910505102093	DN472B LED20S/840 WIA- E C WH PCC P	-	-	-
910505102098	DN470B LED30S/830 DIA- VLC-E C ELP3 WH P	-	-	-
910505102099	DN470B LED30S/830 DIA- VLC-E C WH P	-	-	-
910505102101	DN470B LED30S/840 DIA- VLC-E C ELP3 WH P	-	-	-
910505102102	DN470B LED30S/840 DIA- VLC-E C WH P	-	-	-
910505102111	DN472B LED20S/830 DIA- VLC-E C WH PCC P	-	-	-
910505102113	DN472B LED20S/840 DIA- VLC-E C WH PCC P	-	-	-
910505102115	DN472B LED30S/830 DIA- VLC-E C WH PCC P	-	-	-
910505102116	DN472B LED30S/840 DIA- VLC-E C WH PCC P	-	-	-
910505102147	DN470B LED20S/830 WIA- E C WH P	-	-	-
910505102271	DN470B LED20S/830 PSD-E C WH P	-	-	0.4
910505102272	DN470B LED30S/830 PSD-E C WH P	-	-	0.4
910505102288	DN470B LED20S/840 PSD-E C WH P	-	-	0.4
910505102289	DN470B LED30S/840 PSD-E C WH P	-	-	0.4

Order Code	Full Product Name	Flickering		
		Number of light sources	value as per EN	Stroboscopic effect visibility measure (SVM)
912500100070	DN472B LED20S/830 PSU- E C WH PCC P	1	-	-
912500100071	DN472B LED20S/840 PSU- E C WH PCC P	1	-	-
912500100522	DN470B LED20S/830 PSU-E C WH P	1	-	-
912500100523	DN470B LED20S/840 PSU-E C WH P	1	-	-
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	1	-	-
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	1	-	-
912500101305	DN470B LED30S/830 PSU-E C WH P	-	-	-
912500101307	DN470B LED30S/840 PSU-E C WH P	-	-	-
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	-	-	-
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	-	-	-
912500103008	DN471C LED20S/830 DIA- VLC D22H16 WH	-	1	0.4
912500103011	DN471C LED20S/830 PSU D22H16 WH	-	1	0.4
912500103014	DN471C LED20S/840 DIA- VLC D22H16 WH	-	1	0.4
912500103017	DN471C LED20S/840 PSU D22H16 WH	-	1	0.4
912500103020	DN470P LED20S/830 DIA- VLC D22H16 WH	-	1	0.4
912500103023	DN470P LED20S/830 PSU D22H16 WH	-	1	0.4
912500103026	DN470P LED20S/840 DIA- VLC D22H16 WH	-	1	0.4
912500103029	DN470P LED20S/840 PSU D22H16 WH	-	1	0.4
910505102033	DN460B LED11S/830 DIA- VLC-E C ELP3 WH P	-	-	-
910505102034	DN460B LED11S/830 DIA- VLC-E C WH P	-	-	0.4
910505102035	DN460B LED11S/840 DIA- VLC-E C WH P	-	-	-
910505102036	DN460B LED20S/840 DIA- VLC-E C WH P	-	-	-
910505102072	DN462B LED11S/830 DIA- VLC-E C WH PCC P	-	-	-

Order Code	Full Product Name	Flickering		
		Number of light sources	value as per EN	Stroboscopic effect visibility measure (SVM)
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	-	-
910505102284	DN460B LED11S/830 PSD-E C WH P	-	-	0.4
910505102285	DN460B LED11S/840 PSD-E C WH P	-	-	0.4
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	1	-	-
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	1	-	-
912500100514	DN460B LED11S/830 PSU-E C WH P	1	-	0.4
912500100515	DN460B LED11S/840 PSU-E C WH P	1	-	-
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	1	-	-
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	1	-	-
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	-	-	-
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	-	-	-
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	1	-	-
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	1	-	-
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	-	-	-
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	-	-	-
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	-	-	0.4
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	-	-	0.4
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	1	-	-
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	1	-	-
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	-	1	0.4
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	-	1	0.4
912500103034	DN470T LED20S/830 PSU-D22H16 3C GR	-	1	0.4
912500103036	DN470T LED20S/840 PSU-D22H16 3C GR	-	1	0.4
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	-	1	0.4

Order Code	Full Product Name	Flickering		
		Number of light sources	value as per EN	Stroboscopic effect visibility measure (SVM)
912500102997	DN470C LED20S/830 PSU-D22H16 GR	-	1	0.4
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	-	1	0.4
912500103004	DN470C LED20S/840 PSU-D22H16 GR	-	1	0.4
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	-	1	0.4
912500102998	DN470C LED20S/830 PSU-D22H16 WH	-	1	0.4
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	-	1	0.4
912500103005	DN470C LED20S/840 PSU-D22H16 WH	-	1	0.4
912500100267	DN470T LED20S/830 PSU-D22H16 3C BK	1	1	0.4
912500100268	DN470T LED20S/840 PSU-D22H16 3C BK	1	1	0.4
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	1	1	0.4
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	1	1	0.4
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	-	1	0.4
912500103022	DN470P LED20S/830 PSU-D22H16 GR	-	1	0.4
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	-	1	0.4
912500103028	DN470P LED20S/840 PSU-D22H16 GR	-	1	0.4
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	-	1	0.4
912500103010	DN471C LED20S/830 PSU-D22H16 GR	-	1	0.4
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	-	1	0.4
912500103016	DN471C LED20S/840 PSU-D22H16 GR	-	1	0.4
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	-	1	0.4
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	-	1	0.4
912500103035	DN470T LED20S/830 PSU-D22H16 3C WH	-	1	0.4
912500103037	DN470T LED20S/840 PSU-D22H16 3C WH	-	1	0.4

Operating and Electrical

Power				
Order Code	Full Product Name	Input Voltage	Consumption	
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	220-240 V	15.2 W	
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	220-240 V	10.6 W	
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	220-240 V	15.2 W	
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	220-240 V	10.6 W	
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	220-240 V	18 W	
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	220-240 V	10.6 W	
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	220-240 V	10.6 W	
910505102286	DN461B LED11S/830 PSD-E C WH P	220-240 V	9.6 W	
910505102287	DN461B LED11S/840 PSD-E C WH P	220-240 V	9.6 W	
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	220 to 240 V	9.7 W	
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	220 to 240 V	9.7 W	
912500100518	DN461B LED11S/830 PSU-E C WH P	220-240 V	10.2 W	
912500100519	DN461B LED11S/840 PSU-E C WH P	220-240 V	10.2 W	
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	220-240 V	10.2 W	
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	220-240 V	10.2 W	
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	220 to 240 V	16.2 W	
912500103009	DN471C LED20S/830 PSU D22H16 BK	220 to 240 V	16.4 W	
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	220 to 240 V	16.2 W	
912500103015	DN471C LED20S/840 PSU D22H16 BK	220 to 240 V	16.4 W	
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	220 to 240 V	16.2 W	
912500103021	DN470P LED20S/830 PSU D22H16 BK	220 to 240 V	16.4 W	
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	220 to 240 V	16.2 W	
912500103027	DN470P LED20S/840 PSU D22H16 BK	220 to 240 V	16.4 W	
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	220 to 240 V	16.2 W	
912500102996	DN470C LED20S/830 PSU D22H16 BK	220 to 240 V	16.4 W	
Power				
Order Code	Full Product Name	Input Voltage	Consumption	
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	220 to 240 V	16.2 W	
912500103003	DN470C LED20S/840 PSU D22H16 BK	220 to 240 V	16.4 W	
910505102087	DN471B LED20S/830 WIA-E C WH P	220-240 V	16.2 W	
910505102089	DN471B LED20S/840 WIA-E C WH P	220-240 V	16.2 W	
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	220-240 V	20.5 W	
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	220-240 V	15.8 W	
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	220-240 V	20.5 W	
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	220-240 V	15.8 W	
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	220-240 V	28 W	
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	220-240 V	23.5 W	
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	220-240 V	28 W	
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	220-240 V	23.5 W	
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	220-240 V	15.8 W	
910505102119	DN473B LED20S/840 DIA-VLC-E C C WH PCC P	220-240 V	15.8 W	
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	220-240 V	23.5 W	
910505102121	DN473B LED30S/840 DIA-VLC-E C C WH PCC P	220-240 V	23.5 W	
910505102290	DN471B LED20S/830 PSD-E C WH P	220-240 V	15.2 W	
910505102291	DN471B LED20S/840 PSD-E C WH P	220-240 V	15.2 W	
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	220 to 240 V	15.2 W	
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	220 to 240 V	15.2 W	
912500100526	DN471B LED20S/830 PSU-E C WH P	220-240 V	15.2 W	
912500100527	DN471B LED20S/840 PSU-E C WH P	220-240 V	15.2 W	
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	220-240 V	15.2 W	
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	220-240 V	15.2 W	
912500101314	DN471B LED30S/830 PSU-E C WH P	220-240 V	22.5 W	

Power				
Order Code	Full Product Name	Input Voltage	Consumption	
912500101315	DN471B LED30S/840 PSU-E C WH P	220-240 V	22.5 W	
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	220-240 V	22.5 W	
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	220-240 V	22.5 W	
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	220-240 V	10.6 W	
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	220-240 V	20.5 W	
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	220-240 V	15.8 W	
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	220-240 V	20.5 W	
910505102085	DN470B LED20S/840 WIA-E C WH P	220-240 V	16.2 W	
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	220-240 V	16.2 W	
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	220-240 V	16.2 W	
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	220-240 V	28 W	
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	220-240 V	23.5 W	
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	220-240 V	28 W	
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	220-240 V	23.5 W	
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	220-240 V	15.8 W	
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	220-240 V	15.8 W	
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	220-240 V	23.5 W	
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	220-240 V	23.5 W	
910505102147	DN470B LED20S/830 WIA-E C WH P	220-240 V	16.2 W	
910505102271	DN470B LED20S/830 PSD-E C WH P	220-240 V	15.2 W	
910505102272	DN470B LED30S/830 PSD-E C WH P	220-240 V	22.5 W	
910505102288	DN470B LED20S/840 PSD-E C WH P	220-240 V	15.2 W	
910505102289	DN470B LED30S/840 PSD-E C WH P	220-240 V	22.5 W	
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	220 to 240 V	15.2 W	
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	220 to 240 V	15.2 W	
Power				
Order Code	Full Product Name	Input Voltage	Consumption	
912500100522	DN470B LED20S/830 PSU-E C WH P	220-240 V	15.2 W	
912500100523	DN470B LED20S/840 PSU-E C WH P	220-240 V	15.2 W	
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	220-240 V	15.2 W	
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	220-240 V	15.2 W	
912500101305	DN470B LED30S/830 PSU-E C WH P	220-240 V	22.5 W	
912500101307	DN470B LED30S/840 PSU-E C WH P	220-240 V	22.5 W	
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	220-240 V	22.5 W	
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	220-240 V	22.5 W	
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	220 to 240 V	16.2 W	
912500103011	DN471C LED20S/830 PSU D22H16 WH	220 to 240 V	16.4 W	
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	220 to 240 V	16.2 W	
912500103017	DN471C LED20S/840 PSU D22H16 WH	220 to 240 V	16.4 W	
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	220 to 240 V	16.2 W	
912500103023	DN470P LED20S/830 PSU D22H16 WH	220 to 240 V	16.4 W	
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	220 to 240 V	16.2 W	
912500103029	DN470P LED20S/840 PSU D22H16 WH	220 to 240 V	16.4 W	
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	220-240 V	15.2 W	
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	220-240 V	10.6 W	
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	220-240 V	10.6 W	
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	220-240 V	18 W	
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	220-240 V	10.6 W	
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	220-240 V	10.6 W	
910505102284	DN460B LED11S/830 PSD-E C WH P	220-240 V	9.6 W	
910505102285	DN460B LED11S/840 PSD-E C WH P	220-240 V	9.6 W	
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	220 to 240 V	9.7 W	

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	220 to 240 V	9.7 W
912500100514	DN460B LED11S/830 PSU-E C WH P	220-240 V	10.2 W
912500100515	DN460B LED11S/840 PSU-E C WH P	220-240 V	10.2 W
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	220-240 V	10.2 W
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	220-240 V	10.2 W
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	220-240 V	10.6 W
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	220-240 V	10.6 W
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	220-240 V	9.7 W
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	220-240 V	9.7 W
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	220-240 V	15.8 W
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	220-240 V	15.8 W
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	220-240 V	9.6 W
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	220-240 V	9.6 W
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	220-240 V	19.2 W
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	220-240 V	19.2 W
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	220 to 240 V	16.2 W
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	220 to 240 V	16.2 W
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	220 to 240 V	16.4 W
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	220 to 240 V	16.4 W
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	220 to 240 V	16.2 W
912500102997	DN470C LED20S/830 PSU D22H16 GR	220 to 240 V	16.4 W
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	220 to 240 V	16.2 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
912500103004	DN470C LED20S/840 PSU D22H16 GR	220 to 240 V	16.4 W
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	220 to 240 V	16.2 W
912500102998	DN470C LED20S/830 PSU D22H16 WH	220 to 240 V	16.4 W
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	220 to 240 V	16.2 W
912500103005	DN470C LED20S/840 PSU D22H16 WH	220 to 240 V	16.4 W
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	220 to 240 V	16.4 W
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	220 to 240 V	16.4 W
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	220 to 240 V	16.2 W
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	220 to 240 V	16.2 W
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	220 to 240 V	16.2 W
912500103022	DN470P LED20S/830 PSU D22H16 GR	220 to 240 V	16.4 W
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	220 to 240 V	16.2 W
912500103028	DN470P LED20S/840 PSU D22H16 GR	220 to 240 V	16.4 W
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	220 to 240 V	16.2 W
912500103010	DN471C LED20S/830 PSU D22H16 GR	220 to 240 V	16.4 W
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	220 to 240 V	16.2 W
912500103016	DN471C LED20S/840 PSU D22H16 GR	220 to 240 V	16.4 W
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	220 to 240 V	16.2 W
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	220 to 240 V	16.2 W
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	220 to 240 V	16.4 W
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	220 to 240 V	16.4 W

Temperature

Order Code	Full Product Name	Ambient temperature range
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	+10 to +40 °C

Order Code	Full Product Name	Ambient temperature range
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	+10 to +40 °C

Order Code	Full Product Name	Ambient temperature range	Order Code	Full Product Name	Ambient temperature range
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	+10 to +40 °C	910505102290	DN471B LED20S/830 PSD-E C WH P	+10 to +40 °C
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C	910505102291	DN471B LED20S/840 PSD-E C WH P	+10 to +40 °C
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C	912500100074	DN473B LED20S/830 PSU-E C WH PCC P	-15 to +40 °C
910505102286	DN461B LED11S/830 PSD-E C WH P	+10 to +40 °C	912500100075	DN473B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C
910505102287	DN461B LED11S/840 PSD-E C WH P	+10 to +40 °C	912500100526	DN471B LED20S/830 PSU-E C WH P	+10 to +40 °C
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	-15 to +40 °C	912500100527	DN471B LED20S/840 PSU-E C WH P	+10 to +40 °C
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	-15 to +40 °C	912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	+10 to +40 °C
912500100518	DN461B LED11S/830 PSU-E C WH P	+10 to +40 °C	912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	+10 to +40 °C
912500100519	DN461B LED11S/840 PSU-E C WH P	+10 to +40 °C	912500101314	DN471B LED30S/830 PSU-E C WH P	+10 to +40 °C
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	+10 to +40 °C	912500101315	DN471B LED30S/840 PSU-E C WH P	+10 to +40 °C
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	+10 to +40 °C	912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	+10 to +40 °C
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	+10 to +40 °C	912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C
912500103009	DN471C LED20S/830 PSU D22H16 BK	+10 to +40 °C	910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	+10 to +40 °C
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	+10 to +40 °C	910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
912500103015	DN471C LED20S/840 PSU D22H16 BK	+10 to +40 °C	910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	+10 to +40 °C
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	+10 to +40 °C	910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
912500103021	DN470P LED20S/830 PSU D22H16 BK	+10 to +40 °C	910505102085	DN470B LED20S/840 WIA-E C WH P	+10 to +40 °C
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	+10 to +40 °C	910505102091	DN472B LED20S/830 WIA-E C WH PCC P	+10 to +40 °C
912500103027	DN470P LED20S/840 PSU D22H16 BK	+10 to +40 °C	910505102093	DN472B LED20S/840 WIA-E C WH PCC P	+10 to +40 °C
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	+10 to +40 °C	910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
912500102996	DN470C LED20S/830 PSU D22H16 BK	+10 to +40 °C	910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	+10 to +40 °C
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	+10 to +40 °C	910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
912500103003	DN470C LED20S/840 PSU D22H16 BK	+10 to +40 °C	910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C
910505102087	DN471B LED20S/830 WIA-E C WH P	+10 to +40 °C	910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C
910505102089	DN471B LED20S/840 WIA-E C WH P	+10 to +40 °C	910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	+10 to +40 °C	910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	910505102147	DN470B LED20S/830 WIA-E C WH P	+10 to +40 °C
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	+10 to +40 °C	910505102271	DN470B LED20S/830 PSD-E C WH P	+10 to +40 °C
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	910505102272	DN470B LED30S/830 PSD-E C WH P	+10 to +40 °C
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	+10 to +40 °C	910505102288	DN470B LED20S/840 PSD-E C WH P	+10 to +40 °C
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	910505102289	DN470B LED30S/840 PSD-E C WH P	+10 to +40 °C
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C	912500100070	DN472B LED20S/830 PSU-E C WH PCC P	-15 to +40 °C
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C	912500100071	DN472B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C	912500100522	DN470B LED20S/830 PSU-E C WH P	+10 to +40 °C
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C	912500100523	DN470B LED20S/840 PSU-E C WH P	+10 to +40 °C
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C	912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	+10 to +40 °C

Order Code	Full Product Name	Ambient temperature range
912500101305	DN470B LED30S/830 PSU-E C WH P	+10 to +40 °C
912500101307	DN470B LED30S/840 PSU-E C WH P	+10 to +40 °C
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	+10 to +40 °C
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	+10 to +40 °C
912500103011	DN471C LED20S/830 PSU D22H16 WH	+10 to +40 °C
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	+10 to +40 °C
912500103017	DN471C LED20S/840 PSU D22H16 WH	+10 to +40 °C
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	+10 to +40 °C
912500103023	DN470P LED20S/830 PSU D22H16 WH	+10 to +40 °C
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	+10 to +40 °C
912500103029	DN470P LED20S/840 PSU D22H16 WH	+10 to +40 °C
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	+10 to +40 °C
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	+10 to +40 °C
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	+10 to +40 °C
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C
910505102284	DN460B LED11S/830 PSD-E C WH P	+10 to +40 °C
910505102285	DN460B LED11S/840 PSD-E C WH P	+10 to +40 °C
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	-15 to +40 °C
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	-15 to +40 °C
912500100514	DN460B LED11S/830 PSU-E C WH P	+10 to +40 °C
912500100515	DN460B LED11S/840 PSU-E C WH P	+10 to +40 °C
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	+10 to +40 °C
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	+10 to +40 °C
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	+10 to +40 °C
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	+10 to +40 °C
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	-15 to +40 °C
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	-15 to +40 °C
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	+10 to +40 °C
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	+10 to +40 °C
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	+10 to +40 °C

Order Code	Full Product Name	Ambient temperature range
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	+10 to +40 °C
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	-15 to +40 °C
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	-15 to +40 °C
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	+10 to +40 °C
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	+10 to +40 °C
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	+10 to +40 °C
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	+10 to +40 °C
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	+10 to +40 °C
912500102997	DN470C LED20S/830 PSU D22H16 GR	+10 to +40 °C
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	+10 to +40 °C
912500103004	DN470C LED20S/840 PSU D22H16 GR	+10 to +40 °C
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	+10 to +40 °C
912500102998	DN470C LED20S/830 PSU D22H16 WH	+10 to +40 °C
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	+10 to +40 °C
912500103005	DN470C LED20S/840 PSU D22H16 WH	+10 to +40 °C
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	+10 to +40 °C
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	+10 to +40 °C
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	+10 to +40 °C
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	+10 to +40 °C
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	+10 to +40 °C
912500103022	DN470P LED20S/830 PSU D22H16 GR	+10 to +40 °C
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	+10 to +40 °C
912500103028	DN470P LED20S/840 PSU D22H16 GR	+10 to +40 °C
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	+10 to +40 °C
912500103010	DN471C LED20S/830 PSU D22H16 GR	+10 to +40 °C
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	+10 to +40 °C
912500103016	DN471C LED20S/840 PSU D22H16 GR	+10 to +40 °C
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	+10 to +40 °C
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	+10 to +40 °C
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	+10 to +40 °C
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	+10 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	Yes
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	Yes
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	Yes
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	Yes
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	Yes
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	Yes
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	Yes
910505102286	DN461B LED11S/830 PSD-E C WH P	Yes
910505102287	DN461B LED11S/840 PSD-E C WH P	Yes
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	No
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	No
912500100518	DN461B LED11S/830 PSU-E C WH P	No
912500100519	DN461B LED11S/840 PSU-E C WH P	No
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	No
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	No
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	Yes
912500103009	DN471C LED20S/830 PSU D22H16 BK	No
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	Yes
912500103015	DN471C LED20S/840 PSU D22H16 BK	No
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	Yes
912500103021	DN470P LED20S/830 PSU D22H16 BK	No
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	Yes
912500103027	DN470P LED20S/840 PSU D22H16 BK	No
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	Yes
912500102996	DN470C LED20S/830 PSU D22H16 BK	No
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	Yes
912500103003	DN470C LED20S/840 PSU D22H16 BK	No
910505102087	DN471B LED20S/830 WIA-E C WH P	Yes
910505102089	DN471B LED20S/840 WIA-E C WH P	Yes
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	Yes
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	Yes
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	Yes
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	Yes
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	Yes
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	Yes
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	Yes
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	Yes
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	Yes
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	Yes
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	Yes
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	Yes
910505102290	DN471B LED20S/830 PSD-E C WH P	Yes
910505102291	DN471B LED20S/840 PSD-E C WH P	Yes
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	No
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	No
912500100526	DN471B LED20S/830 PSU-E C WH P	No
912500100527	DN471B LED20S/840 PSU-E C WH P	No
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	No
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	No
912500101314	DN471B LED30S/830 PSU-E C WH P	No
912500101315	DN471B LED30S/840 PSU-E C WH P	No
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	No

Order Code	Full Product Name	Dimmable
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	No
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	Yes
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	Yes
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	Yes
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	Yes
910505102085	DN470B LED20S/840 WIA-E C WH P	Yes
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	Yes
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	Yes
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	Yes
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	Yes
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	Yes
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	Yes
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	Yes
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	Yes
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	Yes
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	Yes
910505102147	DN470B LED20S/830 WIA-E C WH P	Yes
910505102271	DN470B LED20S/830 PSD-E C WH P	Yes
910505102272	DN470B LED30S/830 PSD-E C WH P	Yes
910505102288	DN470B LED20S/840 PSD-E C WH P	Yes
910505102289	DN470B LED30S/840 PSD-E C WH P	Yes
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	No
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	No
912500100522	DN470B LED20S/830 PSU-E C WH P	No
912500100523	DN470B LED20S/840 PSU-E C WH P	No
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	No
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	No
912500101305	DN470B LED30S/830 PSU-E C WH P	No
912500101307	DN470B LED30S/840 PSU-E C WH P	No
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	No
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	No
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	Yes
912500103011	DN471C LED20S/830 PSU D22H16 WH	No
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	Yes
912500103017	DN471C LED20S/840 PSU D22H16 WH	No
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	Yes
912500103023	DN470P LED20S/830 PSU D22H16 WH	No
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	Yes
912500103029	DN470P LED20S/840 PSU D22H16 WH	No
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	Yes
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	Yes
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	Yes
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	Yes
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	Yes
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	Yes
910505102284	DN460B LED11S/830 PSD-E C WH P	Yes
910505102285	DN460B LED11S/840 PSD-E C WH P	Yes
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	No
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	No
912500100514	DN460B LED11S/830 PSU-E C WH P	No
912500100515	DN460B LED11S/840 PSU-E C WH P	No
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	No

Order Code	Full Product Name	Dimmable
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	No
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	Yes
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	Yes
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	No
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	No
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	Yes
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	Yes
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	Yes
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	Yes
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	No
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	No
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	Yes
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	No
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	No
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	No
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	Yes
912500102997	DN470C LED20S/830 PSU D22H16 GR	No
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	Yes
912500103004	DN470C LED20S/840 PSU D22H16 GR	No
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	Yes

Order Code	Full Product Name	Dimmable
912500102998	DN470C LED20S/830 PSU D22H16 WH	No
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	Yes
912500103005	DN470C LED20S/840 PSU D22H16 WH	No
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	No
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	No
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	Yes
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	No
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	Yes
912500103022	DN470P LED20S/830 PSU D22H16 GR	No
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	Yes
912500103028	DN470P LED20S/840 PSU D22H16 GR	No
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	Yes
912500103010	DN471C LED20S/830 PSU D22H16 GR	No
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	Yes
912500103016	DN471C LED20S/840 PSU D22H16 GR	No
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	Yes
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	No
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	No
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	White
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	White
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	White
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	White
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	White
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	White
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	White
910505102286	DN461B LED11S/830 PSD-E C WH P	White
910505102287	DN461B LED11S/840 PSD-E C WH P	White
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	White
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	White
912500100518	DN461B LED11S/830 PSU-E C WH P	White
912500100519	DN461B LED11S/840 PSU-E C WH P	White
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	White
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	White
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	Black
912500103009	DN471C LED20S/830 PSU D22H16 BK	Black
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	Black
912500103015	DN471C LED20S/840 PSU D22H16 BK	Black
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	Black
912500103021	DN470P LED20S/830 PSU D22H16 BK	Black
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	Black
912500103027	DN470P LED20S/840 PSU D22H16 BK	Black
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	Black
912500102996	DN470C LED20S/830 PSU D22H16 BK	Black
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	Black
912500103003	DN470C LED20S/840 PSU D22H16 BK	Black
910505102087	DN471B LED20S/830 WIA-E C WH P	White

Order Code	Full Product Name	Housing Color
910505102089	DN471B LED20S/840 WIA-E C WH P	White
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	White
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	White
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	White
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	White
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	White
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	White
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	White
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	White
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	White
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	White
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	White
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	White
910505102290	DN471B LED20S/830 PSD-E C WH P	White
910505102291	DN471B LED20S/840 PSD-E C WH P	White
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	White
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	White
912500100526	DN471B LED20S/830 PSU-E C WH P	White
912500100527	DN471B LED20S/840 PSU-E C WH P	White
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	White
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	White
912500101314	DN471B LED30S/830 PSU-E C WH P	White
912500101315	DN471B LED30S/840 PSU-E C WH P	White
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	White
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	White
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	White
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	White
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	White

Order Code	Full Product Name	Housing Color
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	White
910505102085	DN470B LED20S/840 WIA-E C WH P	White
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	White
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	White
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	White
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	White
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	White
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	White
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	White
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	White
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	White
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	White
910505102147	DN470B LED20S/830 WIA-E C WH P	White
910505102271	DN470B LED20S/830 PSD-E C WH P	White
910505102272	DN470B LED30S/830 PSD-E C WH P	White
910505102288	DN470B LED20S/840 PSD-E C WH P	White
910505102289	DN470B LED30S/840 PSD-E C WH P	White
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	White
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	White
912500100522	DN470B LED20S/830 PSU-E C WH P	White
912500100523	DN470B LED20S/840 PSU-E C WH P	White
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	White
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	White
912500101305	DN470B LED30S/830 PSU-E C WH P	White
912500101307	DN470B LED30S/840 PSU-E C WH P	White
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	White
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	White
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	White
912500103011	DN471C LED20S/830 PSU D22H16 WH	White
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	White
912500103017	DN471C LED20S/840 PSU D22H16 WH	White
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	White
912500103023	DN470P LED20S/830 PSU D22H16 WH	White
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	White
912500103029	DN470P LED20S/840 PSU D22H16 WH	White
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	White
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	White
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	White
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	White
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	White
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	White
910505102284	DN460B LED11S/830 PSD-E C WH P	White
910505102285	DN460B LED11S/840 PSD-E C WH P	White
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	White

Order Code	Full Product Name	Housing Color
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	White
912500100514	DN460B LED11S/830 PSU-E C WH P	White
912500100515	DN460B LED11S/840 PSU-E C WH P	White
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	White
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	White
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	White
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	White
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	White
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	White
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	White
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	White
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	White
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	White
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	White
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	White
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	Gray
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	Gray
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	Gray
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	Gray
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	Gray
912500102997	DN470C LED20S/830 PSU D22H16 GR	Gray
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	Gray
912500103004	DN470C LED20S/840 PSU D22H16 GR	Gray
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	White
912500102998	DN470C LED20S/830 PSU D22H16 WH	White
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	White
912500103005	DN470C LED20S/840 PSU D22H16 WH	White
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	Black
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	Black
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	Black
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	Black
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	Gray
912500103022	DN470P LED20S/830 PSU D22H16 GR	Gray
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	Gray
912500103028	DN470P LED20S/840 PSU D22H16 GR	Gray
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	Gray
912500103010	DN471C LED20S/830 PSU D22H16 GR	Gray
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	Gray
912500103016	DN471C LED20S/840 PSU D22H16 GR	Gray
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	White
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	White
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	White
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	White

Approval and Application

Order Code	Full Product Name	Mech. impact	Ingress
		protection	protection
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3	IK02	IP20
	WH P		

Order Code	Full Product Name	Mech. impact	Ingress
		protection	protection
910505102038	DN461B LED11S/830 DIA-VLC-E C WH	IK02	IP20
	P		

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	IK02	IP20
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	IK02	IP20
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	IK02	IP20
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	IK02	IP20
910505102286	DN461B LED11S/830 PSD-E C WH P	IK02	IP20
910505102287	DN461B LED11S/840 PSD-E C WH P	IK02	IP20
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	IK06	IP54
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	IK06	IP54
912500100518	DN461B LED11S/830 PSU-E C WH P	IK02	IP20
912500100519	DN461B LED11S/840 PSU-E C WH P	IK02	IP20
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	IK02	IP20
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	IK02	IP20
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	IK02	IP20
912500103009	DN471C LED20S/830 PSU D22H16 BK	IK02	IP20
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	IK02	IP20
912500103015	DN471C LED20S/840 PSU D22H16 BK	IK02	IP20
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	IK02	IP20
912500103021	DN470P LED20S/830 PSU D22H16 BK	IK02	IP20
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	IK02	IP20
912500103027	DN470P LED20S/840 PSU D22H16 BK	IK02	IP20
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	IK02	IP20
912500102996	DN470C LED20S/830 PSU D22H16 BK	IK02	IP20
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	IK02	IP20
912500103003	DN470C LED20S/840 PSU D22H16 BK	IK02	IP20
910505102087	DN471B LED20S/830 WIA-E C WH P	IK02	IP20
910505102089	DN471B LED20S/840 WIA-E C WH P	IK02	IP20
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	IK02	IP20
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	IK02	IP20

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102108	DN471B LED30S/840 DIA-VLC-E C WH P	IK02	IP20
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	IK02	IP20
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	IK02	IP54
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	IK02	IP54
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	IK02	IP54
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	IK02	IP54
910505102290	DN471B LED20S/830 PSD-E C WH P	IK02	IP20
910505102291	DN471B LED20S/840 PSD-E C WH P	IK02	IP20
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	IK06	IP54
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	IK06	IP54
912500100526	DN471B LED20S/830 PSU-E C WH P	IK02	IP20
912500100527	DN471B LED20S/840 PSU-E C WH P	IK02	IP20
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	IK02	IP20
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	IK02	IP20
912500101314	DN471B LED30S/830 PSU-E C WH P	IK02	IP20
912500101315	DN471B LED30S/840 PSU-E C WH P	IK02	IP20
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	IK02	IP20
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	IK02	IP20
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	IK02	IP20
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	IK02	IP20
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	IK02	IP20
910505102085	DN470B LED20S/840 WIA-E C WH P	IK02	IP20
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	IK02	IP54
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	IK02	IP54
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	IK02	IP20

Order Code	Full Product Name	Mech. impact	Ingress	Mech. impact	Ingress
		protection code	protection code		
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	IK02	IP20	910505102034	DN460B LED11S/830 DIA-VLC-E C WH P
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	IK02	IP20	910505102035	DN460B LED11S/840 DIA-VLC-E C WH P
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	IK02	IP20	910505102036	DN460B LED20S/840 DIA-VLC-E C WH P
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	IK02	IP20	910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	IK02	IP20	910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	IK02	IP20	910505102284	DN460B LED11S/830 PSD-E C WH P
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	IK02	IP54	910505102285	DN460B LED11S/840 PSD-E C WH P
910505102147	DN470B LED20S/830 WIA-E C WH P	IK02	IP20	912500100062	DN462B LED11S/830 PSU-E C WH PCC P
910505102271	DN470B LED20S/830 PSD-E C WH P	IK02	IP20	912500100063	DN462B LED11S/840 PSU-E C PCC WH P
910505102272	DN470B LED30S/830 PSD-E C WH P	IK02	IP20	9125001000514	DN460B LED11S/830 PSU-E C WH P
910505102288	DN470B LED20S/840 PSD-E C WH P	IK02	IP20	9125001000515	DN460B LED11S/840 PSU-E C WH P
910505102289	DN470B LED30S/840 PSD-E C WH P	IK02	IP20	9125001000534	DN460B LED11S/830 PSU-E C ELP3 WH P
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	IK06	IP54	9125001000535	DN460B LED11S/840 PSU-E C ELP3 WH P
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	IK06	IP54	910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P
912500100522	DN470B LED20S/830 PSU-E C WH P	IK02	IP20	910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P
912500100523	DN470B LED20S/840 PSU-E C WH P	IK02	IP20	9125001000530	DN462B LED11S/830 PSU-E C WH PCO P
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	IK02	IP20	9125001000531	DN462B LED11S/840 PSU-E C WH PCO P
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	IK02	IP20	910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P
912500101305	DN470B LED30S/830 PSU-E C WH P	IK02	IP20	910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P
912500101307	DN470B LED30S/840 PSU-E C WH P	IK02	IP20	910505102292	DN472B LED11S/830 PSD-E C WH PCO P
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	IK02	IP20	910505102293	DN472B LED11S/840 PSD-E C WH PCO P
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	IK02	IP20	912500100542	DN472B LED20S/830 PSU-E C WH PCO P
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	IK02	IP20	912500100543	DN472B LED20S/840 PSU-E C WH PCO P
912500103011	DN471C LED20S/830 PSU D22H16 WH	IK02	IP20	912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	IK02	IP20	912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR
912500103017	DN471C LED20S/840 PSU D22H16 WH	IK02	IP20	912500103034	DN470T LED20S/830 PSU D22H16 3C GR
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	IK02	IP20	912500103036	DN470T LED20S/840 PSU D22H16 3C GR
912500103023	DN470P LED20S/830 PSU D22H16 WH	IK02	IP20		
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	IK02	IP20		
912500103029	DN470P LED20S/840 PSU D22H16 WH	IK02	IP20		
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	IK02	IP20		

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	IK02	IP20
912500102997	DN470C LED20S/830 PSU D22H16 GR	IK02	IP20
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	IK02	IP20
912500103004	DN470C LED20S/840 PSU D22H16 GR	IK02	IP20
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	IK02	IP20
912500102998	DN470C LED20S/830 PSU D22H16 WH	IK02	IP20
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	IK02	IP20
912500103005	DN470C LED20S/840 PSU D22H16 WH	IK02	IP20
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	IK02	IP20
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	IK02	IP20
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	IK02	IP20
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	IK02	IP20

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	IK02	IP20
912500103022	DN470P LED20S/830 PSU D22H16 GR	IK02	IP20
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	IK02	IP20
912500103028	DN470P LED20S/840 PSU D22H16 GR	IK02	IP20
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	IK02	IP20
912500103010	DN471C LED20S/830 PSU D22H16 GR	IK02	IP20
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	IK02	IP20
912500103016	DN471C LED20S/840 PSU D22H16 GR	IK02	IP20
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	IK02	IP20
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	IK02	IP20
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	IK02	IP20
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	IK02	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102286	DN461B LED11S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
910505102287	DN461B LED11S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
912500100518	DN461B LED11S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
912500100519	DN461B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	(0.43, 0.40) SDCM<3
912500103009	DN471C LED20S/830 PSU D22H16 BK	(0.43, 0.40) SDCM<3
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	(0.38, 0.38) SDCM<3
912500103015	DN471C LED20S/840 PSU D22H16 BK	(0.38, 0.38) SDCM<3
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	(0.43, 0.40) SDCM<3
912500103021	DN470P LED20S/830 PSU D22H16 BK	(0.43, 0.40) SDCM<3
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	(0.38, 0.38) SDCM<3
912500103027	DN470P LED20S/840 PSU D22H16 BK	(0.38, 0.38) SDCM<3
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	(0.43, 0.40) SDCM<3
912500102996	DN470C LED20S/830 PSU D22H16 BK	(0.43, 0.40) SDCM<3
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	(0.38, 0.38) SDCM<3

Order Code	Full Product Name	Initial chromaticity
912500103003	DN470C LED20S/840 PSU D22H16 BK	(0.38, 0.38) SDCM<3
910505102087	DN471B LED20S/830 WIA-E C WH P	(0.43, 0.40) SDCM<3
910505102089	DN471B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102290	DN471B LED20S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
910505102291	DN471B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
912500100526	DN471B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
912500100527	DN471B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
912500101314	DN471B LED30S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
912500101315	DN471B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3

Order Code	Full Product Name	Initial chromaticity
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
910505102085	DN470B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102147	DN470B LED20S/830 WIA-E C WH P	(0.43, 0.40) SDCM<3
910505102271	DN470B LED20S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
910505102272	DN470B LED30S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
910505102288	DN470B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
910505102289	DN470B LED30S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
912500100522	DN470B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
912500100523	DN470B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
912500101305	DN470B LED30S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
912500101307	DN470B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	(0.43, 0.40) SDCM<3
912500103011	DN471C LED20S/830 PSU D22H16 WH	(0.43, 0.40) SDCM<3
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	(0.38, 0.38) SDCM<3
912500103017	DN471C LED20S/840 PSU D22H16 WH	(0.38, 0.38) SDCM<3
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	(0.43, 0.40) SDCM<3
912500103023	DN470P LED20S/830 PSU D22H16 WH	(0.43, 0.40) SDCM<3
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	(0.38, 0.38) SDCM<3
912500103029	DN470P LED20S/840 PSU D22H16 WH	(0.38, 0.38) SDCM<3
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
910505102284	DN460B LED11S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3

Order Code	Full Product Name	Initial chromaticity
910505102285	DN460B LED11S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	(0.38, 0.38) SDCM<3
912500100514	DN460B LED11S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
912500100515	DN460B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	(0.43, 0.40) SDCM<3
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	(0.38, 0.38) SDCM<3
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	(0.43, 0.40) SDCM<3
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	(0.43, 0.40) SDCM<3
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	(0.38, 0.38) SDCM<3
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	(0.43, 0.40) SDCM<3
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	(0.38, 0.38) SDCM<3
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	(0.43, 0.40) SDCM<3
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	(0.43, 0.40) SDCM<3
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	(0.38, 0.38) SDCM<3
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	(0.43, 0.40) SDCM<3
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	(0.38, 0.38) SDCM<3
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	(0.43, 0.40) SDCM<3
912500102997	DN470C LED20S/830 PSU D22H16 GR	(0.43, 0.40) SDCM<3
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	(0.38, 0.38) SDCM<3
912500103004	DN470C LED20S/840 PSU D22H16 GR	(0.38, 0.38) SDCM<3
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	(0.43, 0.40) SDCM<3
912500102998	DN470C LED20S/830 PSU D22H16 WH	(0.43, 0.40) SDCM<3
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	(0.38, 0.38) SDCM<3
912500103005	DN470C LED20S/840 PSU D22H16 WH	(0.38, 0.38) SDCM<3
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	(0.43, 0.40) SDCM<3
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	(0.38, 0.38) SDCM<3
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	(0.43, 0.40) SDCM<3
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	(0.38, 0.38) SDCM<3
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	(0.43, 0.40) SDCM<3
912500103022	DN470P LED20S/830 PSU D22H16 GR	(0.43, 0.40) SDCM<3
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	(0.38, 0.38) SDCM<3
912500103028	DN470P LED20S/840 PSU D22H16 GR	(0.38, 0.38) SDCM<3
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	(0.43, 0.40) SDCM<3
912500103010	DN471C LED20S/830 PSU D22H16 GR	(0.43, 0.40) SDCM<3
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	(0.38, 0.38) SDCM<3
912500103016	DN471C LED20S/840 PSU D22H16 GR	(0.38, 0.38) SDCM<3
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	(0.43, 0.40) SDCM<3
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	(0.38, 0.38) SDCM<3
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	(0.43, 0.40) SDCM<3
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	(0.38, 0.38) SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	-
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	-
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	-
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	-
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	-
910505102286	DN461B LED11S/830 PSD-E C WH P	-
910505102287	DN461B LED11S/840 PSD-E C WH P	-
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	1%
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	1%
912500100518	DN461B LED11S/830 PSU-E C WH P	1%
912500100519	DN461B LED11S/840 PSU-E C WH P	1%
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	1%
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	1%
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	-
912500103009	DN471C LED20S/830 PSU D22H16 BK	-
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	-
912500103015	DN471C LED20S/840 PSU D22H16 BK	-
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	-
912500103021	DN470P LED20S/830 PSU D22H16 BK	-
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	-
912500103027	DN470P LED20S/840 PSU D22H16 BK	-
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	-
912500102996	DN470C LED20S/830 PSU D22H16 BK	-
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	-
912500103003	DN470C LED20S/840 PSU D22H16 BK	-
910505102087	DN471B LED20S/830 WIA-E C WH P	-
910505102089	DN471B LED20S/840 WIA-E C WH P	-
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	-
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	-
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	-
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	-
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	-
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	-
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	-
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	-
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	-
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	-
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	-
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	-
910505102290	DN471B LED20S/830 PSD-E C WH P	-
910505102291	DN471B LED20S/840 PSD-E C WH P	-
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	1%
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	1%
912500100526	DN471B LED20S/830 PSU-E C WH P	1%
912500100527	DN471B LED20S/840 PSU-E C WH P	1%
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	1%
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	1%
912500101314	DN471B LED30S/830 PSU-E C WH P	1%
912500101315	DN471B LED30S/840 PSU-E C WH P	1%
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	1%
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	1%

Order Code	Full Product Name	Driver failure rate at 5000 h
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	-
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	-
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	-
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	-
910505102085	DN470B LED20S/840 WIA-E C WH P	-
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	-
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	-
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	-
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	-
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	-
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	-
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	-
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-
910505102147	DN470B LED20S/830 WIA-E C WH P	-
910505102271	DN470B LED20S/830 PSD-E C WH P	-
910505102272	DN470B LED30S/830 PSD-E C WH P	-
910505102288	DN470B LED20S/840 PSD-E C WH P	-
910505102289	DN470B LED30S/840 PSD-E C WH P	-
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	1%
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	1%
912500100522	DN470B LED20S/830 PSU-E C WH P	1%
912500100523	DN470B LED20S/840 PSU-E C WH P	1%
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	1%
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	1%
912500101305	DN470B LED30S/830 PSU-E C WH P	1%
912500101307	DN470B LED30S/840 PSU-E C WH P	1%
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	1%
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	1%
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	-
912500103011	DN471C LED20S/830 PSU D22H16 WH	-
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	-
912500103017	DN471C LED20S/840 PSU D22H16 WH	-
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	-
912500103023	DN470P LED20S/830 PSU D22H16 WH	-
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	-
912500103029	DN470P LED20S/840 PSU D22H16 WH	-
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	-
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	-
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	-
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	-
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-
910505102284	DN460B LED11S/830 PSD-E C WH P	-
910505102285	DN460B LED11S/840 PSD-E C WH P	-
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	1%
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	1%
912500100514	DN460B LED11S/830 PSU-E C WH P	1%
912500100515	DN460B LED11S/840 PSU-E C WH P	1%
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	1%

Order Code	Full Product Name	Driver failure rate at 5000 h
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	1%
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	-
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	-
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	1%
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	1%
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	-
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	-
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	-
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	-
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	1%
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	1%
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	-
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	-
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	-
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	-
912500102994	DN470C LED20S/830 DIA-VLC D22H16 GR	-
912500102997	DN470C LED20S/830 PSU D22H16 GR	-
912500103001	DN470C LED20S/840 DIA-VLC D22H16 GR	-
912500103004	DN470C LED20S/840 PSU D22H16 GR	-
912500102995	DN470C LED20S/830 DIA-VLC D22H16 WH	-
912500102998	DN470C LED20S/830 PSU D22H16 WH	-

Order Code	Full Product Name	Driver failure rate at 5000 h
912500103002	DN470C LED20S/840 DIA-VLC D22H16 WH	-
912500103005	DN470C LED20S/840 PSU D22H16 WH	-
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	1%
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	1%
912500100269	DN470T LED20S/830 DIA-VLC D22H16 5C6 BK	1%
912500100270	DN470T LED20S/840 DIA-VLC D22H16 5C6 BK	1%
912500103019	DN470P LED20S/830 DIA-VLC D22H16 GR	-
912500103022	DN470P LED20S/830 PSU D22H16 GR	-
912500103025	DN470P LED20S/840 DIA-VLC D22H16 GR	-
912500103028	DN470P LED20S/840 PSU D22H16 GR	-
912500103007	DN471C LED20S/830 DIA-VLC D22H16 GR	-
912500103010	DN471C LED20S/830 PSU D22H16 GR	-
912500103013	DN471C LED20S/840 DIA-VLC D22H16 GR	-
912500103016	DN471C LED20S/840 PSU D22H16 GR	-
912500103031	DN470T LED20S/830 DIA-VLC D22H16 5C6 WH	-
912500103033	DN470T LED20S/840 DIA-VLC D22H16 5C6 WH	-
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	-
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	-

Application Conditions

Order Code	Full Product Name	Suitable for	
		Maximum dim level	random switching
910505102037	DN461B LED11S/830 DIA-VLC-E C ELP3 WH P	1%	Yes
910505102038	DN461B LED11S/830 DIA-VLC-E C WH P	1%	Yes
910505102039	DN461B LED11S/840 DIA-VLC-E C ELP3 WH P	1%	Yes
910505102040	DN461B LED11S/840 DIA-VLC-E C WH P	1%	Yes
910505102071	DN461B LED20S/840 DIA-VLC-E C WH P	1%	Yes
910505102077	DN463B LED11S/830 DIA-VLC-E C WH PCC P	1%	Yes
910505102078	DN463B LED11S/840 DIA-VLC-E C WH PCC P	1%	Yes
910505102286	DN461B LED11S/830 PSD-E C WH P	1%	Yes
910505102287	DN461B LED11S/840 PSD-E C WH P	1%	Yes
912500100066	DN463B LED11S/830 PSU-E C WH PCC P	Not applicable	Yes
912500100067	DN463B LED11S/840 PSU-E C WH PCC P	Not applicable	Yes
912500100518	DN461B LED11S/830 PSU-E C WH P	Not applicable	Yes
912500100519	DN461B LED11S/840 PSU-E C WH P	Not applicable	Yes
912500100538	DN461B LED11S/830 PSU-E C ELP3 WH P	Not applicable	Yes

Order Code	Full Product Name	Suitable for	
		Maximum dim level	random switching
912500100539	DN461B LED11S/840 PSU-E C ELP3 WH P	Not applicable	Yes
912500103006	DN471C LED20S/830 DIA-VLC D22H16 BK	1%	No
912500103009	DN471C LED20S/830 PSU D22H16 BK	Not applicable	No
912500103012	DN471C LED20S/840 DIA-VLC D22H16 BK	1%	No
912500103015	DN471C LED20S/840 PSU D22H16 BK	Not applicable	No
912500103018	DN470P LED20S/830 DIA-VLC D22H16 BK	1%	No
912500103021	DN470P LED20S/830 PSU D22H16 BK	Not applicable	No
912500103024	DN470P LED20S/840 DIA-VLC D22H16 BK	1%	No
912500103027	DN470P LED20S/840 PSU D22H16 BK	Not applicable	No
912500102993	DN470C LED20S/830 DIA-VLC D22H16 BK	1%	No
912500102996	DN470C LED20S/830 PSU D22H16 BK	Not applicable	No
912500102999	DN470C LED20S/840 DIA-VLC D22H16 BK	1%	No
912500103003	DN470C LED20S/840 PSU D22H16 BK	Not applicable	No
910505102087	DN471B LED20S/830 WIA-E C WH P	1%	Yes
910505102089	DN471B LED20S/840 WIA-E C WH P	1%	Yes
910505102103	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	1%	Yes

Order Code	Full Product Name	Suitable for		Maximum dim level	random switching
910505102104	DN471B LED20S/830 DIA-VLC-E C WH P	1%	Yes		
910505102105	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102106	DN471B LED20S/840 DIA-VLC-E C WH P	1%	Yes		
910505102107	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102108	DN471B LED30S/830 DIA-VLC-E C WH P	1%	Yes		
910505102109	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102110	DN471B LED30S/840 DIA-VLC-E C WH P	1%	Yes		
910505102118	DN473B LED20S/830 DIA-VLC-E C WH PCC P	1%	Yes		
910505102119	DN473B LED20S/840 DIA-VLC-E C WH PCC P	1%	Yes		
910505102120	DN473B LED30S/830 DIA-VLC-E C WH PCC P	1%	Yes		
910505102121	DN473B LED30S/840 DIA-VLC-E C WH PCC P	1%	Yes		
910505102290	DN471B LED20S/830 PSD-E C WH P	1%	Yes		
910505102291	DN471B LED20S/840 PSD-E C WH P	1%	Yes		
912500100074	DN473B LED20S/830 PSU-E C WH PCC P	Not applicable	Yes		
912500100075	DN473B LED20S/840 PSU-E C WH PCC P	Not applicable	Yes		
912500100526	DN471B LED20S/830 PSU-E C WH P	Not applicable	Yes		
912500100527	DN471B LED20S/840 PSU-E C WH P	Not applicable	Yes		
912500100550	DN471B LED20S/830 PSU-E C ELP3 WH P	Not applicable	Yes		
912500100551	DN471B LED20S/840 PSU-E C ELP3 WH P	Not applicable	Yes		
912500101314	DN471B LED30S/830 PSU-E C WH P	Not applicable	Yes		
912500101315	DN471B LED30S/840 PSU-E C WH P	Not applicable	Yes		
912500101326	DN471B LED30S/830 PSU-E C ELP3 WH P	Not applicable	Yes		
912500101327	DN471B LED30S/840 PSU-E C ELP3 WH P	Not applicable	Yes		
910505102079	DN470B LED11S/840 DIA-VLC-E C WH P	1%	Yes		
910505102080	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102081	DN470B LED20S/830 DIA-VLC-E C WH P	1%	Yes		
910505102082	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102085	DN470B LED20S/840 WIA-E C WH P	1%	Yes		
Order Code	Full Product Name	Suitable for		Maximum dim level	random switching
910505102091	DN472B LED20S/830 WIA-E C WH PCC P	1%	Yes		
910505102093	DN472B LED20S/840 WIA-E C WH PCC P	1%	Yes		
910505102098	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102099	DN470B LED30S/830 DIA-VLC-E C WH P	1%	Yes		
910505102101	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	1%	Yes		
910505102102	DN470B LED30S/840 DIA-VLC-E C WH P	1%	Yes		
910505102111	DN472B LED20S/830 DIA-VLC-E C WH PCC P	1%	Yes		
910505102113	DN472B LED20S/840 DIA-VLC-E C WH PCC P	1%	Yes		
910505102115	DN472B LED30S/830 DIA-VLC-E C WH PCC P	1%	Yes		
910505102116	DN472B LED30S/840 DIA-VLC-E C WH PCC P	1%	Yes		
910505102147	DN470B LED20S/830 WIA-E C WH P	1%	Yes		
910505102271	DN470B LED20S/830 PSD-E C WH P	1%	Yes		
910505102272	DN470B LED30S/830 PSD-E C WH P	1%	Yes		
910505102288	DN470B LED20S/840 PSD-E C WH P	1%	Yes		
910505102289	DN470B LED30S/840 PSD-E C WH P	1%	Yes		
912500100070	DN472B LED20S/830 PSU-E C WH PCC P	Not applicable	Yes		
912500100071	DN472B LED20S/840 PSU-E C WH PCC P	Not applicable	Yes		
912500100522	DN470B LED20S/830 PSU-E C WH P	Not applicable	Yes		
912500100523	DN470B LED20S/840 PSU-E C WH P	Not applicable	Yes		
912500100546	DN470B LED20S/830 PSU-E C ELP3 WH P	Not applicable	Yes		
912500100547	DN470B LED20S/840 PSU-E C ELP3 WH P	Not applicable	Yes		
912500101305	DN470B LED30S/830 PSU-E C WH P	Not applicable	Yes		
912500101307	DN470B LED30S/840 PSU-E C WH P	Not applicable	Yes		
912500101322	DN470B LED30S/830 PSU-E C ELP3 WH P	Not applicable	Yes		
912500101323	DN470B LED30S/840 PSU-E C ELP3 WH P	Not applicable	Yes		
912500103008	DN471C LED20S/830 DIA-VLC D22H16 WH	1%	No		
912500103011	DN471C LED20S/830 PSU D22H16 WH	Not applicable	No		
912500103014	DN471C LED20S/840 DIA-VLC D22H16 WH	1%	No		
912500103017	DN471C LED20S/840 PSU D22H16 WH	Not applicable	No		
912500103020	DN470P LED20S/830 DIA-VLC D22H16 WH	1%	No		
912500103023	DN470P LED20S/830 PSU D22H16 WH	Not applicable	No		

Order Code	Full Product Name	Suitable for	
		Maximum dim level	random switching
912500103026	DN470P LED20S/840 DIA-VLC D22H16 WH	1%	No
912500103029	DN470P LED20S/840 PSU D22H16 WH	Not applicable	No
910505102033	DN460B LED11S/830 DIA-VLC-E C ELP3 WH P	1%	Yes
910505102034	DN460B LED11S/830 DIA-VLC-E C WH P	1%	Yes
910505102035	DN460B LED11S/840 DIA-VLC-E C WH P	1%	Yes
910505102036	DN460B LED20S/840 DIA-VLC-E C WH P	1%	Yes
910505102072	DN462B LED11S/830 DIA-VLC-E C WH PCC P	1%	Yes
910505102074	DN462B LED11S/840 DIA-VLC-E C WH PCC P	1%	Yes
910505102284	DN460B LED11S/830 PSD-E C WH P	1%	Yes
910505102285	DN460B LED11S/840 PSD-E C WH P	1%	Yes
912500100062	DN462B LED11S/830 PSU-E C WH PCC P	Not applicable	Yes
912500100063	DN462B LED11S/840 PSU-E C PCC WH P	Not applicable	Yes
912500100514	DN460B LED11S/830 PSU-E C WH P	Not applicable	Yes
912500100515	DN460B LED11S/840 PSU-E C WH P	Not applicable	Yes
912500100534	DN460B LED11S/830 PSU-E C ELP3 WH P	Not applicable	Yes
912500100535	DN460B LED11S/840 PSU-E C ELP3 WH P	Not applicable	Yes
910505102073	DN462B LED11S/830 DIA-VLC-E C WH PCO P	1%	Yes
910505102075	DN462B LED11S/840 DIA-VLC-E C WH PCO P	1%	Yes
912500100530	DN462B LED11S/830 PSU-E C WH PCO P	Not applicable	Yes
912500100531	DN462B LED11S/840 PSU-E C WH PCO P	Not applicable	Yes
910505102112	DN472B LED20S/830 DIA-VLC-E C WH PCO P	1%	Yes
910505102114	DN472B LED20S/840 DIA-VLC-E C WH PCO P	1%	Yes
910505102292	DN472B LED11S/830 PSD-E C WH PCO P	1%	Yes
910505102293	DN472B LED11S/840 PSD-E C WH PCO P	1%	Yes
912500100542	DN472B LED20S/830 PSU-E C WH PCO P	Not applicable	Yes
912500100543	DN472B LED20S/840 PSU-E C WH PCO P	Not applicable	Yes
912500103030	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR	1%	No

Order Code	Full Product Name	Suitable for	
		Maximum dim level	random switching
912500103032	DN470T LED20S/840 DIA-VLC D22H16 5C6 GR	1%	No
912500103034	DN470T LED20S/830 PSU D22H16 3C GR	Not applicable	No
912500103036	DN470T LED20S/840 PSU D22H16 3C GR	Not applicable	No
912500102994	DN470C LED20S/830 DIA-VLC D22H16 1% GR	Not applicable	No
912500102997	DN470C LED20S/830 PSU D22H16 GR	Not applicable	No
912500103001	DN470C LED20S/840 DIA-VLC D22H16 1% GR	Not applicable	No
912500103004	DN470C LED20S/840 PSU D22H16 GR	Not applicable	No
912500102995	DN470C LED20S/830 DIA-VLC D22H16 1% WH	Not applicable	No
912500102998	DN470C LED20S/830 PSU D22H16 WH	Not applicable	No
912500103002	DN470C LED20S/840 DIA-VLC D22H16 1% WH	Not applicable	No
912500103005	DN470C LED20S/840 PSU D22H16 WH	Not applicable	No
912500100267	DN470T LED20S/830 PSU D22H16 3C BK	Not applicable	No
912500100268	DN470T LED20S/840 PSU D22H16 3C BK	Not applicable	No
912500100269	DN470T LED20S/830 DIA-VLC D22H16 1% 5C6 BK	Not applicable	No
912500100270	DN470T LED20S/840 DIA-VLC D22H16 1% 5C6 BK	Not applicable	No
912500103019	DN470P LED20S/830 DIA-VLC D22H16 1% GR	Not applicable	No
912500103022	DN470P LED20S/830 PSU D22H16 GR	Not applicable	No
912500103025	DN470P LED20S/840 DIA-VLC D22H16 1% GR	Not applicable	No
912500103028	DN470P LED20S/840 PSU D22H16 GR	Not applicable	No
912500103007	DN471C LED20S/830 DIA-VLC D22H16 1% GR	Not applicable	No
912500103010	DN471C LED20S/830 PSU D22H16 GR	Not applicable	No
912500103013	DN471C LED20S/840 DIA-VLC D22H16 1% GR	Not applicable	No
912500103016	DN471C LED20S/840 PSU D22H16 GR	Not applicable	No
912500103031	DN470T LED20S/830 DIA-VLC D22H16 1% 5C6 WH	Not applicable	No
912500103033	DN470T LED20S/840 DIA-VLC D22H16 1% 5C6 WH	Not applicable	No
912500103035	DN470T LED20S/830 PSU D22H16 3C WH	Not applicable	No
912500103037	DN470T LED20S/840 PSU D22H16 3C WH	Not applicable	No

