



High quality and robust performance

PrimaVision Compact for CDM

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- Optimal lamp performance thanks to minimal lamp power tolerance
- CDM lamp life increased by up to 30%
- CDM lamp life increased by up to 30%
- Eliminates all visible lamp flicker
- Eliminates all visible lamp flicker

Features


- Minimal lamp power spread
- Minimal lamp power spread
- Low gear energy losses
- Low gear energy losses
- Lamp end-of-life detection
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours
- Long lifetime of 40,000 hours

Application

- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only
- Suitable for indoor use only




PrimaVision Compact for CDM

Versions



GPPR IPVG4pp PHL 0010


Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 50 /I CDM 220-240V 50/60Hz	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

Product	D1	C1	A1	A2	B1
HID-PV C 50 /S CDM 220-240V 50/60Hz	4.9 mm	32.2 mm	109.6 mm	98.5 mm	74.4 mm

Product details



HID-PV C 50 /I



HID-PV C 50 /S

PrimaVision Compact for CDM

Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	24

Mechanical and Housing

Order Code	Full Product Name	Housing
913700665166	HID-PV C 50 /I CDM 220-240V 50/60Hz	/I

Order Code	Full Product Name	Housing
913700664966	HID-PV C 50 /S CDM 220-240V 50/60Hz	/S

