



# PrimaVision SDW-TG (50W & 100W) for SDW-TG - High quality and robust performance

## PrimaVision for SDW-TG

Robust, lightweight and one-piece HID electronic gear for SDW-TG lamps (mini White SON) Lightweight, one-piece electronic gear for 50 and 100 W SDW-TG lamps (mini White SON)

### Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- Reduces color differences between lamps and initial lumen spread
- Performance is independent of mains voltage

### Features

- Available as Standard (/S) version for use in a luminaire, or with separate strain relief for independent use on a (false) ceiling
- Minimal lamp power spread
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

### Application

- Shop lighting, for a cozy atmosphere (e.g. in furniture shops) and excellent display of fresh goods (e.g. in butcher's shops, bakeries, florists)
- Suitable for indoor use only

# PrimaVision for SDW-TG



## Versions



GPPR HIDSTRL1 PHL



## Dimensional drawing



Product	C1	C3	A1	A3	B1
HID-STRAIN RELIEF	30 mm	16 mm	40 mm	40 mm	62 mm

Product	D1	C1	A1	A2	B1	B2
HID-PV 100 /S SDW-TG 220-240V 50/60Hz	4.5 mm	37.0 mm	150.0 mm	133.6 mm	90.0 mm	70.0 mm

## Operating and Electrical

Order Code	Full Product Name	Input Frequency	Input Voltage	Line Frequency	Number of Products on MCB (16A Type B) (Nom)
53986130	HID-STRAIN RELIEF	-	-	-	-

Order Code	Full Product Name	Input Frequency	Input Voltage	Line Frequency	Number of Products on MCB (16A Type B) (Nom)
88754900	HID-PV 100 /S SDW-TG	50 to 60 Hz	220 to 240 V	50 to 60 Hz	14

## PrimaVision for SDW-TG

Order Code	Full Product Name	Input Frequency	Input Voltage	Line Frequency	Number of Products on MCB (16A Type B) (Nom)
	220-240V				
	50/60Hz				

### Mechanical and Housing

Order Code	Full Product Name	Housing
53986130	HID-STRAIN RELIEF	-

Order Code	Full Product Name	Housing
88754900	HID-PV 100 /S SDW-TG 220-240V 50/60Hz	/S

