



# Incredible colors, warm atmosphere

## MASTER SDW-TG Mini

Range of high-efficiency, discharge lamps with warm color to be used in small, open luminaires designed around MASTERColour CDM-T lamps

### Benefits

- Exceptional brightness and color rendering especially of warm colors, e.g. red and gold
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps

### Features

- Unique warm color quality
- Lamp design is well-suited to be used in luminaires for MASTERColour CDM-T power-spots
- UV-block glass

### Application

- Shop lighting (creates cosy atmosphere e.g. in furniture shops), excellent display of fresh goods (at butchers, bakeries, flower-shops)

### Warnings and Safety

- Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER SDW-TG Mini

## Versions



SDW-TG, 100W, GX12-1

## Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTER SDW-TG Mini 100W/825 GX12-11CT/12	20 mm	0.75 in	18 mm	54.5 mm	57.5 mm	56	110 mm
MASTER SDW-TG Mini 50W/825 GX12-11CT/12	20 mm	0.75 in	14.5 mm	53.5 mm	56.5 mm	55 mm	103 mm

# MASTER SDW-TG Mini

## Approval and Application

Energy Efficiency Label (EEL) B

## Controls and Dimming

Dimmable No

## General Information

Cap-Base GX12-1  
 Life To 50% Failures (Nom) 10000 h  
 Operating Position UNIVERSAL  
 System Description -

## Light Technical

Color Code 825  
 Color Designation Golden White  
 Correlated Color Temperature (Nom) 2500 K  
 Color Rendering Index (Min) 80  
 Lumen Maintenance 10000 h (Min) 65 %  
 Lumen Maintenance 10000 h (Nom) 75 %  
 Lumen Maintenance 2000 h (Min) 85 %  
 Lumen Maintenance 2000 h (Nom) 95 %  
 Lumen Maintenance 5000 h (Min) 75 %

## Mechanical and Housing

Bulb Finish Clear  
 Bulb Material -  
 Bulb Shape T19

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/	Mercury (Hg)
		1000 h	Content (Nom)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	109 kWh	15.2 mg
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	59 kWh	5.7 mg

## Operating and Electrical (1/2)

Order Code	Full Product Name	Voltage	Voltage	Voltage	Power
		(Max)	(Min)	(Nom)	(Rated)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	98 V	84 V	91 V	99.0 W

Order Code	Full Product Name	Voltage	Voltage	Voltage	Power
		(Max)	(Min)	(Nom)	(Rated)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	90 V	78 V	85 V	54.0 W

## Operating and Electrical (2/2)

Order Code	Full Product Name	Re-ignition Time (Min)
		(Max)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	1.5 min

Order Code	Full Product Name	Re-ignition Time (Min)
		(Max)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	1.0 min

## General Information

Order Code	Full Product Name	Life To 20%	Life To 5%
		Failures (Nom)	Failures (Nom)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	8000 h	5000 h

Order Code	Full Product Name	Life To 20%	Life To 5%
		Failures (Nom)	Failures (Nom)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	9000 h	7000 h

## Luminaire Design Requirements

## MASTER SDW-TG Mini

Order Code	Full Product Name	Bulb Temperature (Max)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	650 °C

Order Code	Full Product Name	Bulb Temperature (Max)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	500 °C

### Light Technical (1/2)

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color	
				Rendering Index (Nom)	Lumen Maintenance 5000 h (Nom)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	469	406	83	80 %
928159905131	MASTER SDW-TG	468	408	81	85 %

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color	
				Rendering Index (Nom)	Lumen Maintenance 5000 h (Nom)
	Mini 50W/825 GX12-1 1CT/12				

### Light Technical (2/2)

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	50 lm/W	4400 lm	4900 lm

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	44 lm/W	2100 lm	2400 lm

