



Product Description

SON H

High Pressure Sodium lamp with opalized outer bulb retrofit for High Pressure Mercury lamps

Benefits

• Instant and cost-effective upgrade of light level and reduction of energy use replacing HPL

Features

- · Direct replacement for mercury lamps as they operate on the same control gear
- · High luminous efficacy
- Robust construction is vibration- and shock-resistant leading to a reliable life

Application

- \cdot Road and residential lighting
- · Commercial and industrial applications

Warnings and Safety

- For use with control gear designed for high-pressure mercury lamps
- · For outdoor use only
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

SON H

Versions



Dimensional drawing

Product	D (max)	C (max)
SON H 110W I E27 1CT/24	71 mm	156 mm

