



Product Description

SON-T

High Pressure Sodium lamp with clear tubular outer bulb

Benefits

- SON-T Pro is a cost-efficient and reliable solution in High Pressure Sodium

Features

- Clear tubular outer bulb
- High luminous efficacy
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Dimming possible with dedicated gear

Application

- Road and residential lighting
- Decorative floodlighting
- Commercial and industrial applications
- Recreational sports facilities Outdoor and Indoor

Warnings and Safety


- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

SON-T

Versions



Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 70W/220 E27 1CT/12	36 mm	42 mm	102 mm	156 mm
SON-T 150W E E40 SL/12	47 mm	58 mm	132 mm	209 mm
SON-T 1000W E E40 1SL/4	66 mm	145 mm	240 mm	390 mm
SON-T 100W E E40 SL/12				
SON-T 400W E E40 SL/12	47 mm	82 mm	175 mm	286 mm
SON-T 250W E E40 SL/12	47 mm	66 mm	158 mm	255 mm

Controls and Dimming

Dimmable	yes
----------	-----

General Information

Operating Position	UNIVERSAL
System Description	External Ignitor (E)

Light Technical

Colour Code	220
Correlated Colour Temperature (Nom)	2000 K
Colour Rendering Index (Max)	25
Colour Rendering Index (Nom)	-

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928152800035	SON-T 70W/220 E27 1CT/12	77 kWh	A+	16 mg
928481500092	SON-T 100W E E40 SL/12	110 kWh	A+	20.4 mg
928487100096	SON-T 150W E E40 SL/12	162 kWh	A+	20.4 mg
928487200098	SON-T 250W E E40 SL/12	275 kWh	A+	20.4 mg
928487300098	SON-T 400W E E40 SL/12	431 kWh	A+	24.5 mg
928487400091	SON-T 1000W E E40 1SL/4	1056 kWh	A++	22.65 mg

Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928152800035	SON-T 70W/220 E27 1CT/12	0.98 A	105 V	75 V	90 V
928481500092	SON-T 100W E E40 SL/12	1.2 A	115 V	85 V	100 V
928487100096	SON-T 150W E E40 SL/12	1.8 A	115 V	85 V	100 V

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928487200098	SON-T 250W E E40 SL/12	3 A	115 V	85 V	100 V
928487300098	SON-T 400W E E40 SL/12	4.6 A	115 V	85 V	100 V
928487400091	SON-T 1000W E E40 1SL/4	10.6 A	115 V	85 V	100 V

Operating and Electrical (2/2)

Order Code	Full Product Name	Power (Rated)	Re-Ignition Time
		(Nom)	(Min) (Max)
928152800035	SON-T 70W/220 E27 1CT/12	70.0 W	180 s
928481500092	SON-T 100W E E40 SL/12	100.0 W	120 s
928487100096	SON-T 150W E E40 SL/12	147.0 W	180 s

Order Code	Full Product Name	Power (Rated)	Re-Ignition Time
		(Nom)	(Min) (Max)
928487200098	SON-T 250W E E40 SL/12	250.0 W	120 s
928487300098	SON-T 400W E E40 SL/12	392.0 W	120 s
928487400091	SON-T 1000W E E40 1SL/4	960.0 W	240 s

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Life To 10%	Life To 20%	Life To 50%
			Failures (Nom)	Failures (Nom)	Failures (Nom)
928152800035	SON-T 70W/220 E27 1CT/12	E27	15000 h	19000 h	28000 h
928481500092	SON-T 100W E E40 SL/12	E40	12000 h	-	28000 h
928487100096	SON-T 150W E E40 SL/12	E40	-	20000 h	28000 h

Order Code	Full Product Name	Cap-Base	Life To 10%	Life To 20%	Life To 50%
			Failures (Nom)	Failures (Nom)	Failures (Nom)
928487200098	SON-T 250W E E40 SL/12	E40	-	20000 h	28000 h
928487300098	SON-T 400W E E40 SL/12	E40	-	20000 h	28000 h
928487400091	SON-T 1000W E E40 1SL/4	E40	-	14000 h	20000 h

General Information (2/2)

Order Code	Full Product Name	Life To 5% Failures (Nom)	LSF 12000 h Rated	LSF 16000 h Rated	LSF 2000 h Rated	LSF 20000 h Rated	LSF 4000 h Rated	LSF 6000 h Rated	LSF 8000 h Rated
		928152800035	SON-T 70W/220 E27 1CT/12	12000 h	95 %	89 %	99 %	79 %	99 %
928481500092	SON-T 100W E E40 SL/12	-	-	-	-	-	-	-	-
928487100096	SON-T 150W E E40 SL/12	12000 h	-	-	-	-	-	-	-
928487200098	SON-T 250W E E40 SL/12	12000 h	-	-	-	-	-	-	-
928487300098	SON-T 400W E E40 SL/12	12000 h	-	-	-	-	-	-	-
928487400091	SON-T 1000W E E40 1SL/4	8000 h	-	-	-	-	-	-	-

Luminaire Design Requirements

Order Code	Full Product Name	Bulb Temperature (Max)
928152800035	SON-T 70W/220 E27 1CT/12	350 °C
928481500092	SON-T 100W E E40 SL/12	450 °C
928487100096	SON-T 150W E E40 SL/12	450 °C

Order Code	Full Product Name	Bulb Temperature (Max)
928487200098	SON-T 250W E E40 SL/12	450 °C
928487300098	SON-T 400W E E40 SL/12	450 °C
928487400091	SON-T 1000W E E40 1SL/4	450 °C

Light Technical (1/3)

Order Code	Full Product Name	Chromaticity	Chromaticity	LLMF	LLMF
		Coordinate X (Nom)	Coordinate Y (Nom)	12000 h Rated	16000 h Rated
928152800035	SON-T 70W/220 E27 1CT/12	540	413	81 %	81 %
928481500092	SON-T 100W E E40 SL/12	-	-	-	-
928487100096	SON-T 150W E E40 SL/12	-	-	-	-

Order Code	Full Product Name	Chromaticity	Chromaticity	LLMF	LLMF
		Coordinate X (Nom)	Coordinate Y (Nom)	12000 h Rated	16000 h Rated
928487200098	SON-T 250W E E40 SL/12	-	-	-	-
928487300098	SON-T 400W E E40 SL/12	-	-	-	-
928487400091	SON-T 1000W E E40 1SL/4	-	-	-	-

Light Technical (2/3)

Order Code	Full Product Name	LLMF	LLMF	LLMF	LLMF	LLMF	Lumen	Lumen	Lumen	Lumen
		2000 h Rated	20000 h Rated	4000 h Rated	6000 h Rated	8000 h Rated	Maintenance 2000 h (Min)	Maintenance 2000 h (Nom)	Maintenance 5000 h (Min)	Maintenance 5000 h (Nom)
928152800035	SON-T 70W/220 E27 1CT/12	89 %	80 %	86 %	85 %	84 %	-	-	-	-
928481500092	SON-T 100W E E40 SL/12	-	-	-	-	-	85 %	95 %	80 %	90 %
928487100096	SON-T 150W E E40 SL/12	-	-	-	-	-	90 %	95 %	85 %	90 %
928487200098	SON-T 250W E E40 SL/12	-	-	-	-	-	95 %	98 %	92 %	96 %
928487300098	SON-T 400W E E40 SL/12	-	-	-	-	-	94 %	97 %	88 %	94 %
928487400091	SON-T 1000W E E40 1SL/4	-	-	-	-	-	90 %	95 %	80 %	90 %

Light Technical (3/3)

Order Code	Full Product Name	Luminous	Luminous	Ratio	
		Efficacy (rated) (Nom)	Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)	Scotopic/Photopic Lumens
928152800035	SON-T 70W/220 E27 1CT/12	84 lm/W	-	6000 lm	0.50
928481500092	SON-T 100W E E40 SL/12	90 lm/W	8100 lm	9000 lm	-
928487100096	SON-T 150W E E40 SL/12	98 lm/W	13500 lm	15000 lm	-

Order Code	Full Product Name	Luminous	Luminous	Ratio	
		Efficacy (rated) (Nom)	Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)	Scotopic/Photopic Lumens
928487200098	SON-T 250W E E40 SL/12	110 lm/W	25200 lm	28000 lm	-
928487300098	SON-T 400W E E40 SL/12	123 lm/W	43200 lm	48000 lm	-

