



The longest life and most reliable solution in road lighting

MASTER SON-T APIA Plus Xtra

High Pressure Sodium lamp with clear tubular outer bulb shape, high output and longest reliable lifetime

Benefits

- Most-cost effective solution (both initial as well as running cost) in this category
- 6 years service life
- Highest lumen output, maintained over life

Features

- Completely lead-free lamps with tubular outer bulb
- Ceramic discharge tube with new Active Philips Integrated Antenna (APIA) for up to 6 years service lifetime (Xtra)
- Robust construction with few welding points is highly vibration- and shock-resistant, further reducing early failures and extending lamp life
- "Plus" concept with high efficacy for high light output
- Special versions of the 250W and 400W lamps of the MASTER SON(-T) APIA Plus Xtra range are compatible with electronic gear using HF operation of the lamps. HF Control gear requirements (LDi guideline) and lamp performance specifications on HF ballasts can be obtained from the local Philips representative

Application

- Road and residential lighting
- Decorative floodlighting, illumination
- Industrial area lighting
- Recreational sports facilities indoor and outdoor

MASTER SON-T APIA Plus Xtra

Warnings and Safety


- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- HF gear must comply with Philips LDi guideline
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR SONTAPIA Plus-Xtra E27

Dimensional drawing



Product	D (max)	O	L	C (max)
MST SON-T APIA Plus Xtra 100W E40 1SL/12	48 mm	47 mm	132 mm	210 mm
MST SON-T APIA Plus Xtra 150W E40 1SL/12	48 mm	61 mm	132 mm	210 mm
MST SON-T APIA Plus Xtra 250W E40 1SL/12	48 mm	65 mm	158 mm	257 mm
MST SON-T APIA Plus Xtra 400W E40 1SL/12	48 mm	83 mm	175 mm	283 mm
MST SON-T APIA Plus Xtra 50W E27 1SL/12	36 mm	35 mm	102 mm	156 mm
MST SON-T APIA Plus Xtra 70W E27 1SL/12	36 mm	42 mm	102 mm	156 mm

General Information	
Operating Position	UNIVERSAL
Light Technical	
Chromaticity Coordinate Y (Nom)	0.42
Color rendering index (CRI)	-
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

General Information

MASTER SON-T APIA Plus Xtra

Order Code	Full Product Name	Cap-Base
93358100	MASTER SON-T APIA Plus Xtra 50W E27 1SL/12	E27
92290500	MASTER SON-T APIA Plus Xtra 70W E27 1SL/12	E27
92323000	MASTER SON-T APIA Plus Xtra 100W E40 1SL/12	E40

Order Code	Full Product Name	Cap-Base
92733700	MASTER SON-T APIA Plus Xtra 150W E40 1SL/12	E40
92737500	MASTER SON-T APIA Plus Xtra 250W E40 1SL/12	E40
92741200	MASTER SON-T APIA Plus Xtra 400W E40 1SL/12	E40

Light Technical

Order Code	Full Product Name	Chromaticity	Correlated Color	Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Temperature (Nom)	(rated) (Nom)	
93358100	MASTER SON-T APIA Plus Xtra 50W E27 1SL/12	0.54	1900 K	83 lm/W	4,500 lm
92290500	MASTER SON-T APIA Plus Xtra 70W E27 1SL/12	0.54	1900 K	96 lm/W	7,200 lm
92323000	MASTER SON-T APIA Plus Xtra 100W E40 1SL/12	0.535	2000 K	110 lm/W	11,550 lm
92733700	MASTER SON-T APIA Plus Xtra	0.535	2000 K	118.51 lm/W	18,200 lm

Order Code	Full Product Name	Chromaticity	Correlated Color	Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Temperature (Nom)	(rated) (Nom)	
	150W E40 1SL/12				
92737500	MASTER SON-T APIA Plus Xtra 250W E40 1SL/12	0.535	2000 K	132 lm/W	33,700 lm
92741200	MASTER SON-T APIA Plus Xtra 400W E40 1SL/12	0.535	2000 K	140 lm/W	55,400 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Voltage	Power
		(Nom)	(Nom)	Consumption
93358100	MASTER SON-T APIA Plus Xtra 50W E27 1SL/12	-	86 V	54.0 W
92290500	MASTER SON-T APIA Plus Xtra 70W E27 1SL/12	-	92 V	75.0 W
92323000	MASTER SON-T APIA Plus Xtra 100W E40 1SL/12	1,150 mA	-	105 W

Order Code	Full Product Name	Lamp Current	Voltage	Power
		(Nom)	(Nom)	Consumption
92733700	MASTER SON-T APIA Plus Xtra 150W E40 1SL/12	-	98 V	154.0 W
92737500	MASTER SON-T APIA Plus Xtra 250W E40 1SL/12	-	99 V	255.0 W
92741200	MASTER SON-T APIA Plus Xtra 400W E40 1SL/12	-	98 V	397.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
93358100	MASTER SON-T APIA Plus Xtra 50W E27 1SL/12	T35
92290500	MASTER SON-T APIA Plus Xtra 70W E27 1SL/12	T35
92323000	MASTER SON-T APIA Plus Xtra 100W E40 1SL/12	T46

Order Code	Full Product Name	Bulb Shape
92733700	MASTER SON-T APIA Plus Xtra 150W E40 1SL/12	T46
92737500	MASTER SON-T APIA Plus Xtra 250W E40 1SL/12	T46
92741200	MASTER SON-T APIA Plus Xtra 400W E40 1SL/12	T46

Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg) Content	Mercury (Hg) Content
		kWh/1000 h	(Max)	(Nom)
93358100	MASTER SON-T APIA Plus Xtra 50W E27 1SL/12	54 kWh	9.8 mg	9.8 mg

Order Code	Full Product Name	Energy Consumption	Mercury (Hg) Content	Mercury (Hg) Content
		kWh/1000 h	(Max)	(Nom)
92290500	MASTER SON-T APIA Plus Xtra 70W E27 1SL/12	75 kWh	12.2 mg	12.2 mg

MASTER SON-T APIA Plus Xtra

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)
92323000	MASTER SON-T APIA Plus Xtra 100W E40 1SL/12	103 kWh	16.3 mg	16.3 mg
92733700	MASTER SON-T APIA Plus Xtra 150W E40 1SL/12	154 kWh	15.1 mg	15.1 mg
92737500	MASTER SON-T APIA Plus Xtra 250W E40 1SL/12	255 kWh	15.1 mg	15.1 mg
92741200	MASTER SON-T APIA Plus Xtra 400W E40 1SL/12	397 kWh	19.6 mg	19.6 mg

