



The most reliable solution in road lighting

MASTER SON-T PIA Plus

High Pressure Sodium lamp with clear tubular outer bulb, high output and long reliable lifetime

Benefits

- Initial investment saving options with "Plus" concept
- High lumen output, maintained over life
- Minimal maintenance cost

Features

- Clear tubular outer bulb
- Ceramic discharge tube with Unique Philips Integrated Antenna (PIA) concept enabling long and reliable lifetime
- "Plus" concept with high efficacy translates into high light output and improved lumen maintenance
- Robust construction with few welding points is highly vibration- and shock-resistant, further reducing early failures and extending lamp life
- Dimmable

Application

- Road and residential lighting
- Decorative floodlighting, illumination
- Industrial area lighting
- Recreational sports facilities indoor and outdoor

MASTER SON-T PIA Plus


Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Dimensional drawing



Product
MASTER SON-T PIA Plus 100W/220 E40 1SL/12
MASTER SON-T PIA Plus 250W E40 1SL/12
MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12
MSTSON-TPIA Plus 70W E27 1CT/12
MASTER SON-T PIA Plus 400W E E40 1SL/12
MASTER SON-T PIA Plus 400W E40 1SL/12
MASTER SON-T PIA Plus 150W E40 1SL/12
MASTER SON-T PIA Plus 70W/220 E27 1SL/12
MASTER SON-T PIA Plus 250W E E40 1SL/12
MASTER SON-T PIA Plus 600W/220 E40 1SL/12

General Information	
Operating Position	UNIVERSAL
System Description	External Ignitor (E)
Light Technical	
Colour Code	220
Correlated Colour Temperature (Nom)	2000 K
Colour Rendering Index (Max)	25
Mechanical and Housing	
Bulb Finish	Clear

Approval and Application

MASTER SON-T PIA Plus

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	275 kWh	A+	15.1 mg
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	275 kWh	A+	15.1 mg
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	440 kWh	A++	20 mg
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	440 kWh	A++	20 mg
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	169 kWh	A+	15 mg

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	110 kWh	A+	16.3 mg
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	663 kWh	A++	24 mg
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	169 kWh	A+	13.9 mg
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	80 kWh	A+	12 mg
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	80 kWh	A+	12.2 mg

Controls and Dimming

Order Code	Full Product Name	Dimmable
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	Yes
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	Yes
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	Yes
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	Yes
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	Yes

Order Code	Full Product Name	Dimmable
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	Yes
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	No
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	No
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	Yes
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	No

Operating and Electrical

Order Code	Full Product Name	Lamp Current (EM)				Re-Ignition Time (Min)	
		(Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Rated) (Nom)	(Max)
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	3 A	115 V	85 V	100 V	250.0 W	120 s
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	3 A	115 V	85 V	100 V	250.0 W	120 s
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	4.5 A	115 V	85 V	100 V	400.0 W	120 s
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	4.5 A	115 V	85 V	100 V	400.0 W	120 s
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	1.8 A	115 V	85 V	100 V	154.0 W	180 s
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	1.2 A	115 V	85 V	100 V	100.0 W	120 s
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	5.8 A	125 V	95 V	110 V	603 W	60 s
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	1.8 A	115 V	85 V	100 V	154.0 W	180 s
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	0.975 A	105 V	75 V	90 V	73.0 W	30 s
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	0.975 A	103 V	73 V	93 V	73.0 W	30 s

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Life To 10% Failures (Nom)	Life To 20% Failures (Nom)	Life To 50% Failures (Nom)	Life To 5% Failures (Nom)	LSF 12000 h Rated	LSF 16000 h Rated
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	E40	24000 h	28000 h	36000 h	20500 h	99 %	98 %
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	E40	24000 h	28000 h	36000 h	20500 h	99 %	98 %
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	E40	24000 h	28000 h	36000 h	20500 h	99 %	98 %
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	E40	24000 h	28000 h	36000 h	20500 h	99 %	98 %
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	E40	24000 h	28000 h	36000 h	20500 h	99 %	98 %
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	E40	21000 h	26000 h	36000 h	17000 h	98 %	96 %
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	E40	15000 h	20000 h	30000 h	12000 h	-	-
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	E40	24000 h	28000 h	32000 h	20500 h	-	-

MASTER SON-T PIA Plus

Order Code	Full Product Name	Cap-Base	Life To 10% Failures (Nom)	Life To 20% Failures (Nom)	Life To 50% Failures (Nom)	Life To 5% Failures (Nom)	LSF 12000 h Rated	LSF 16000 h Rated
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	E27	20000 h	23500 h	30000 h	17000 h	99 %	96 %
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	E27	20000 h	23500 h	28000 h	17000 h	-	-

General Information (2/2)

Order Code	Full Product Name	LSF	LSF	LSF	LSF	LSF
		2000 h Rated	20000 h Rated	4000 h Rated	6000 h Rated	8000 h Rated
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	100 %	95 %	99 %	99 %	99 %
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	100 %	95 %	99 %	99 %	99 %
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	100 %	95 %	99 %	99 %	99 %
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	100 %	95 %	99 %	99 %	99 %
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	100 %	95 %	99 %	99 %	99 %

Order Code	Full Product Name	LSF	LSF	LSF	LSF	LSF
		2000 h Rated	20000 h Rated	4000 h Rated	6000 h Rated	8000 h Rated
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	100 %	91 %	99 %	99 %	99 %
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	-	-	-	-	-
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	-	-	-	-	-
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	99 %	90 %	99 %	99 %	99 %
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	-	-	-	-	-

Luminaire Design Requirements

Order Code	Full Product Name	Bulb Temperature (Max)
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	450 °C
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	450 °C
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	450 °C
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	450 °C
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	450 °C

Order Code	Full Product Name	Bulb Temperature (Max)
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	450 °C
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	450 °C
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	450 °C
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	350 °C
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	350 °C

Light Technical (1/3)

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Colour Rendering Index (Nom)	LLMF 12000 h Rated	LLMF 16000 h Rated	LLMF 2000 h Rated	LLMF 20000 h Rated
		17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	530	420	-	96 %	95 %
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	530	420	-	96 %	95 %	99 %	94 %
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	525	425	-	92 %	90 %	99 %	88 %
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	525	425	-	92 %	90 %	99 %	88 %
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	535	420	-	96 %	95 %	99 %	94 %
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	535	420	-	92 %	90 %	98 %	89 %
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	526	424	-	-	-	-	-
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	535	420	-	-	-	-	-
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	540	420	-	83 %	82 %	90 %	81 %
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	540	420	-	-	-	-	-

Light Technical (2/3)

MASTER SON-T PIA Plus

Order Code	Full Product Name	LLMF 4000 h Rated	LLMF 6000 h Rated	LLMF 8000 h Rated	Lumen Maintenance 2000 h (Min)	Lumen Maintenance 2000 h (Nom)	Lumen Maintenance 20000 h	Lumen Maintenance 5000 h (Min)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	98 %	97 %	96 %	-	-	-	-	-	127 lm/W
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	98 %	97 %	96 %	-	-	-	-	-	127 lm/W
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	97 %	96 %	94 %	95 %	99 %	88 %	90.5 %	96.5 %	137 lm/W
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	97 %	96 %	94 %	95 %	99 %	88 %	90.5 %	96.5 %	137 lm/W
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	98 %	97 %	96 %	-	-	-	-	-	116 lm/W
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	96 %	95 %	94 %	-	-	-	-	-	106 lm/W
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	-	-	-	85 %	96 %	77 %	80 %	90 %	143.5 lm/W
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	-	-	-	94 %	97 %	-	88 %	95 %	117 lm/W
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	87 %	86 %	85 %	-	90 %	81 %	-	86.5 %	91 lm/W
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	-	-	-	90 %	95 %	-	85 %	92 %	91 lm/W

Light Technical (3/3)

Order Code	Full Product Name	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)	Ratio Scotopic/ Photopic Lumens
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	-	33000 lm	0.60
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	-	33000 lm	0.60
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	-	55800 lm	0.60
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	-	55800 lm	0.60
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	-	17700 lm	0.55

Order Code	Full Product Name	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)	Ratio Scotopic/ Photopic Lumens
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	-	10700 lm	0.55
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	-	86500 lm	0.60
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	14500 lm	18000 lm	-
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	-	6600 lm	0.50
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	5940 lm	6600 lm	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
17987615	MASTER SON-T PIA Plus 250W E E40 1SL/12	T46
18075300	MASTER SON-T PIA Plus 250W E40 1SL/12	T46
17988315	MASTER SON-T PIA Plus 400W E E40 1SL/12	T46
18077700	MASTER SON-T PIA Plus 400W E40 1SL/12	T46
19229515	MASTER SON-T PIA Plus 150W/220 E40 - 1SL/12	T46
19230115	MST SON-T PIA PLUS 100W/220 E40 SL/12	T46
19742915	MASTER SON-T PIA Plus 600W/220 E40 1SL/12	T46
18073900	MASTER SON-T PIA Plus 150W E40 1SL/12	T46

Order Code	Full Product Name	Bulb Shape
19266015	MASTER SON-T PIA Plus 70W/220 E27 1SL/12	T35
18069200	MASTER SON-T PIA Plus 70W E27 1SL/12	T35

MASTER SON-T PIA Plus

