



# Essential LEDtube - Affordable LED solution

## Essential LEDtube

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

### Benefits

- Reduced electricity costs thanks to significant energy savings
- Longer lifetime minimizes re-lamping for reduced maintenance costs
- A better choice for the environment – no mercury

### Features

- Affordable LED replacement for T8 fluorescent lamps
- Energy consumption less than half that of normal fluorescent lamps
- 25,000 hours lifetime, double that of normal fluorescent lamps
- No mercury; glass-free tube – no breakage concerns

### Application

- Retail, offices
- Industry, warehouses, public places, schools, hospitals, car parks


# Essential LEDtube

## Versions



# Essential LEDtube

## Dimensional drawing



A3

Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W840 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
CorePro LEDtube 600mm 8W830 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
CorePro LEDtube 600mm 8W865 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
CorePro LEDtube 1200mm 16W840 G5 I APR	15.8 mm	19 mm	1149 mm	1156.1 mm	1163.2 mm
CorePro LEDtube 1200mm 16W830 G5 I APR	15.8 mm	19 mm	1149 mm	1156.1 mm	1163.2 mm
CorePro LEDtube 1200mm 16W865 G5 I APR	15.8 mm	19 mm	1149 mm	1156.1 mm	1163.2 mm

Product	D1	D2	A1	A2	A3		
LEDtube HO 600mm 10W 730 T8 AP I G	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
LEDtube HO 1200mm 20W 740 T8 AP I G	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm		
LEDtube HO 600mm 10W 740 T8 AP I G	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
LEDtube HO 1200mm 20W 765 T8 AP I G	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm		
LEDtube HO 600mm 10W 765 T8 AP I G	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
LEDtube HO 1200mm 20W 730 T8 AP I G	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm		
LEDtube 1200mm 16W 765 T8 AP I G	25.68 mm	28 mm	1198 mm	1205 mm	1212 mm	1212 mm	27.8 mm
LEDtube 600mm 8W 740 T8 AP I G	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm
LEDtube 1200mm 16W 740 T8 AP I G	25.68 mm	28 mm	1198 mm	1205 mm	1212 mm	1212 mm	27.8 mm
LEDtube 600mm 8W 765 T8 AP I G	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm

# Essential LEDtube

## Controls and Dimming

Dimmable	No
----------	----

## Operating and Electrical

Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

## General Information

Switching Cycle	50000X
-----------------	--------

## Light Technical

Llmf At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

## Temperature

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001184538	LEDtube 1200mm 16W 740 T8 AP I G	16 kWh	A+
929001184638	LEDtube 1200mm 16W 765 T8 AP I G	16 kWh	A+
929001184738	LEDtube 600mm 8W 740 T8 AP I G	8 kWh	A+
929001184838	LEDtube 600mm 8W 765 T8 AP I G	8 kWh	A+
929001277208	LEDtube HO 1200mm 20W 740 T8 AP I G	20 kWh	A+
929001277308	LEDtube HO 1200mm 20W 765 T8 AP I G	20 kWh	A+
929001277408	LEDtube HO 600mm 10W 740 T8 AP I G	10 kWh	A+
929001277508	LEDtube HO 600mm 10W 765 T8 AP I G	10 kWh	A+
929001299808	LEDtube HO 1200mm 20W 730 T8 AP I G	20 kWh	A+
929001299908	LEDtube HO 600mm 10W 730 T8 AP I G	10 kWh	A+
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	8 kWh	A++
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	8 kWh	A++
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	8 kWh	A++
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	16 kWh	A++
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	16 kWh	A++
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	16 kWh	A++

## Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
929001184538	LEDtube 1200mm 16W 740 T8 AP I G	220-240 V	16 W
929001184638	LEDtube 1200mm 16W 765 T8 AP I G	220-240 V	16 W
929001184738	LEDtube 600mm 8W 740 T8 AP I G	220-240 V	8 W
929001184838	LEDtube 600mm 8W 765 T8 AP I G	220-240 V	8 W
929001277208	LEDtube HO 1200mm 20W 740 T8 AP I G	220-240 V	20 W
929001277308	LEDtube HO 1200mm 20W 765 T8 AP I G	220-240 V	20 W
929001277408	LEDtube HO 600mm 10W 740 T8 AP I G	220-240 V	10 W
929001277508	LEDtube HO 600mm 10W 765 T8 AP I G	220-240 V	10 W
929001299808	LEDtube HO 1200mm 20W 730 T8 AP I G	220-240 V	20 W

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
929001299908	LEDtube HO 600mm 10W 730 T8 AP I G	220-240 V	10 W
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	100-240 V	8 W
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	100-240 V	8 W
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	100-240 V	8 W
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	100-240 V	16 W
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	100-240 V	16 W
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	100-240 V	16 W

## General Information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)
929001184538	LEDtube 1200mm 16W 740 T8 AP I G	G13	15000 h
929001184638	LEDtube 1200mm 16W 765 T8 AP I G	G13	15000 h
929001184738	LEDtube 600mm 8W 740 T8 AP I G	G13	15000 h
929001184838	LEDtube 600mm 8W 765 T8 AP I G	G13	15000 h
929001277208	LEDtube HO 1200mm 20W 740 T8 AP I G	G13	15000 h
929001277308	LEDtube HO 1200mm 20W 765 T8 AP I G	G13	15000 h
929001277408	LEDtube HO 600mm 10W 740 T8 AP I G	G13	15000 h
929001277508	LEDtube HO 600mm 10W 765 T8 AP I G	G13	15000 h
929001299808	LEDtube HO 1200mm 20W 730 T8 AP I G	G13	15000 h

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)
929001299908	LEDtube HO 600mm 10W 730 T8 AP I G	G13	15000 h
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	G5	30000 h
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	G5	30000 h
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	G5	30000 h
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	G5	30000 h

## Essential LEDtube

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	G5	30000 h

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	G5	30000 h

### Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)	Colour Rendering Index (Nom)	Luminous Flux (Nom)
929001184538	LEDtube 1200mm 16W 740 T8 AP I G	740	4000 K	73	1600 lm
929001184638	LEDtube 1200mm 16W 765 T8 AP I G	765	6500 K	73	1600 lm
929001184738	LEDtube 600mm 8W 740 T8 AP I G	740	4000 K	73	800 lm
929001184838	LEDtube 600mm 8W 765 T8 AP I G	765	6500 K	73	800 lm
929001277208	LEDtube HO 1200mm 20W 740 T8 AP I G	740	4000 K	70	2100 lm
929001277308	LEDtube HO 1200mm 20W 765 T8 AP I G	765	6500 K	70	2100 lm
929001277408	LEDtube HO 600mm 10W 740 T8 AP I G	740	4000 K	70	1050 lm
929001277508	LEDtube HO 600mm 10W 765 T8 AP I G	765	6500 K	70	1050 lm
929001299808	LEDtube HO 1200mm 20W 730 T8 AP I G	730	3000 K	70	1900 lm

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)	Colour Rendering Index (Nom)	Luminous Flux (Nom)
929001299908	LEDtube HO 600mm 10W 730 T8 AP I G	730	3000 K	70	950 lm
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	830	3000 K	80	1000 lm
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	840	4000 K	80	1050 lm
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	865	6500 K	80	1050 lm
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	830	3000 K	80	2000 lm
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	840	4000 K	80	2100 lm
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	865	6500 K	80	2100 lm

### Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001184538	LEDtube 1200mm 16W 740 T8 AP I G	60 °C
929001184638	LEDtube 1200mm 16W 765 T8 AP I G	60 °C
929001184738	LEDtube 600mm 8W 740 T8 AP I G	60 °C
929001184838	LEDtube 600mm 8W 765 T8 AP I G	60 °C
929001277208	LEDtube HO 1200mm 20W 740 T8 AP I G	65 °C
929001277308	LEDtube HO 1200mm 20W 765 T8 AP I G	65 °C
929001277408	LEDtube HO 600mm 10W 740 T8 AP I G	65 °C
929001277508	LEDtube HO 600mm 10W 765 T8 AP I G	65 °C
929001299808	LEDtube HO 1200mm 20W 730 T8 AP I G	65 °C
929001299908	LEDtube HO 600mm 10W 730 T8 AP I G	65 °C
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	70 °C
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	70 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	70 °C
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	70 °C
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	70 °C
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	70 °C

# Essential LEDtube

