



Superior color rendering

High CRI T12

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Benefits

- Low mercury and TCLP compliant*
- Reduced maintenance costs with fewer relamping cycles
- *The EPA's TCLP test is used to determine if an item can be managed as hazardous or non-hazardous waste. Philips ALTO and ALTO II lamps are TCLP compliant and can be managed as non-hazardous waste.

Features

- Up to 90 CRI
- Operates on magnetic or electronic ballast
- Direct retrofit for current T12 solution

Application

- Ideal for applications requiring superior color and continuous maintained light output.

High CRI T12

Versions



G13, T12-UR



G13, T12





G13, T12



FA8, T12

Dimensional drawing



Product

F40T12/CWSupreme/PLUS/ALTO 30PK

Product

F96T12/C50Supreme/ALTO 15pk

F96T12/CW Supreme/ALTO 15PK


Product

FB40/T12/CW Supreme/6 12PK

FB40/T12/NX/6 12PK

High CRI T12

Dimensional drawing



Product
F40T12/NX/ALTO 30PK
F40T12/CWSupreme/ALTO
F40T12/C50Supreme/ALTO 30pk

Approval and Application

Order Code	Full Product Name	Energy Saving Product	Mercury (Hg) Content (Nom)
423087	FB40/T12/CW Supreme/6 12PK	Not Applicable	10.0 mg
423095	FB40/T12/NX/6 12PK	Not Applicable	10.0 mg
423129	F40T12/CWSupreme/PLUS/ALTO 30PK	Energy Saving	4.4 mg
423889	F40T12/CWSupreme/ALTO	Energy Saving	4.4 mg

Order Code	Full Product Name	Energy Saving Product	Mercury (Hg) Content (Nom)
423897	F40T12/C50Supreme/ALTO 30pk	Energy Saving	4.4 mg
423186	F40T12/NX/ALTO 30PK	Energy Saving	4.4 mg
423871	F96T12/C50Supreme/ALTO 15pk	Energy Saving	6.8 mg
423194	F96T12/CW Supreme/ALTO 15PK	Energy Saving	6.8 mg

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
423087	FB40/T12/CW Supreme/6 12PK	40 W
423095	FB40/T12/NX/6 12PK	40 W
423129	F40T12/CWSupreme/PLUS/ALTO 30PK	40 W
423889	F40T12/CWSupreme/ALTO	40 W

Order Code	Full Product Name	Power (Rated) (Nom)
423897	F40T12/C50Supreme/ALTO 30pk	40 W
423186	F40T12/NX/ALTO 30PK	40 W
423871	F96T12/C50Supreme/ALTO 15pk	75 W
423194	F96T12/CW Supreme/ALTO 15PK	75 W

General Information

Order Code	Full Product Name	Cap-Base	Life 12-Hr Start [Hrs]	Life 3-Hr Start [Hrs]	System Description
423087	FB40/T12/CW Supreme/6 12PK	G13	-	18000 h	-
423095	FB40/T12/NX/6 12PK	G13	-	18000 h	-
423129	F40T12/CWSupreme/PLUS/ALTO 30PK	G13	30000 h	24000 h	-
423889	F40T12/CWSupreme/ALTO	G13	24000 h	20000 h	RS

Order Code	Full Product Name	Cap-Base	Life 12-Hr Start [Hrs]	Life 3-Hr Start [Hrs]	System Description
423897	F40T12/C50Supreme/ALTO 30pk	G13	24000 h	20000 h	-
423186	F40T12/NX/ALTO 30PK	G13	24000 h	20000 h	-
423871	F96T12/C50Supreme/ALTO 15pk	FA8	-	12000 h	-
423194	F96T12/CW Supreme/ALTO 15PK	FA8	-	12000 h	-

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Design Mean Lumens	Luminous Flux (Nom)
423087	FB40/T12/CW Supreme/6 12PK	Cool White Supreme	4100 K	90	1955 lm	2300 lm
423095	FB40/T12/NX/6 12PK	Neutral DX	3500 K	90	1955 lm	2300 lm

High CRI T12

Order Code	Full Product Name	Color Designation	Correlated Color Temperature	Color Rendering Index		
			(Nom)	(Nom)	Design Mean Lumens	Luminous Flux (Nom)
423129	F40T12/CWSupreme/PLUS/ALTO 30PK	Cool White Supreme	4100 K	89	2200 lm	2550 lm
423889	F40T12/CWSupreme/ALTO	Cool White Supreme	4100 K	89	2250 lm	2600 lm
423897	F40T12/C50Supreme/ALTO 30pk	C50 Supreme	5000 K	90	2160 lm	2545 lm
423186	F40T12/NX/ALTO 30PK	Neutral DX	3500 K	88	2220 lm	2550 lm
423871	F96T12/C50Supreme/ALTO 15pk	C50 Supreme	5000 K	90	4250 lm	5000 lm
423194	F96T12/CW Supreme/ALTO 15PK	Cool White Supreme	4100 K	89	4250 lm	5000 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape	Order Code	Full Product Name	Bulb Shape
423087	FB40/T12/CW Supreme/6 12PK	T12-6U	423897	F40T12/C50Supreme/ALTO 30pk	T12
423095	FB40/T12/NX/6 12PK	T12-6U	423186	F40T12/NX/ALTO 30PK	T12
423129	F40T12/CWSupreme/PLUS/ALTO 30PK	T12	423871	F96T12/C50Supreme/ALTO 15pk	T12
423889	F40T12/CWSupreme/ALTO	T12	423194	F96T12/CW Supreme/ALTO 15PK	T12

