



Retail Sales T12

Retail Sales T12

High Performance, Long Life, Environmentally-Responsible Lamps. These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Versions





G13, T12

G13, T12

Retail Sales T12

Dimensional drawing



General information	
Cap-Base	G13
Mechanical and housing	
Bulb Shape	T12

Operating and electrical

Order Code	Full Product Name	Power (Nom)
141507	F14T12/SOFT WHITE/15 6PK	14 W
141465	F15T12/SOFT WHITE/18 6PK	15 W

Product
F14T12/SOFT WHITE/15 6PK
F15T12/SOFT WHITE/18 6pk

Product
F40T12/DAYLIGHT DELUXE/ALTO 30PK

Order Code	Full Product Name	Power (Nom)
409383	F40T12/DAYLIGHT DELUXE/ALTO 30PK	40 W

General information

Order Code	Full Product Name	Life 3-Hr Start [Hrs]	Life With 3 Hour Per Day Use
141507	F14T12/SOFT WHITE/15 6PK	9000 h	4 a
141465	F15T12/SOFT WHITE/18 6PK	9000 h	4 a

Order Code	Full Product Name	Life 3-Hr Start [Hrs]	Life With 3 Hour Per Day Use
409383	F40T12/DAYLIGHT DELUXE/ ALTO 30PK	20000 h	7 a

Light technical

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Design Mean Lumens	Luminous Flux (Nom)
141507	F14T12/SOFT WHITE/15 6PK	Ultralume 30	Ultralume 30	3000 K	85	560 lm	700 lm
141465	F15T12/SOFT WHITE/18 6PK	Ultralume 30	Ultralume 30	3000 K	85	720 lm	800 lm

Retail Sales T12

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color	Color Rendering	Design Mean	Luminous Flux (Nom)
				Temperature (Nom)	Index (Nom)	Lumens	
409383	F40T12/DAYLIGHT DELUXE/ALTO 30PK	57	Daylight Deluxe	6500 K	90	2025 lm	2325 lm

Approval and application

Order Code	Full Product Name	Energy Saving	Mercury (Hg)
		Product	Content (Nom)
141507	F14T12/SOFT WHITE/15 6PK	-	-
141465	F15T12/SOFT WHITE/18 6PK	-	-

Order Code	Full Product Name	Energy Saving	Mercury (Hg)
		Product	Content (Nom)
409383	F40T12/DAYLIGHT DELUXE/ALTO 30PK	Not Applicable	4.4 mg

