



Environmentally Responsible Lamps

U-Bent Rapid Start T12

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Benefits

- Sustainable Lighting Solution -Less mercury and fewer lamps in landfills, combined with energy efficiency, reduces the impact on the environment.
- 12 month warranty period.
- TCLP compliant*
- * Fluorescent lamps that are TCLP compliant reduce the amount of pollutants released into the environment.

Features

- Full Line of 6" Leg Spacing.
- Outstanding Lumen Performance.
- Reduces the impact on the environment.
- Low mercury.
- Available in 34 watts with 3000, 3500, 4100, and 5000 color temperatures. Available in 40 watts ultralume 3000,3500,4100 and Spec 30,35, and 41 color temperatures. Also available in 40 watts daylight deluxe.

Application

- Ideal for commercial applications with 2' x 2' fixtures.


U-Bent Rapid Start T12

Versions



G13, T12-UR

Dimensional drawing



Product

FB40DX/6 12PK

