



Environmentally Responsible Lamps

Preheat T8

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Benefits

- Sustainable lighting solution - Reduces the impact on the environment.
- Warranty Period: 12 months.

Features

- Requires a starter or preheat switch. Several seconds of warm-up time is required before starting.
- Available in 15 watts Daylight, Warm White, Cool White, Plant Light. 30 watts Daylight and Cool White.

Application

- Ideal for under cabinet replacement lighting.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Preheat T8

Versions



G13, T8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/CW 25PK	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
F15T8/D 25PK	1-1/8 in	17-1/4 in	17-1/2 in	17-7/16 in	17-13/16 in

Approval and application

Mercury (Hg) Content (Nom) 2.0 mg

Controls and dimming

Dimmable Yes

Operating and electrical

Lamp Current (Nom) 0.335 A

Voltage (Nom) 55 V

Power (Nom) 15.5 W

General information

Cap-Base G13

Life To 10% Failures (Nom) 10000 h

Life To 50% Failures (Nom) 13000 h

Light technical

Lumen Maintenance 10000 h (Nom) 75 %

Lumen Maintenance 2000 h (Nom) 90 %

Lumen Maintenance 5000 h (Nom) 80 %

Mechanical and housing

Bulb Shape T8

Light technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color	
				Temperature (Nom)	Color Rendering Index (Nom)
407197	F15T8/CW 25PK	33-640	Cool White (CW)	4100 K	63
407205	F15T8/D 25PK	54-765	Cool Daylight	6200 K	75

Preheat T8

Light technical (2/2)

Order Code	Full Product Name	Luminous Flux (Nom)	Order Code	Full Product Name	Luminous Flux (Nom)
407197	F15T8/CW 25PK	830 lm	407205	F15T8/D 25PK	725 lm

