



Retail Sales T8

Retail Sales T8

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Versions



G13, T8

Retail Sales T8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/COOL WHITE PLUS/18 ALTO SL 6	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
F15T8 BRIGHT WHITE/18 ALTO SL6	1-1/8 in	17-1/4 in	17-1/2 in	17-7/16 in	17-13/16 in

Approval and application

Mercury (Hg) Content (Nom)	2.0 mg
----------------------------	--------

Controls and dimming

Dimmable	Yes
----------	-----

Operating and electrical

Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V
Power (Nom)	15.5 W

General information

Cap-Base	G13
Life To 10% Failures (Nom)	10000 h
Life To 50% Failures (Nom)	13000 h

Mechanical and housing

Bulb Shape	T8
------------	----

Light technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color	Color Rendering
				Temperature (Nom)	Index (Nom)
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	33-640	Cool White (CW)	4100 K	63
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	830	Soft White	3000 K	83

Light technical (2/2)

Order Code	Full Product Name	Lumen	Lumen	Lumen	Luminous Flux (Nom)
		Maintenance 10000 h (Nom)	Maintenance 2000 h (Nom)	Maintenance 5000 h (Nom)	
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	75 %	90 %	80 %	830 lm
392126	F15T8 BRIGHT	-	93 %	88 %	990 lm

Order Code	Full Product Name	Lumen	Lumen	Lumen	Luminous Flux (Nom)
		Maintenance 10000 h (Nom)	Maintenance 2000 h (Nom)	Maintenance 5000 h (Nom)	
	WHITE/18 ALTO 6PK				

